

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908595

Luminaire Tested: DFN2DIP-PN3F0-090D080US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908595
REPORT IS A COMBINATION OF REPORTS P901114 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D080US840-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15723.6 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 154.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908595

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908595

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		55
1	98	94	90	87	90	87	84	81	73	71	69		61	59	58		50
2	90	83	77	72	82	76	71	67	65	61	58		54	52	49		44
3	82	73	66	60	75	68	62	57	58	53	49		48	45	42		40
4	75	65	57	51	69	60	54	48	51	46	42		43	40	37		36
5	69	58	50	44	64	54	47	42	46	41	37		39	35	32		32
6	64	52	44	39	59	49	42	37	42	36	32		36	31	28		30
7	59	47	40	34	55	44	37	32	38	33	29		32	28	25		27
8	55	43	36	30	51	40	33	29	35	29	26		30	26	23		25
9	51	39	32	27	47	37	30	26	32	27	23		28	23	20		23
10	48	36	29	24	44	34	28	23	30	24	21		25	21	19		22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4391	4391	4391
5°	4396	4318	4347
10°	4350	4231	4204
15°	4287	4088	3984
20°	4205	3892	3714
25°	4121	3673	3453
30°	4010	3449	3123
35°	3900	3209	2834
40°	3789	2960	2502
45°	3659	2685	2201
50°	3525	2407	1908
55°	3385	2111	1626
60°	3222	1802	1337
65°	3035	1487	1201
70°	2808	1195	1084
75°	2522	1046	982
80°	2109	868	846
85°	1432	564	624

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3659 cd/sqm

TEST NUMBER: P908595

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	2.2
10°-20°	966.5	6.1
20°-30°	1356.9	8.6
30°-40°	1479.1	9.4
40°-50°	1359.4	8.6
50°-60°	1067.6	6.8
60°-70°	694.9	4.4
70°-80°	357.7	2.3
80°-90°	96.1	0.6
90°-100°	89.9	0.6
100°-110°	335.1	2.1
110°-120°	888.9	5.7
120°-130°	1474.3	9.4
130°-140°	1566.0	10.0
140°-150°	1455.4	9.3
150°-160°	1170.1	7.4
160°-170°	754.0	4.8
170°-180°	259.5	1.7
0°-30°	2675.4	17.0
0°-40°	4154.5	26.4
0°-60°	6581.5	41.9
0°-90°	7730.3	49.2
90°-120°	1314.0	8.4
90°-150°	5809.7	36.9
90°-180°	7993.0	50.8
0°-180°	15723.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3756	3756	3756	3756	3756	
5°	3756	3739	3695	3726	3716	356
15°	3573	3535	3420	3355	3321	1007
25°	3243	3134	2910	2771	2720	1492
35°	2794	2621	2322	2108	2033	1749
45°	2284	2057	1700	1458	1377	1764
55°	1737	1472	1105	901	836	1552
65°	1173	897	592	476	466	1163
75°	625	387	272	248	245	661
85°	146	75	64	64	64	168
90°	2	24	39	49	53	15
95°	128	63	77	87	85	152
105°	600	659	120	142	150	641
115°	1134	1168	1217	304	162	1117
125°	1604	1630	1667	1681	1687	1430
135°	1985	2016	2034	2054	2050	1533
145°	2302	2300	2334	2348	2338	1440
155°	2535	2518	2541	2553	2537	1168
165°	2671	2660	2665	2679	2665	755
175°	2732	2719	2723	2736	2717	260
180°	2726	2726	2726	2726	2726	

TEST NUMBER: P908595

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3756.4	3756.4	3756.4	3756.4	3756.4
2.5°	3773.4	3756.4	3718.8	3753.2	3746.3
5°	3756.4	3739.4	3695.1	3725.7	3715.6
7.5°	3725.7	3705.5	3657.9	3671.3	3654.3
10°	3685.0	3661.2	3593.4	3582.9	3562.7
12.5°	3634.1	3603.5	3511.5	3491.3	3453.7
15°	3572.8	3535.3	3419.9	3355.3	3321.4
17.5°	3501.4	3447.0	3304.1	3229.4	3175.0
20°	3419.9	3351.7	3181.8	3097.1	3022.0
22.5°	3331.5	3253.3	3056.0	2940.5	2889.7
25°	3243.2	3134.2	2909.9	2770.7	2719.5
27.5°	3137.9	3022.0	2773.9	2614.1	2535.9
30°	3025.7	2896.2	2624.2	2451.1	2359.1
32.5°	2916.7	2760.2	2481.7	2277.7	2192.5
35°	2794.5	2621.0	2322.0	2107.8	2032.8
37.5°	2675.4	2488.3	2172.3	1937.5	1852.8
40°	2549.6	2345.8	2015.8	1774.5	1686.2
42.5°	2420.4	2203.0	1859.6	1607.9	1523.1
45°	2284.5	2056.6	1699.8	1458.1	1376.6
47.5°	2155.4	1914.1	1546.9	1305.3	1230.6
50°	2012.6	1771.2	1397.2	1162.5	1091.4
52.5°	1873.0	1618.0	1254.5	1030.1	965.5
55°	1737.0	1471.9	1104.7	901.0	836.4
57.5°	1597.8	1325.9	972.4	781.9	727.5
60°	1454.9	1183.0	832.8	659.6	605.2
62.5°	1315.8	1043.8	713.8	550.8	523.7
65°	1172.9	897.4	591.5	476.1	465.6
67.5°	1036.9	761.3	476.1	418.0	407.9
70°	894.1	629.0	394.3	360.3	346.6
72.5°	758.1	506.3	329.6	302.6	295.8
75°	625.4	387.4	272.0	248.1	244.9
77.5°	493.0	275.2	214.2	200.6	193.7
80°	370.4	197.3	163.0	149.7	149.7
82.5°	258.2	132.7	112.2	105.3	105.3
85°	146.0	74.6	64.5	64.5	64.5
87.5°	54.4	27.1	27.1	23.8	23.8
90°	1.9	23.6	39.4	49.4	53.2
92.5°	49.4	41.5	47.4	51.3	53.2
95°	128.2	63.0	76.9	86.9	84.8
97.5°	230.8	69.1	100.5	106.6	108.5
100°	349.3	79.0	112.5	128.2	132.1
102.5°	479.4	475.5	116.4	137.9	144.1
105°	599.8	659.0	120.4	142.0	150.0
107.5°	739.8	789.0	124.4	145.9	153.9
110°	874.1	915.3	345.4	148.0	155.8

TEST NUMBER: P908595

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1000.4	1035.7	1002.3	151.8	157.9
115°	1134.4	1167.9	1217.3	303.9	161.9
117.5°	1250.8	1290.2	1323.9	1041.6	524.8
120°	1381.1	1410.6	1446.2	1469.9	1203.5
122.5°	1491.4	1523.1	1562.7	1574.4	1576.5
125°	1603.9	1629.6	1667.1	1680.9	1686.8
127.5°	1706.5	1734.1	1763.9	1783.5	1785.4
130°	1803.2	1834.8	1856.4	1878.2	1876.3
132.5°	1901.9	1927.6	1949.2	1967.0	1965.1
135°	1984.8	2016.4	2034.0	2054.0	2049.9
137.5°	2071.5	2095.2	2115.1	2134.8	2128.9
140°	2156.3	2172.2	2193.8	2211.6	2201.7
142.5°	2227.6	2241.3	2266.8	2282.6	2272.7
145°	2302.5	2300.4	2333.9	2347.7	2337.8
147.5°	2367.4	2361.6	2395.0	2404.9	2397.1
150°	2430.6	2416.8	2448.4	2460.1	2450.3
152.5°	2483.9	2468.1	2497.6	2509.6	2495.8
155°	2535.2	2517.6	2541.2	2552.9	2537.3
157.5°	2576.6	2560.9	2578.7	2592.5	2576.6
160°	2612.2	2600.3	2612.2	2623.9	2610.1
162.5°	2643.6	2631.9	2641.7	2655.5	2637.8
165°	2671.3	2659.6	2665.4	2679.2	2665.4
167.5°	2693.0	2681.1	2687.2	2701.0	2683.2
170°	2710.9	2698.9	2702.9	2716.7	2698.9
172.5°	2722.6	2710.9	2714.8	2728.7	2710.9
175°	2732.4	2718.6	2722.6	2736.3	2716.7
177.5°	2736.3	2722.6	2724.6	2738.5	2720.7
180°	2726.5	2726.5	2726.5	2726.5	2726.5



TEST NUMBER: P908595

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.17	12.99	13.14	13.97	15.26	8.14	8.96	9.11	9.94	11.23
	3H	13.84	14.58	14.82	15.57	16.87	9.32	10.05	10.30	11.04	12.35
	4H	14.45	15.14	15.44	16.13	17.45	9.76	10.46	10.76	11.45	12.77
	6H	14.86	15.50	15.87	16.50	17.83	10.08	10.72	11.09	11.72	13.05
	8H	14.99	15.59	16.00	16.61	17.93	10.17	10.78	11.18	11.79	13.12
	12H	15.04	15.62	16.06	16.63	17.98	10.21	10.79	11.22	11.79	13.14
4H	2H	12.19	12.88	13.19	13.88	15.19	8.73	9.42	9.73	10.42	11.73
	3H	14.01	14.59	15.02	15.61	16.94	10.07	10.65	11.08	11.67	13.00
	4H	14.69	15.22	15.71	16.24	17.59	10.61	11.14	11.63	12.16	13.51
	6H	15.20	15.66	16.23	16.70	18.05	11.03	11.48	12.05	12.52	13.87
	8H	15.38	15.80	16.40	16.83	18.19	11.15	11.57	12.18	12.61	13.97
	12H	15.47	15.85	16.51	16.89	18.26	11.21	11.59	12.26	12.64	14.01
8H	4H	14.66	15.08	15.69	16.12	17.48	10.89	11.31	11.92	12.34	13.71
	6H	15.22	15.57	16.27	16.64	18.00	11.40	11.75	12.45	12.82	14.18
	8H	15.43	15.74	16.49	16.80	18.18	11.59	11.89	12.65	12.95	14.33
	12H	15.57	15.84	16.63	16.89	18.31	11.70	11.97	12.76	13.02	14.45
12H	4H	14.61	14.99	15.66	16.04	17.41	10.89	11.27	11.94	12.32	13.69
	6H	15.19	15.50	16.26	16.56	17.94	11.45	11.75	12.51	12.81	14.19
	8H	15.41	15.68	16.47	16.73	18.16	11.65	11.92	12.72	12.97	14.40