

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908374

Luminaire Tested: DFN2DIP-PN2F0-050D040US840-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P908374  
REPORT IS A COMBINATION OF REPORTS P899488 AND P896349  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN2F0-050D040US840-RLLFLL  
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7866.9 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 82  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9821  
Total Harmonic Distortion (THDi): 0.08  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P908374  
CATALOG NUMBER: DFN2DIP-PN2F0-050D040US840-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P908374

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US840-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	60	60	60	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	54	53	52	47
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45	48	46	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	43	41	39	35
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	32	29	26	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	30	26	24	21
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	27	24	21	19
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19	25	22	19	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4520	4520	4520
5°	4520	4439	4470
10°	4468	4342	4318
15°	4399	4189	4087
20°	4311	3982	3806
25°	4220	3752	3535
30°	4100	3517	3193
35°	3983	3266	2893
40°	3863	3006	2550
45°	3725	2720	2240
50°	3581	2432	1937
55°	3430	2125	1646
60°	3255	1805	1349
65°	3053	1482	1207
70°	2808	1181	1083
75°	2500	1022	971
80°	2057	831	822
85°	1345	517	585

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3725 cd/sqm



TEST NUMBER: P908374

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US840-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.6	2.5
10°-20°	536.9	6.8
20°-30°	753.8	9.6
30°-40°	821.7	10.4
40°-50°	755.2	9.6
50°-60°	593.1	7.5
60°-70°	386.1	4.9
70°-80°	198.7	2.5
80°-90°	54.4	0.7
90°-100°	79.1	1.0
100°-110°	251.2	3.2
110°-120°	429.8	5.5
120°-130°	565.3	7.2
130°-140°	634.5	8.1
140°-150°	622.2	7.9
150°-160°	522.0	6.6
160°-170°	346.2	4.4
170°-180°	121.0	1.5
0°-30°	1486.3	18.9
0°-40°	2308.0	29.3
0°-60°	3656.4	46.5
0°-90°	4295.6	54.6
90°-120°	760.1	9.7
90°-150°	2582.2	32.8
90°-180°	3571.0	45.4
0°-180°	7866.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2078	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1617	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1143	944	810	765	980
55°	965	818	614	500	465	862
65°	652	499	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	1	14	38	35	37	8
95°	56	67	69	69	67	63
105°	232	235	237	239	239	245
115°	431	438	436	434	431	427
125°	627	637	634	630	629	561
135°	812	823	826	825	822	627
145°	985	993	999	1000	996	616
155°	1126	1130	1133	1138	1135	519
165°	1226	1224	1224	1232	1227	346
175°	1275	1272	1270	1278	1271	121
180°	1278	1278	1278	1278	1278	



TEST NUMBER: P908374

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US840-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2086.9	2086.9	2086.9	2086.9	2086.9
2.5°	2096.3	2086.9	2066.1	2085.1	2081.2
5°	2086.9	2077.5	2052.9	2069.8	2064.3
7.5°	2069.8	2058.6	2032.2	2039.6	2030.1
10°	2047.2	2034.0	1996.3	1990.5	1979.2
12.5°	2018.9	2002.0	1950.9	1939.6	1918.7
15°	1984.9	1964.1	1900.0	1864.1	1845.2
17.5°	1945.2	1915.0	1835.6	1794.1	1763.8
20°	1900.0	1862.1	1767.7	1720.6	1678.9
22.5°	1850.9	1807.4	1697.8	1633.7	1605.4
25°	1801.7	1741.2	1616.6	1539.2	1510.8
27.5°	1743.2	1678.9	1541.1	1452.3	1408.9
30°	1680.9	1609.0	1457.9	1361.7	1310.6
32.5°	1620.4	1533.5	1378.8	1265.4	1218.1
35°	1552.5	1456.1	1290.0	1170.9	1129.3
37.5°	1486.3	1382.4	1206.9	1076.4	1029.4
40°	1416.4	1303.2	1119.8	985.8	936.8
42.5°	1344.7	1223.9	1033.1	893.2	846.2
45°	1269.2	1142.6	944.3	810.1	764.8
47.5°	1197.4	1063.4	859.4	725.2	683.7
50°	1118.1	984.0	776.3	645.8	606.3
52.5°	1040.6	898.9	696.9	572.3	536.4
55°	965.0	817.7	613.7	500.5	464.6
57.5°	887.7	736.6	540.2	434.4	404.1
60°	808.3	657.2	462.6	366.5	336.2
62.5°	730.9	579.9	396.6	306.0	290.9
65°	651.6	498.6	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.8	349.4	219.0	200.2	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.6
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.9	35.9	35.9
87.5°	30.3	15.0	15.0	13.2	13.2
90°	1.1	13.8	37.8	35.4	36.6
92.5°	23.8	32.3	33.5	34.6	34.6
95°	56.2	67.1	69.0	69.0	67.1
97.5°	93.6	103.6	107.9	107.9	107.9
100°	136.7	145.6	148.7	148.7	147.5
102.5°	182.2	188.7	193.0	194.1	193.0
105°	231.9	234.9	237.2	239.1	239.1
107.5°	281.1	285.8	285.8	286.5	281.1
110°	328.9	335.1	335.1	335.1	332.0



TEST NUMBER: P908374

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US840-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	380.5	387.1	385.9	382.8	380.5
115°	431.3	437.6	435.6	434.4	431.3
117.5°	481.8	490.3	484.9	481.8	478.8
120°	532.7	541.1	532.7	532.7	529.2
122.5°	578.9	589.7	584.3	581.2	578.9
125°	627.4	637.0	634.0	630.5	629.3
127.5°	674.8	686.7	682.5	677.8	674.8
130°	719.0	733.0	731.0	728.7	724.5
132.5°	768.7	779.5	780.3	774.9	771.8
135°	811.5	823.4	825.8	824.6	821.5
137.5°	859.3	868.9	870.8	870.0	865.5
140°	901.2	910.9	916.3	916.3	912.0
142.5°	944.4	954.0	957.0	958.3	954.0
145°	985.2	992.9	999.1	1000.3	996.0
147.5°	1021.8	1031.4	1036.0	1037.9	1033.7
150°	1059.6	1066.1	1070.4	1073.8	1070.4
152.5°	1093.1	1099.5	1105.0	1109.2	1105.0
155°	1126.5	1129.6	1133.1	1138.5	1135.0
157.5°	1155.5	1157.7	1159.6	1167.4	1162.0
160°	1181.2	1183.6	1184.7	1191.2	1186.6
162.5°	1205.1	1205.1	1206.3	1213.6	1208.2
165°	1225.6	1224.4	1224.4	1232.0	1226.7
167.5°	1244.1	1240.5	1240.5	1248.3	1242.8
170°	1257.9	1254.8	1253.6	1261.3	1254.8
172.5°	1267.5	1264.5	1263.2	1271.0	1264.5
175°	1275.3	1272.1	1269.8	1277.5	1271.0
177.5°	1279.5	1276.4	1274.0	1280.6	1274.0
180°	1277.5	1277.5	1277.5	1277.5	1277.5



TEST NUMBER: P908374  
 CATALOG NUMBER: DFN2DIP-PN2F0-050D040US840-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.69	13.56	13.61	14.50	15.70	8.66	9.53	9.58	10.46	11.67
	3H	14.35	15.13	15.29	16.07	17.30	9.83	10.61	10.77	11.56	12.79
	4H	14.95	15.68	15.90	16.63	17.87	10.27	11.01	11.22	11.96	13.20
	6H	15.35	16.03	16.32	16.99	18.24	10.58	11.26	11.54	12.21	13.47
	8H	15.47	16.12	16.44	17.09	18.34	10.66	11.31	11.63	12.28	13.53
	12H	15.53	16.14	16.50	17.11	18.38	10.70	11.31	11.67	12.28	13.55
4H	2H	12.71	13.44	13.66	14.39	15.63	9.25	9.98	10.20	10.93	12.17
	3H	14.52	15.13	15.48	16.11	17.36	10.58	11.19	11.55	12.17	13.43
	4H	15.20	15.75	16.17	16.73	18.01	11.12	11.67	12.09	12.65	13.93
	6H	15.69	16.17	16.68	17.17	18.45	11.52	12.00	12.51	13.00	14.27
	8H	15.86	16.31	16.85	17.30	18.59	11.64	12.09	12.63	13.08	14.37
	12H	15.94	16.35	16.95	17.35	18.65	11.70	12.10	12.70	13.11	14.40
8H	4H	15.16	15.61	16.15	16.60	17.89	11.39	11.83	12.37	12.83	14.12
	6H	15.71	16.08	16.72	17.11	18.40	11.88	12.25	12.90	13.29	14.58
	8H	15.91	16.24	16.93	17.26	18.56	12.06	12.39	13.08	13.41	14.72
	12H	16.04	16.32	17.06	17.34	18.69	12.17	12.45	13.19	13.47	14.82
12H	4H	15.12	15.52	16.12	16.53	17.82	11.39	11.79	12.40	12.80	14.10
	6H	15.68	16.01	16.70	17.03	18.34	11.93	12.25	12.95	13.27	14.58
	8H	15.89	16.18	16.91	17.19	18.54	12.12	12.41	13.15	13.43	14.78