

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911033

Luminaire Tested: DFN2DIP-PN2F0-020D020US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911033
REPORT IS A COMBINATION OF REPORTS P900981 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D020US850-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4391.6 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911033

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911033

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1869	1869	1869
5°	1869	1839	1853
10°	1851	1810	1825
15°	1821	1777	1783
20°	1781	1731	1740
25°	1742	1678	1691
30°	1692	1628	1629
35°	1646	1569	1564
40°	1589	1510	1502
45°	1532	1451	1439
50°	1470	1388	1365
55°	1404	1316	1297
60°	1330	1231	1219
65°	1248	1142	1127
70°	1145	1033	1027
75°	1003	903	931
80°	830	738	755
85°	562	467	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1532 cd/sqm

TEST NUMBER: P911033

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.8
10°-20°	228.6	5.2
20°-30°	335.9	7.6
30°-40°	390.1	8.9
40°-50°	389.6	8.9
50°-60°	339.7	7.7
60°-70°	251.1	5.7
70°-80°	142.1	3.2
80°-90°	38.8	0.9
90°-100°	24.7	0.6
100°-110°	92.0	2.1
110°-120°	244.0	5.6
120°-130°	404.8	9.2
130°-140°	429.9	9.8
140°-150°	399.6	9.1
150°-160°	321.3	7.3
160°-170°	207.0	4.7
170°-180°	71.2	1.6
0°-30°	645.7	14.7
0°-40°	1035.8	23.6
0°-60°	1765.1	40.2
0°-90°	2197.1	50.0
90°-120°	360.7	8.2
90°-150°	1595.0	36.3
90°-180°	2194.0	50.0
0°-180°	4391.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	1	6	11	14	15	4
95°	35	17	21	24	23	42
105°	165	181	33	39	41	176
115°	311	321	334	83	44	307
125°	440	447	458	462	463	393
135°	545	554	558	564	563	421
145°	632	632	641	645	642	395
155°	696	691	698	701	697	321
165°	733	730	732	736	732	207
175°	750	746	748	751	746	71
180°	749	749	749	749	749	

TEST NUMBER: P911033

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	0.6	6.5	10.8	13.5	14.6
92.5°	13.5	11.4	13.0	14.1	14.6
95°	35.2	17.3	21.1	23.8	23.3
97.5°	63.3	19.0	27.6	29.3	29.8
100°	95.9	21.6	30.8	35.2	36.3
102.5°	131.6	130.5	31.9	37.9	39.6
105°	164.7	180.9	33.0	38.9	41.1
107.5°	203.2	216.6	34.2	40.0	42.3
110°	240.0	251.3	94.8	40.7	42.8



TEST NUMBER: P911033

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.6	284.3	275.1	41.7	43.4
115°	311.4	320.6	334.3	83.4	44.5
117.5°	343.3	354.2	363.4	286.0	144.1
120°	379.2	387.3	397.0	403.6	330.4
122.5°	409.4	418.1	429.0	432.2	432.8
125°	440.4	447.4	457.7	461.5	463.1
127.5°	468.6	476.1	484.3	489.6	490.2
130°	495.1	503.7	509.7	515.7	515.1
132.5°	522.1	529.2	535.1	540.0	539.5
135°	545.0	553.6	558.4	563.9	562.8
137.5°	568.7	575.2	580.7	586.1	584.4
140°	592.0	596.4	602.3	607.2	604.5
142.5°	611.5	615.4	622.4	626.7	623.9
145°	632.1	631.6	640.8	644.6	641.9
147.5°	650.0	648.3	657.5	660.2	658.1
150°	667.3	663.5	672.2	675.4	672.7
152.5°	681.9	677.6	685.7	689.0	685.1
155°	696.0	691.1	697.7	700.9	696.6
157.5°	707.4	703.1	708.0	711.8	707.4
160°	717.2	713.9	717.2	720.4	716.6
162.5°	725.7	722.5	725.3	729.1	724.2
165°	733.4	730.2	731.7	735.6	731.7
167.5°	739.4	736.0	737.7	741.6	736.6
170°	744.2	740.9	742.0	745.8	740.9
172.5°	747.5	744.2	745.4	749.1	744.2
175°	750.1	746.4	747.5	751.2	745.8
177.5°	751.2	747.5	748.0	751.8	746.9
180°	748.6	748.6	748.6	748.6	748.6

TEST NUMBER: P911033

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US850-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.33	10.19	10.29	11.16	12.44	8.90	9.76	9.85	10.73	12.00
	3H	10.97	11.74	11.94	12.73	14.02	10.49	11.27	11.46	12.25	13.54
	4H	11.55	12.28	12.53	13.26	14.56	11.06	11.80	12.05	12.78	14.08
	6H	11.93	12.60	12.92	13.59	14.91	11.44	12.12	12.44	13.11	14.42
	8H	12.03	12.67	13.03	13.68	14.99	11.54	12.18	12.54	13.19	14.50
	12H	12.07	12.68	13.07	13.68	15.01	11.58	12.19	12.58	13.19	14.52
4H	2H	9.78	10.51	10.77	11.50	12.80	9.43	10.17	10.42	11.15	12.45
	3H	11.62	12.24	12.62	13.25	14.57	11.23	11.84	12.22	12.85	14.17
	4H	12.32	12.88	13.33	13.89	15.23	11.91	12.47	12.92	13.48	14.81
	6H	12.82	13.30	13.84	14.33	15.67	12.40	12.88	13.42	13.91	15.25
	8H	12.96	13.41	13.98	14.43	15.78	12.54	12.98	13.55	14.01	15.36
	12H	13.02	13.43	14.06	14.47	15.82	12.59	13.00	13.63	14.03	15.39
8H	4H	12.51	12.96	13.53	13.98	15.33	12.14	12.59	13.16	13.61	14.96
	6H	13.12	13.49	14.16	14.55	15.90	12.74	13.11	13.78	14.18	15.53
	8H	13.32	13.65	14.37	14.70	16.07	12.94	13.27	13.99	14.32	15.69
	12H	13.44	13.73	14.49	14.77	16.18	13.04	13.33	14.10	14.38	15.79
12H	4H	12.49	12.90	13.53	13.94	15.29	12.13	12.54	13.17	13.58	14.93
	6H	13.14	13.47	14.19	14.52	15.89	12.78	13.11	13.83	14.16	15.52
	8H	13.37	13.66	14.42	14.70	16.11	13.00	13.29	14.05	14.33	15.74