

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911053

Luminaire Tested: DFN2DIP-PN2F0-030D020US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911053
REPORT IS A COMBINATION OF REPORTS P900983 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D020US850-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5489.6 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 43.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911053

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911053

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		65
1	100	96	92	88	93	90	86	83	78	75	73		67	66	64		58
2	91	84	77	72	85	78	73	68	68	64	61		59	56	53		51
3	83	73	66	60	77	69	62	57	60	55	51		52	48	45		45
4	76	65	57	51	71	61	54	48	54	48	44		47	42	39		40
5	70	58	50	44	65	55	47	42	48	42	38		42	37	34		36
6	64	52	44	38	60	49	42	36	43	37	33		38	33	30		33
7	60	47	39	33	56	44	37	32	39	33	29		35	30	26		30
8	55	43	35	30	52	40	33	28	36	30	26		32	27	23		28
9	52	39	32	26	48	37	30	25	33	27	23		29	24	21		26
10	48	36	29	24	45	34	27	23	30	25	21		27	22	19		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2804	2804	2804
5°	2804	2759	2779
10°	2777	2716	2737
15°	2731	2665	2675
20°	2671	2597	2610
25°	2612	2517	2537
30°	2539	2442	2444
35°	2469	2354	2347
40°	2383	2265	2254
45°	2298	2176	2158
50°	2205	2082	2048
55°	2106	1974	1946
60°	1995	1846	1828
65°	1873	1713	1690
70°	1717	1551	1540
75°	1503	1356	1396
80°	1244	1107	1134
85°	845	700	710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2298 cd/sqm

TEST NUMBER: P911053

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	2.2
10°-20°	342.8	6.2
20°-30°	503.8	9.2
30°-40°	585.2	10.7
40°-50°	584.4	10.6
50°-60°	509.6	9.3
60°-70°	376.7	6.9
70°-80°	213.1	3.9
80°-90°	57.6	1.0
90°-100°	24.7	0.4
100°-110°	92.0	1.7
110°-120°	244.0	4.4
120°-130°	404.8	7.4
130°-140°	429.9	7.8
140°-150°	399.6	7.3
150°-160°	321.3	5.9
160°-170°	207.0	3.8
170°-180°	71.2	1.3
0°-30°	968.5	17.6
0°-40°	1553.6	28.3
0°-60°	2647.7	48.2
0°-90°	3295.1	60.0
90°-120°	360.7	6.6
90°-150°	1595.0	29.1
90°-180°	2194.0	40.0
0°-180°	5489.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1294	1294	1294	1294	1294	
5°	1294	1290	1276	1286	1283	123
15°	1232	1225	1209	1214	1208	347
25°	1115	1106	1084	1087	1084	513
35°	962	950	930	922	916	601
45°	783	774	756	742	737	604
55°	593	585	570	555	549	530
65°	400	392	380	368	362	395
75°	209	207	200	193	196	223
85°	51	50	49	45	44	57
90°	1	6	11	14	15	5
95°	35	17	21	24	23	42
105°	165	181	33	39	41	176
115°	311	321	334	83	44	307
125°	440	447	458	462	463	393
135°	545	554	558	564	563	421
145°	632	632	641	645	642	395
155°	696	691	698	701	697	321
165°	733	730	732	736	732	207
175°	750	746	748	751	746	71
180°	749	749	749	749	749	

TEST NUMBER: P911053

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1294.5	1294.5	1294.5	1294.5	1294.5
2.5°	1302.1	1295.9	1282.1	1294.5	1292.2
5°	1294.5	1289.7	1275.9	1285.9	1283.4
7.5°	1285.9	1278.5	1264.7	1274.8	1272.2
10°	1272.2	1263.5	1248.6	1258.5	1254.8
12.5°	1253.5	1246.1	1231.2	1237.3	1234.9
15°	1232.3	1225.0	1208.7	1213.7	1207.5
17.5°	1206.1	1198.8	1182.5	1188.7	1182.5
20°	1177.5	1170.1	1152.7	1156.4	1151.5
22.5°	1149.0	1137.8	1121.5	1121.5	1119.0
25°	1115.3	1105.5	1084.3	1086.7	1084.3
27.5°	1077.9	1069.2	1053.1	1049.4	1043.2
30°	1040.7	1030.7	1012.1	1008.3	1003.3
32.5°	1000.9	993.4	973.5	965.9	960.9
35°	962.3	949.9	929.9	922.4	916.1
37.5°	918.7	907.5	887.5	878.8	872.6
40°	873.9	863.9	843.9	832.9	827.9
42.5°	830.3	820.3	800.5	787.9	780.5
45°	783.1	774.3	755.6	741.9	736.9
47.5°	736.9	728.3	708.3	694.6	687.1
50°	688.4	682.1	664.7	647.3	641.1
52.5°	641.1	632.4	616.3	602.5	593.8
55°	592.6	585.1	570.1	555.3	549.1
57.5°	544.0	537.8	521.6	506.6	501.6
60°	495.4	490.5	473.1	459.3	455.7
62.5°	448.1	439.4	427.0	414.5	409.6
65°	399.7	392.1	379.7	368.5	362.3
67.5°	349.9	343.6	332.4	323.7	318.7
70°	303.8	298.8	287.6	278.8	273.9
72.5°	256.5	251.4	245.2	236.5	232.9
75°	209.0	206.7	200.4	193.0	195.5
77.5°	166.8	161.8	159.3	155.6	151.9
80°	124.5	123.2	120.7	117.0	114.6
82.5°	84.6	84.6	83.5	78.4	78.4
85°	51.0	49.8	48.6	44.8	43.6
87.5°	22.4	20.0	17.4	13.8	12.4
90°	0.6	6.5	10.8	13.5	14.6
92.5°	13.5	11.4	13.0	14.1	14.6
95°	35.2	17.3	21.1	23.8	23.3
97.5°	63.3	19.0	27.6	29.3	29.8
100°	95.9	21.6	30.8	35.2	36.3
102.5°	131.6	130.5	31.9	37.9	39.6
105°	164.7	180.9	33.0	38.9	41.1
107.5°	203.2	216.6	34.2	40.0	42.3
110°	240.0	251.3	94.8	40.7	42.8

TEST NUMBER: P911053

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.6	284.3	275.1	41.7	43.4
115°	311.4	320.6	334.3	83.4	44.5
117.5°	343.3	354.2	363.4	286.0	144.1
120°	379.2	387.3	397.0	403.6	330.4
122.5°	409.4	418.1	429.0	432.2	432.8
125°	440.4	447.4	457.7	461.5	463.1
127.5°	468.6	476.1	484.3	489.6	490.2
130°	495.1	503.7	509.7	515.7	515.1
132.5°	522.1	529.2	535.1	540.0	539.5
135°	545.0	553.6	558.4	563.9	562.8
137.5°	568.7	575.2	580.7	586.1	584.4
140°	592.0	596.4	602.3	607.2	604.5
142.5°	611.5	615.4	622.4	626.7	623.9
145°	632.1	631.6	640.8	644.6	641.9
147.5°	650.0	648.3	657.5	660.2	658.1
150°	667.3	663.5	672.2	675.4	672.7
152.5°	681.9	677.6	685.7	689.0	685.1
155°	696.0	691.1	697.7	700.9	696.6
157.5°	707.4	703.1	708.0	711.8	707.4
160°	717.2	713.9	717.2	720.4	716.6
162.5°	725.7	722.5	725.3	729.1	724.2
165°	733.4	730.2	731.7	735.6	731.7
167.5°	739.4	736.0	737.7	741.6	736.6
170°	744.2	740.9	742.0	745.8	740.9
172.5°	747.5	744.2	745.4	749.1	744.2
175°	750.1	746.4	747.5	751.2	745.8
177.5°	751.2	747.5	748.0	751.8	746.9
180°	748.6	748.6	748.6	748.6	748.6

TEST NUMBER: P911053

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US850-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.61	12.57	12.48	13.46	14.58	11.18	12.14	12.04	13.02	14.14
	3H	13.26	14.12	14.14	15.02	16.17	12.78	13.64	13.66	14.54	15.69
	4H	13.84	14.65	14.73	15.56	16.71	13.36	14.17	14.25	15.07	16.23
	6H	14.23	14.98	15.14	15.89	17.06	13.74	14.49	14.65	15.40	16.57
	8H	14.33	15.04	15.24	15.97	17.14	13.84	14.56	14.76	15.48	16.65
	12H	14.37	15.05	15.29	15.97	17.17	13.88	14.56	14.80	15.48	16.68
4H	2H	12.08	12.89	12.98	13.79	14.95	11.73	12.54	12.63	13.44	14.60
	3H	13.93	14.61	14.84	15.54	16.71	13.53	14.21	14.44	15.14	16.31
	4H	14.63	15.25	15.55	16.18	17.38	14.22	14.84	15.14	15.77	16.96
	6H	15.13	15.67	16.07	16.62	17.82	14.71	15.25	15.65	16.20	17.40
	8H	15.27	15.77	16.21	16.72	17.93	14.85	15.35	15.79	16.30	17.51
	12H	15.34	15.79	16.30	16.76	17.98	14.91	15.36	15.87	16.32	17.54
8H	4H	14.82	15.32	15.76	16.27	17.48	14.46	14.96	15.39	15.90	17.11
	6H	15.43	15.85	16.40	16.84	18.05	15.06	15.48	16.03	16.46	17.67
	8H	15.64	16.01	16.62	16.99	18.22	15.26	15.63	16.24	16.61	17.84
	12H	15.76	16.09	16.74	17.06	18.34	15.37	15.69	16.35	16.66	17.94
12H	4H	14.81	15.26	15.77	16.23	17.45	14.45	14.90	15.41	15.87	17.08
	6H	15.46	15.83	16.43	16.81	18.03	15.10	15.46	16.07	16.44	17.67
	8H	15.69	16.01	16.67	16.99	18.26	15.32	15.64	16.30	16.62	17.89