

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911226

Luminaire Tested: DFN2DIP-PN3F0-060D050US850-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P911226  
REPORT IS A COMBINATION OF REPORTS P899546 AND P896399  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-060D050US850-RLLFLL  
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10563.3 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 94.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9821  
Total Harmonic Distortion (THDi): 0.08  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P911226  
CATALOG NUMBER: DFN2DIP-PN3F0-060D050US850-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P911226

CATALOG NUMBER: DFN2DIP-PN3F0-060D050US850-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54	54	54	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46	46	46	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39	39	39	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34	34	34	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33	30	30	30	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26	26	26	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	23	23	23	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21	21	21	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19	19	19	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17	17	17	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3215	3215	3215
5°	3218	3162	3183
10°	3184	3097	3078
15°	3139	2993	2916
20°	3079	2850	2719
25°	3017	2689	2528
30°	2936	2525	2287
35°	2855	2349	2075
40°	2774	2167	1832
45°	2679	1966	1612
50°	2581	1762	1397
55°	2478	1545	1190
60°	2359	1319	978
65°	2222	1089	879
70°	2056	874	793
75°	1847	766	719
80°	1544	635	619
85°	1049	413	457

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2679 cd/sqm



TEST NUMBER: P911226

CATALOG NUMBER: DFN2DIP-PN3F0-060D050US850-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	257.7	2.4
10°-20°	707.6	6.7
20°-30°	993.4	9.4
30°-40°	1082.8	10.3
40°-50°	995.2	9.4
50°-60°	781.6	7.4
60°-70°	508.8	4.8
70°-80°	261.9	2.5
80°-90°	71.8	0.7
90°-100°	108.5	1.0
100°-110°	344.8	3.3
110°-120°	590.1	5.6
120°-130°	776.0	7.3
130°-140°	871.0	8.2
140°-150°	854.2	8.1
150°-160°	716.5	6.8
160°-170°	475.2	4.5
170°-180°	166.1	1.6
0°-30°	1958.7	18.5
0°-40°	3041.5	28.8
0°-60°	4818.4	45.6
0°-90°	5660.9	53.6
90°-120°	1043.4	9.9
90°-150°	3544.6	33.6
90°-180°	4902.0	46.4
0°-180°	10563.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	2	19	52	49	50	10
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P911226

CATALOG NUMBER: DFN2DIP-PN3F0-060D050US850-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P911226

CATALOG NUMBER: DFN2DIP-PN3F0-060D050US850-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P911226  
 CATALOG NUMBER: DFN2DIP-PN3F0-060D050US850-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.49	12.35	12.43	13.30	14.52	7.46	8.32	8.39	9.27	10.49
	3H	13.17	13.94	14.11	14.89	16.14	8.64	9.41	9.59	10.37	11.61
	4H	13.77	14.50	14.73	15.46	16.71	9.09	9.82	10.05	10.78	12.03
	6H	14.19	14.86	15.16	15.83	17.09	9.41	10.08	10.38	11.04	12.31
	8H	14.32	14.95	15.29	15.93	17.20	9.50	10.13	10.47	11.12	12.38
	12H	14.38	14.98	15.36	15.96	17.25	9.54	10.15	10.52	11.12	12.41
4H	2H	11.51	12.24	12.48	13.20	14.45	8.06	8.78	9.02	9.74	11.00
	3H	13.34	13.94	14.31	14.93	16.20	9.40	10.01	10.38	11.00	12.26
	4H	14.03	14.58	15.01	15.56	16.85	9.95	10.50	10.93	11.48	12.77
	6H	14.54	15.01	15.53	16.02	17.31	10.36	10.83	11.36	11.84	13.13
	8H	14.71	15.15	15.71	16.15	17.46	10.49	10.93	11.48	11.93	13.23
	12H	14.80	15.20	15.82	16.22	17.53	10.55	10.95	11.56	11.96	13.27
8H	4H	14.00	14.44	14.99	15.44	16.74	10.22	10.67	11.22	11.67	12.97
	6H	14.56	14.92	15.58	15.96	17.27	10.74	11.10	11.76	12.14	13.45
	8H	14.77	15.09	15.80	16.12	17.44	10.92	11.24	11.95	12.27	13.59
	12H	14.90	15.19	15.94	16.21	17.58	11.04	11.32	12.07	12.34	13.71
12H	4H	13.95	14.35	14.96	15.36	16.67	10.23	10.63	11.24	11.64	12.95
	6H	14.53	14.85	15.56	15.88	17.20	10.78	11.11	11.81	12.13	13.46
	8H	14.75	15.03	15.78	16.05	17.42	10.99	11.27	12.02	12.30	13.66