

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911274

Luminaire Tested: DFN2DIP-PN3F0-080D030US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911274
REPORT IS A COMBINATION OF REPORTS P899522 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D030US850-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10485.6 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 103.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911274

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911274

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	96	96	96	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	49	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4286	4286	4286
5°	4291	4215	4244
10°	4246	4130	4104
15°	4185	3990	3889
20°	4105	3799	3625
25°	4023	3586	3371
30°	3914	3367	3049
35°	3807	3132	2766
40°	3698	2890	2442
45°	3572	2621	2149
50°	3441	2350	1862
55°	3304	2061	1587
60°	3145	1759	1305
65°	2963	1452	1172
70°	2741	1166	1058
75°	2462	1021	959
80°	2058	847	825
85°	1399	551	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3572 cd/sqm

TEST NUMBER: P911274

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	3.3
10°-20°	943.4	9.0
20°-30°	1324.5	12.6
30°-40°	1443.8	13.8
40°-50°	1327.0	12.7
50°-60°	1042.1	9.9
60°-70°	678.3	6.5
70°-80°	349.2	3.3
80°-90°	92.1	0.9
90°-100°	65.1	0.6
100°-110°	206.9	2.0
110°-120°	354.0	3.4
120°-130°	465.6	4.4
130°-140°	522.6	5.0
140°-150°	512.5	4.9
150°-160°	429.9	4.1
160°-170°	285.1	2.7
170°-180°	99.7	1.0
0°-30°	2611.6	24.9
0°-40°	4055.4	38.7
0°-60°	6424.5	61.3
0°-90°	7544.2	71.9
90°-120°	626.0	6.0
90°-150°	2126.7	20.3
90°-180°	2941.0	28.0
0°-180°	10485.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	1	11	31	29	30	10
95°	46	55	57	57	55	52
105°	191	194	195	197	197	202
115°	355	360	359	358	355	351
125°	517	525	522	519	518	462
135°	668	678	680	679	677	517
145°	812	818	823	824	820	507
155°	928	930	933	938	935	427
165°	1009	1008	1008	1015	1010	285
175°	1050	1048	1046	1052	1047	100
180°	1052	1052	1052	1052	1052	

TEST NUMBER: P911274

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	1.0	11.4	31.1	29.2	30.2
92.5°	19.6	26.6	27.6	28.5	28.5
95°	46.4	55.2	56.8	56.8	55.2
97.5°	77.1	85.3	88.8	88.8	88.8
100°	112.6	119.9	122.4	122.4	121.5
102.5°	150.0	155.5	158.9	159.9	158.9
105°	191.0	193.5	195.4	197.0	197.0
107.5°	231.6	235.3	235.3	236.0	231.6
110°	270.9	276.0	276.0	276.0	273.5

TEST NUMBER: P911274

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	318.8	317.8	315.3	313.4
115°	355.3	360.3	358.8	357.9	355.3
117.5°	396.8	403.8	399.4	396.8	394.2
120°	438.7	445.7	438.7	438.7	435.8
122.5°	476.8	485.6	481.2	478.6	476.8
125°	516.8	524.7	522.1	519.2	518.3
127.5°	555.7	565.6	562.2	558.3	555.7
130°	592.2	603.6	602.1	600.2	596.6
132.5°	633.1	642.0	642.7	638.2	635.7
135°	668.4	678.2	680.1	679.2	676.6
137.5°	707.7	715.6	717.2	716.6	712.8
140°	742.3	750.2	754.7	754.7	751.1
142.5°	777.9	785.7	788.3	789.3	785.7
145°	811.5	817.8	822.9	823.8	820.3
147.5°	841.6	849.5	853.3	854.9	851.4
150°	872.7	878.1	881.5	884.4	881.5
152.5°	900.3	905.6	910.0	913.6	910.0
155°	927.9	930.3	933.2	937.7	934.9
157.5°	951.6	953.5	955.2	961.5	957.1
160°	972.9	974.8	975.8	981.1	977.4
162.5°	992.6	992.6	993.6	999.5	995.1
165°	1009.4	1008.4	1008.4	1014.7	1010.3
167.5°	1024.6	1021.7	1021.7	1028.0	1023.6
170°	1036.0	1033.5	1032.6	1038.9	1033.5
172.5°	1043.9	1041.5	1040.5	1046.8	1041.5
175°	1050.3	1047.8	1045.9	1052.2	1046.8
177.5°	1053.8	1051.2	1049.3	1054.8	1049.3
180°	1052.2	1052.2	1052.2	1052.2	1052.2

TEST NUMBER: P911274

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.01	15.06	14.76	15.82	16.74	9.97	11.02	10.72	11.79	12.71
	3H	15.70	16.63	16.46	17.41	18.36	11.17	12.11	11.94	12.89	13.84
	4H	16.31	17.19	17.09	17.98	18.94	11.63	12.51	12.41	13.30	14.26
	6H	16.74	17.55	17.53	18.35	19.32	11.96	12.77	12.75	13.56	14.54
	8H	16.87	17.64	17.67	18.46	19.43	12.05	12.82	12.85	13.64	14.62
	12H	16.93	17.67	17.74	18.48	19.48	12.10	12.84	12.91	13.64	14.65
4H	2H	14.05	14.93	14.84	15.72	16.68	10.59	11.48	11.38	12.26	13.23
	3H	15.89	16.63	16.69	17.45	18.43	11.96	12.69	12.75	13.51	14.49
	4H	16.59	17.25	17.40	18.07	19.08	12.51	13.17	13.32	13.99	15.00
	6H	17.11	17.68	17.94	18.53	19.54	12.93	13.51	13.76	14.35	15.37
	8H	17.29	17.82	18.12	18.66	19.69	13.06	13.60	13.89	14.44	15.46
	12H	17.39	17.87	18.24	18.73	19.76	13.13	13.61	13.98	14.47	15.51
8H	4H	16.57	17.11	17.40	17.95	18.97	12.80	13.34	13.63	14.17	15.20
	6H	17.14	17.58	18.00	18.46	19.49	13.32	13.76	14.18	14.64	15.67
	8H	17.35	17.75	18.22	18.62	19.67	13.50	13.90	14.38	14.78	15.82
	12H	17.49	17.84	18.37	18.71	19.81	13.63	13.97	14.50	14.84	15.94
12H	4H	16.53	17.01	17.38	17.88	18.91	12.81	13.29	13.66	14.16	15.19
	6H	17.11	17.51	17.98	18.39	19.43	13.36	13.76	14.24	14.64	15.68
	8H	17.34	17.69	18.21	18.55	19.65	13.58	13.93	14.45	14.79	15.90

END OF REPORT