

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911294

Luminaire Tested: DFN2DIP-PN3F0-080D080US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911294
REPORT IS A COMBINATION OF REPORTS P899592 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D080US850-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15392.9 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 141.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911294

CATALOG NUMBER: DFN2DIP-PN3F0-080D080US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911294

CATALOG NUMBER: DFN2DIP-PN3F0-080D080US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83		68	68	68		55
1	98	94	90	87	90	87	84	81	73	71	69		61	59	58		50
2	90	83	77	72	82	76	71	67	65	61	58		54	51	49		44
3	82	73	66	60	75	68	61	57	58	53	49		48	45	42		40
4	75	65	57	51	69	60	54	48	51	46	42		43	40	36		36
5	69	58	50	44	64	54	47	42	46	41	37		39	35	32		32
6	64	52	44	39	59	49	42	37	42	36	32		35	31	28		30
7	59	47	40	34	55	44	37	32	38	33	29		32	28	25		27
8	55	43	36	30	51	40	33	29	35	29	26		30	26	23		25
9	51	39	32	27	47	37	30	26	32	27	23		27	23	20		23
10	48	36	29	24	44	34	28	23	30	24	21		25	21	19		22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4286	4286	4286
5°	4291	4215	4244
10°	4246	4130	4104
15°	4185	3990	3889
20°	4105	3799	3625
25°	4023	3586	3371
30°	3914	3367	3049
35°	3807	3132	2766
40°	3698	2890	2442
45°	3572	2621	2149
50°	3441	2350	1862
55°	3304	2061	1587
60°	3145	1759	1305
65°	2963	1452	1172
70°	2741	1166	1058
75°	2462	1021	959
80°	2058	847	825
85°	1399	551	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3572 cd/sqm

TEST NUMBER: P911294

CATALOG NUMBER: DFN2DIP-PN3F0-080D080US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	2.2
10°-20°	943.4	6.1
20°-30°	1324.5	8.6
30°-40°	1443.8	9.4
40°-50°	1327.0	8.6
50°-60°	1042.1	6.8
60°-70°	678.3	4.4
70°-80°	349.2	2.3
80°-90°	97.1	0.6
90°-100°	173.6	1.1
100°-110°	551.7	3.6
110°-120°	944.1	6.1
120°-130°	1241.6	8.1
130°-140°	1393.7	9.1
140°-150°	1366.6	8.9
150°-160°	1146.4	7.4
160°-170°	760.3	4.9
170°-180°	265.7	1.7
0°-30°	2611.6	17.0
0°-40°	4055.4	26.3
0°-60°	6424.5	41.7
0°-90°	7549.2	49.0
90°-120°	1669.4	10.8
90°-150°	5671.3	36.8
90°-180°	7844.0	51.0
0°-180°	15392.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	3	30	83	78	80	15
95°	124	147	151	151	147	137
105°	509	516	521	525	525	537
115°	947	961	957	954	947	937
125°	1378	1399	1392	1385	1382	1231
135°	1782	1809	1814	1811	1804	1378
145°	2164	2181	2194	2197	2188	1352
155°	2474	2481	2489	2500	2493	1139
165°	2692	2689	2689	2706	2694	759
175°	2801	2794	2789	2806	2792	266
180°	2806	2806	2806	2806	2806	

TEST NUMBER: P911294

CATALOG NUMBER: DFN2DIP-PN3F0-080D080US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	2.6	30.5	83.0	77.9	80.4
92.5°	52.5	71.1	73.6	76.1	76.1
95°	123.5	147.2	151.4	151.4	147.2
97.5°	205.6	227.6	236.9	236.9	236.9
100°	300.3	319.7	326.5	326.5	323.9
102.5°	400.1	414.5	423.7	426.3	423.7
105°	509.3	516.0	521.1	525.3	525.3
107.5°	617.5	627.7	627.7	629.4	617.5
110°	722.4	735.9	735.9	735.9	729.2

TEST NUMBER: P911294

CATALOG NUMBER: DFN2DIP-PN3F0-080D080US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	835.7	850.2	847.6	840.8	835.7
115°	947.4	960.9	956.7	954.2	947.4
117.5°	1058.2	1076.8	1065.0	1058.2	1051.4
120°	1169.9	1188.5	1169.9	1169.9	1162.2
122.5°	1271.4	1295.1	1283.2	1276.5	1271.4
125°	1377.9	1399.1	1392.3	1384.7	1382.3
127.5°	1482.1	1508.2	1498.9	1488.8	1482.1
130°	1579.3	1609.7	1605.5	1600.5	1591.2
132.5°	1688.5	1712.1	1713.8	1702.0	1695.2
135°	1782.3	1808.6	1813.7	1811.1	1804.3
137.5°	1887.2	1908.4	1912.6	1910.9	1900.7
140°	1979.5	2000.5	2012.4	2012.4	2003.1
142.5°	2074.2	2095.3	2102.1	2104.7	2095.3
145°	2163.9	2180.7	2194.3	2196.8	2187.5
147.5°	2244.2	2265.4	2275.4	2279.8	2270.5
150°	2327.1	2341.4	2350.7	2358.4	2350.7
152.5°	2400.7	2415.1	2426.9	2436.3	2426.9
155°	2474.3	2481.1	2488.7	2500.5	2492.9
157.5°	2537.7	2542.8	2547.0	2563.9	2552.1
160°	2594.4	2599.5	2602.0	2616.4	2606.3
162.5°	2646.9	2646.9	2649.4	2665.5	2653.6
165°	2691.7	2689.1	2689.1	2706.1	2694.2
167.5°	2732.2	2724.7	2724.7	2741.6	2729.7
170°	2762.7	2756.0	2753.4	2770.4	2756.0
172.5°	2783.9	2777.2	2774.6	2791.5	2777.2
175°	2800.8	2794.0	2788.9	2805.9	2791.5
177.5°	2810.1	2803.3	2798.2	2812.6	2798.2
180°	2805.9	2805.9	2805.9	2805.9	2805.9

TEST NUMBER: P911294

CATALOG NUMBER: DFN2DIP-PN3F0-080D080US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.07	12.90	13.04	13.88	15.16	8.04	8.86	9.01	9.84	11.13
	3H	13.74	14.48	14.73	15.47	16.78	9.22	9.96	10.20	10.95	12.26
	4H	14.35	15.04	15.34	16.04	17.36	9.67	10.36	10.66	11.36	12.67
	6H	14.76	15.40	15.77	16.40	17.73	9.98	10.62	10.99	11.62	12.95
	8H	14.89	15.50	15.90	16.51	17.84	10.07	10.68	11.08	11.69	13.02
	12H	14.95	15.53	15.96	16.53	17.89	10.11	10.69	11.13	11.70	13.05
4H	2H	12.09	12.78	13.09	13.78	15.10	8.63	9.33	9.63	10.32	11.64
	3H	13.91	14.49	14.92	15.51	16.84	9.97	10.55	10.98	11.57	12.91
	4H	14.60	15.13	15.62	16.14	17.50	10.52	11.04	11.53	12.06	13.41
	6H	15.11	15.56	16.14	16.60	17.95	10.93	11.38	11.96	12.42	13.77
	8H	15.28	15.70	16.31	16.73	18.10	11.05	11.48	12.08	12.51	13.87
	12H	15.37	15.75	16.42	16.80	18.17	11.11	11.50	12.16	12.54	13.91
8H	4H	14.56	14.99	15.59	16.02	17.38	10.79	11.22	11.82	12.25	13.61
	6H	15.12	15.47	16.18	16.55	17.91	11.30	11.65	12.36	12.72	14.09
	8H	15.33	15.64	16.40	16.70	18.08	11.49	11.80	12.55	12.85	14.24
	12H	15.47	15.74	16.53	16.79	18.22	11.60	11.87	12.67	12.93	14.35
12H	4H	14.51	14.90	15.56	15.94	17.31	10.79	11.18	11.84	12.22	13.60
	6H	15.10	15.40	16.16	16.46	17.85	11.35	11.66	12.41	12.72	14.10
	8H	15.31	15.58	16.38	16.64	18.06	11.55	11.82	12.62	12.88	14.30