

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913805

Luminaire Tested: DFN2DIP-PN2F0-040D030US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913805
REPORT IS A COMBINATION OF REPORTS P900995 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D030US927-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5489.8 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913805
CATALOG NUMBER: DFN2DIP-PN2F0-040D030US927-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P913805
 CATALOG NUMBER: DFN2DIP-PN2F0-040D030US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53	48
2	91	83	77	72	84	77	72	67	67	63	59	58	55	52	49	47	45	40
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	57	50	70	61	53	48	53	47	43	45	41	38	39	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29	26
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	24	45	34	27	22	30	24	20	26	22	18	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2671	2671	2671
5°	2671	2627	2647
10°	2644	2586	2607
15°	2601	2538	2547
20°	2544	2473	2486
25°	2488	2397	2416
30°	2418	2325	2328
35°	2351	2242	2235
40°	2270	2157	2147
45°	2189	2073	2055
50°	2100	1983	1950
55°	2006	1880	1853
60°	1900	1759	1741
65°	1783	1631	1610
70°	1635	1477	1467
75°	1433	1291	1330
80°	1185	1054	1079
85°	805	667	676

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2189 cd/sqm



TEST NUMBER: P913805

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	2.1
10°-20°	326.5	5.9
20°-30°	479.8	8.7
30°-40°	557.3	10.2
40°-50°	556.6	10.1
50°-60°	485.3	8.8
60°-70°	358.8	6.5
70°-80°	203.0	3.7
80°-90°	55.0	1.0
90°-100°	26.5	0.5
100°-110°	98.6	1.8
110°-120°	261.5	4.8
120°-130°	433.7	7.9
130°-140°	460.7	8.4
140°-150°	428.1	7.8
150°-160°	344.2	6.3
160°-170°	221.8	4.0
170°-180°	76.3	1.4
0°-30°	922.4	16.8
0°-40°	1479.7	27.0
0°-60°	2521.7	45.9
0°-90°	3138.4	57.2
90°-120°	386.5	7.0
90°-150°	1709.0	31.1
90°-180°	2351.0	42.8
0°-180°	5489.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	1	7	12	15	16	5
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	



TEST NUMBER: P913805

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9



TEST NUMBER: P913805

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1



TEST NUMBER: P913805
 CATALOG NUMBER: DFN2DIP-PN2F0-040D030US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.20	12.13	12.10	13.05	14.21	10.77	11.70	11.66	12.61	13.78
	3H	12.85	13.68	13.76	14.61	15.80	12.37	13.20	13.28	14.13	15.32
	4H	13.43	14.22	14.35	15.14	16.34	12.95	13.73	13.87	14.66	15.86
	6H	13.82	14.54	14.75	15.48	16.69	13.33	14.06	14.26	14.99	16.20
	8H	13.91	14.61	14.85	15.56	16.77	13.43	14.12	14.37	15.07	16.28
	12H	13.96	14.62	14.90	15.56	16.80	13.46	14.12	14.41	15.07	16.31
4H	2H	11.66	12.45	12.59	13.38	14.58	11.31	12.10	12.24	13.03	14.23
	3H	13.51	14.17	14.45	15.13	16.34	13.11	13.77	14.05	14.73	15.94
	4H	14.21	14.82	15.16	15.77	17.01	13.80	14.40	14.75	15.35	16.59
	6H	14.71	15.23	15.67	16.21	17.45	14.29	14.81	15.25	15.79	17.03
	8H	14.85	15.34	15.82	16.31	17.56	14.43	14.92	15.39	15.89	17.14
	12H	14.92	15.36	15.90	16.35	17.60	14.49	14.93	15.47	15.91	17.17
8H	4H	14.41	14.89	15.37	15.86	17.11	14.04	14.52	15.00	15.49	16.74
	6H	15.01	15.42	16.00	16.43	17.68	14.64	15.04	15.63	16.05	17.31
	8H	15.22	15.58	16.22	16.58	17.85	14.84	15.20	15.84	16.20	17.47
	12H	15.34	15.65	16.34	16.65	17.97	14.95	15.26	15.95	16.25	17.57
12H	4H	14.39	14.83	15.37	15.82	17.07	14.03	14.47	15.01	15.46	16.71
	6H	15.04	15.39	16.04	16.40	17.66	14.68	15.03	15.67	16.03	17.30
	8H	15.27	15.58	16.27	16.58	17.89	14.90	15.21	15.90	16.21	17.52