

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914018

Luminaire Tested: DFN2DIP-PN3F0-080D070US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914018
REPORT IS A COMBINATION OF REPORTS P899578 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D070US927-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10294.4 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 134.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914018
CATALOG NUMBER: DFN2DIP-PN3F0-080D070US927-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P914018
 CATALOG NUMBER: DFN2DIP-PN3F0-080D070US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	52	51	50	45
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43	47	45	43	39
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	42	39	37	33
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	38	35	33	29
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29	34	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23	29	25	23	20
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21	26	23	21	18
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	24	21	19	24	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	20	17	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3062	3062	3062
5°	3065	3011	3031
10°	3033	2950	2931
15°	2989	2850	2778
20°	2932	2714	2590
25°	2874	2561	2408
30°	2796	2405	2178
35°	2719	2238	1976
40°	2642	2064	1745
45°	2551	1872	1535
50°	2458	1679	1330
55°	2360	1472	1134
60°	2247	1256	932
65°	2116	1037	837
70°	1958	833	756
75°	1759	729	685
80°	1471	605	589
85°	1000	394	435

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2551 cd/sqm



TEST NUMBER: P914018

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.5	2.4
10°-20°	673.9	6.5
20°-30°	946.1	9.2
30°-40°	1031.3	10.0
40°-50°	947.9	9.2
50°-60°	744.4	7.2
60°-70°	484.5	4.7
70°-80°	249.4	2.4
80°-90°	68.6	0.7
90°-100°	108.5	1.1
100°-110°	344.8	3.3
110°-120°	590.1	5.7
120°-130°	776.1	7.5
130°-140°	871.1	8.5
140°-150°	854.2	8.3
150°-160°	716.6	7.0
160°-170°	475.2	4.6
170°-180°	166.1	1.6
0°-30°	1865.5	18.1
0°-40°	2896.8	28.1
0°-60°	4589.2	44.6
0°-90°	5391.8	52.4
90°-120°	1043.4	10.1
90°-150°	3544.8	34.4
90°-180°	4903.0	47.6
0°-180°	10294.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2619	2619	2619	2619	2619	
5°	2619	2608	2576	2598	2591	248
15°	2491	2465	2385	2340	2316	702
25°	2261	2186	2029	1932	1896	1040
35°	1948	1828	1619	1470	1417	1220
45°	1593	1434	1185	1017	960	1230
55°	1211	1026	770	628	583	1082
65°	818	626	412	332	325	811
75°	436	270	190	173	171	461
85°	102	52	45	45	45	117
90°	2	19	52	49	50	10
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1372	1373	1367	845
155°	1546	1551	1556	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P914018

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2619.3	2619.3	2619.3	2619.3	2619.3
2.5°	2631.1	2619.3	2593.1	2617.0	2612.2
5°	2619.3	2607.5	2576.5	2597.9	2590.8
7.5°	2597.9	2583.8	2550.6	2559.9	2548.1
10°	2569.4	2552.9	2505.6	2498.3	2484.2
12.5°	2534.0	2512.6	2448.5	2434.4	2408.2
15°	2491.3	2465.1	2384.6	2339.6	2315.9
17.5°	2441.4	2403.5	2303.9	2251.9	2213.8
20°	2384.6	2337.1	2218.7	2159.6	2107.2
22.5°	2323.0	2268.4	2130.9	2050.4	2014.9
25°	2261.4	2185.5	2029.0	1932.0	1896.2
27.5°	2187.9	2107.2	1934.2	1822.8	1768.2
30°	2109.7	2019.4	1829.9	1709.1	1645.0
32.5°	2033.8	1924.7	1730.5	1588.2	1528.8
35°	1948.5	1827.6	1619.1	1469.7	1417.4
37.5°	1865.5	1735.0	1514.7	1351.0	1291.9
40°	1777.8	1635.7	1405.6	1237.3	1175.7
42.5°	1687.7	1536.1	1296.6	1121.2	1062.0
45°	1592.9	1434.0	1185.3	1016.8	960.0
47.5°	1502.9	1334.7	1078.6	910.1	858.1
50°	1403.3	1235.1	974.3	810.6	761.0
52.5°	1306.0	1128.1	874.6	718.3	673.3
55°	1211.2	1026.3	770.3	628.2	583.2
57.5°	1114.1	924.5	678.0	545.3	507.2
60°	1014.5	824.9	580.7	459.9	422.0
62.5°	917.4	727.8	497.7	384.0	365.2
65°	817.8	625.7	412.4	332.0	324.6
67.5°	723.0	530.9	332.0	291.4	284.5
70°	623.4	438.6	274.9	251.2	241.7
72.5°	528.6	353.1	229.9	211.0	206.2
75°	436.1	270.1	189.6	173.0	170.8
77.5°	343.8	191.9	149.4	139.8	135.1
80°	258.3	137.6	113.7	104.3	104.3
82.5°	180.1	92.5	78.2	73.4	73.4
85°	101.9	52.0	45.0	45.0	45.0
87.5°	37.9	18.9	18.9	16.6	16.6
90°	1.6	19.0	51.8	48.6	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.7	94.7	92.0
97.5°	128.5	142.2	148.1	148.1	148.1
100°	187.7	199.9	204.1	204.1	202.5
102.5°	250.1	259.0	264.9	266.5	264.9
105°	318.3	322.5	325.7	328.4	328.4
107.5°	386.0	392.3	392.3	393.4	386.0
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P914018

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.4	531.4	529.8	525.5	522.4
115°	592.2	600.6	598.0	596.4	592.2
117.5°	661.4	673.0	665.7	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.1	797.8	794.6
125°	861.3	874.5	870.3	865.5	864.0
127.5°	926.3	942.7	936.9	930.6	926.3
130°	987.1	1006.1	1003.5	1000.4	994.5
132.5°	1055.3	1070.2	1071.2	1063.8	1059.5
135°	1114.0	1130.4	1133.6	1131.9	1127.7
137.5°	1179.6	1192.8	1195.4	1194.4	1188.0
140°	1237.2	1250.5	1257.8	1257.8	1252.0
142.5°	1296.4	1309.6	1313.8	1315.4	1309.6
145°	1352.5	1363.0	1371.5	1373.1	1367.3
147.5°	1402.7	1415.9	1422.3	1424.9	1419.1
150°	1454.5	1463.5	1469.3	1474.1	1469.3
152.5°	1500.5	1509.5	1516.9	1522.7	1516.9
155°	1546.5	1550.7	1555.5	1562.9	1558.1
157.5°	1586.2	1589.4	1592.0	1602.6	1595.1
160°	1621.6	1624.8	1626.3	1635.3	1629.0
162.5°	1654.4	1654.4	1656.0	1666.0	1658.6
165°	1682.4	1680.8	1680.8	1691.4	1683.9
167.5°	1707.8	1703.0	1703.0	1713.6	1706.2
170°	1726.8	1722.6	1721.0	1731.5	1722.6
172.5°	1740.0	1735.7	1734.2	1744.8	1735.7
175°	1750.6	1746.4	1743.2	1753.7	1744.8
177.5°	1756.4	1752.1	1749.0	1758.0	1749.0
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P914018
 CATALOG NUMBER: DFN2DIP-PN3F0-080D070US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.21	12.06	12.16	13.02	14.26	7.18	8.03	8.12	8.99	10.23
	3H	12.89	13.65	13.84	14.61	15.87	8.36	9.12	9.32	10.09	11.35
	4H	13.49	14.21	14.46	15.18	16.45	8.81	9.53	9.78	10.50	11.77
	6H	13.91	14.57	14.89	15.55	16.83	9.13	9.79	10.11	10.76	12.05
	8H	14.03	14.66	15.02	15.65	16.94	9.22	9.85	10.20	10.84	12.12
	12H	14.09	14.69	15.09	15.68	16.98	9.26	9.86	10.25	10.84	12.15
4H	2H	11.23	11.95	12.21	12.92	14.19	7.78	8.49	8.75	9.46	10.73
	3H	13.06	13.65	14.04	14.65	15.94	9.12	9.72	10.10	10.72	12.00
	4H	13.75	14.29	14.74	15.28	16.59	9.66	10.21	10.66	11.20	12.51
	6H	14.26	14.72	15.26	15.74	17.05	10.08	10.55	11.08	11.56	12.87
	8H	14.43	14.87	15.43	15.87	17.20	10.20	10.64	11.21	11.65	12.97
	12H	14.52	14.92	15.54	15.94	17.27	10.27	10.66	11.29	11.68	13.01
8H	4H	13.71	14.15	14.72	15.16	16.48	9.94	10.38	10.95	11.39	12.71
	6H	14.27	14.63	15.30	15.68	17.00	10.45	10.81	11.48	11.86	13.18
	8H	14.49	14.80	15.52	15.84	17.18	10.64	10.96	11.68	11.99	13.33
	12H	14.62	14.90	15.66	15.93	17.31	10.75	11.03	11.79	12.06	13.45
12H	4H	13.67	14.06	14.69	15.08	16.41	9.95	10.34	10.97	11.37	12.69
	6H	14.25	14.57	15.29	15.60	16.94	10.50	10.82	11.54	11.85	13.19
	8H	14.47	14.75	15.51	15.78	17.16	10.71	10.99	11.75	12.02	13.40