

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916510

Luminaire Tested: DFN2DIP-PN2F0-030D020US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916510
REPORT IS A COMBINATION OF REPORTS P899464 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D020US930-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3522.1 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 43.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916510

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916510

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2189	2189	2189
5°	2189	2150	2165
10°	2164	2103	2092
15°	2131	2029	1980
20°	2088	1929	1844
25°	2044	1818	1712
30°	1986	1704	1547
35°	1929	1582	1401
40°	1871	1456	1235
45°	1804	1318	1085
50°	1734	1178	938
55°	1661	1029	798
60°	1576	875	654
65°	1479	718	584
70°	1360	572	525
75°	1211	495	471
80°	996	403	399
85°	651	251	283

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1804 cd/sqm

TEST NUMBER: P916510

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	2.7
10°-20°	260.1	7.4
20°-30°	365.1	10.4
30°-40°	398.0	11.3
40°-50°	365.8	10.4
50°-60°	287.3	8.2
60°-70°	187.0	5.3
70°-80°	96.3	2.7
80°-90°	26.1	0.7
90°-100°	31.9	0.9
100°-110°	101.4	2.9
110°-120°	173.5	4.9
120°-130°	228.2	6.5
130°-140°	256.1	7.3
140°-150°	251.2	7.1
150°-160°	210.7	6.0
160°-170°	139.7	4.0
170°-180°	48.8	1.4
0°-30°	720.0	20.4
0°-40°	1118.0	31.7
0°-60°	1771.2	50.3
0°-90°	2080.5	59.1
90°-120°	306.8	8.7
90°-150°	1042.3	29.6
90°-180°	1442.0	40.9
0°-180°	3522.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1006	994	1003	1000	96
15°	962	951	920	903	894	271
25°	873	843	783	746	732	401
35°	752	705	625	567	547	471
45°	615	553	458	392	370	475
55°	467	396	297	242	225	418
65°	316	242	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	45
90°	0	6	15	14	15	3
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	

TEST NUMBER: P916510

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1015.5	1010.9	1000.8	1010.0	1008.2
5°	1010.9	1006.3	994.4	1002.7	999.9
7.5°	1002.7	997.2	984.4	988.0	983.4
10°	991.6	985.3	967.0	964.2	958.8
12.5°	978.0	969.7	945.0	939.5	929.4
15°	961.5	951.4	920.3	902.9	893.8
17.5°	942.2	927.6	889.2	869.1	854.4
20°	920.3	902.0	856.2	833.5	813.3
22.5°	896.6	875.5	822.4	791.3	777.6
25°	872.8	843.4	783.1	745.6	731.8
27.5°	844.4	813.3	746.5	703.5	682.4
30°	814.2	779.4	706.2	659.7	634.9
32.5°	784.9	742.8	667.9	612.9	590.0
35°	752.0	705.3	624.8	567.2	547.1
37.5°	720.0	669.6	584.6	521.4	498.6
40°	686.2	631.3	542.5	477.5	453.8
42.5°	651.3	592.9	500.4	432.7	409.9
45°	614.8	553.4	457.5	392.4	370.5
47.5°	580.0	515.1	416.3	351.2	331.2
50°	541.6	476.6	376.0	312.8	293.7
52.5°	504.0	435.5	337.6	277.2	259.8
55°	467.4	396.1	297.3	242.5	225.1
57.5°	430.0	356.8	261.7	210.4	195.8
60°	391.5	318.4	224.1	177.5	162.9
62.5°	354.1	280.9	192.1	148.2	141.0
65°	315.6	241.5	159.1	128.1	125.3
67.5°	279.1	204.9	128.1	112.5	109.7
70°	240.6	169.3	106.1	96.9	93.3
72.5°	204.0	136.2	88.7	81.4	79.6
75°	168.3	104.3	73.2	66.8	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.9	40.3	40.3
82.5°	69.5	35.7	30.2	28.4	28.4
85°	39.3	20.1	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0



TEST NUMBER: P916510

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7

TEST NUMBER: P916510

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.56	11.47	11.44	12.37	13.51	6.53	7.44	7.41	8.33	9.47
	3H	12.22	13.04	13.12	13.94	15.11	7.70	8.52	8.60	9.43	10.59
	4H	12.82	13.59	13.73	14.50	15.68	8.15	8.91	9.06	9.83	11.00
	6H	13.23	13.94	14.15	14.86	16.04	8.46	9.16	9.38	10.08	11.27
	8H	13.35	14.02	14.28	14.96	16.14	8.54	9.21	9.47	10.15	11.34
	12H	13.41	14.05	14.34	14.98	16.19	8.58	9.22	9.51	10.15	11.36
4H	2H	10.58	11.35	11.50	12.26	13.44	7.12	7.89	8.04	8.80	9.98
	3H	12.40	13.03	13.32	13.98	15.17	8.46	9.10	9.38	10.04	11.23
	4H	13.08	13.66	14.01	14.60	15.81	8.99	9.58	9.93	10.52	11.73
	6H	13.57	14.08	14.52	15.04	16.25	9.40	9.90	10.35	10.86	12.08
	8H	13.74	14.21	14.69	15.16	16.39	9.52	9.99	10.47	10.95	12.17
	12H	13.83	14.25	14.80	15.22	16.46	9.58	10.00	10.55	10.98	12.21
8H	4H	13.04	13.51	14.00	14.47	15.70	9.27	9.74	10.22	10.69	11.92
	6H	13.59	13.98	14.57	14.98	16.20	9.77	10.15	10.74	11.15	12.38
	8H	13.79	14.14	14.78	15.12	16.37	9.95	10.29	10.93	11.27	12.52
	12H	13.92	14.22	14.91	15.20	16.50	10.06	10.36	11.04	11.34	12.63
12H	4H	13.00	13.42	13.97	14.39	15.63	9.27	9.69	10.24	10.67	11.90
	6H	13.56	13.91	14.55	14.89	16.14	9.81	10.15	10.80	11.14	12.39
	8H	13.77	14.07	14.76	15.06	16.35	10.01	10.31	11.00	11.29	12.58