

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916527

Luminaire Tested: DFN2DIP-PN2F0-030D060US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916527
REPORT IS A COMBINATION OF REPORTS P901024 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D060US930-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6921.9 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 80.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916527

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916527

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2189	2189	2189
5°	2189	2150	2165
10°	2164	2103	2092
15°	2131	2029	1980
20°	2088	1929	1844
25°	2044	1818	1712
30°	1986	1704	1547
35°	1929	1582	1401
40°	1871	1456	1235
45°	1804	1318	1085
50°	1734	1178	938
55°	1661	1029	798
60°	1576	875	654
65°	1479	718	584
70°	1360	572	525
75°	1211	495	471
80°	996	403	399
85°	651	251	283

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1804 cd/sqm

TEST NUMBER: P916527

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	1.4
10°-20°	260.1	3.8
20°-30°	365.1	5.3
30°-40°	398.0	5.8
40°-50°	365.8	5.3
50°-60°	287.3	4.2
60°-70°	187.0	2.7
70°-80°	96.3	1.4
80°-90°	27.5	0.4
90°-100°	54.4	0.8
100°-110°	202.9	2.9
110°-120°	538.2	7.8
120°-130°	892.7	12.9
130°-140°	948.2	13.7
140°-150°	881.3	12.7
150°-160°	708.5	10.2
160°-170°	456.5	6.6
170°-180°	157.1	2.3
0°-30°	720.0	10.4
0°-40°	1118.0	16.2
0°-60°	1771.2	25.6
0°-90°	2081.9	30.1
90°-120°	795.6	11.5
90°-150°	3517.8	50.8
90°-180°	4840.0	69.9
0°-180°	6921.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1006	994	1003	1000	96
15°	962	951	920	903	894	271
25°	873	843	783	746	732	401
35°	752	705	625	567	547	471
45°	615	553	458	392	370	475
55°	467	396	297	242	225	418
65°	316	242	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	45
90°	1	14	24	30	32	6
95°	78	38	47	53	51	92
105°	363	399	73	86	91	388
115°	687	707	737	184	98	676
125°	971	987	1009	1018	1021	866
135°	1202	1221	1232	1244	1241	928
145°	1394	1393	1413	1422	1416	872
155°	1535	1524	1539	1546	1536	707
165°	1618	1610	1614	1622	1614	457
175°	1654	1646	1648	1657	1645	157
180°	1651	1651	1651	1651	1651	

TEST NUMBER: P916527

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1015.5	1010.9	1000.8	1010.0	1008.2
5°	1010.9	1006.3	994.4	1002.7	999.9
7.5°	1002.7	997.2	984.4	988.0	983.4
10°	991.6	985.3	967.0	964.2	958.8
12.5°	978.0	969.7	945.0	939.5	929.4
15°	961.5	951.4	920.3	902.9	893.8
17.5°	942.2	927.6	889.2	869.1	854.4
20°	920.3	902.0	856.2	833.5	813.3
22.5°	896.6	875.5	822.4	791.3	777.6
25°	872.8	843.4	783.1	745.6	731.8
27.5°	844.4	813.3	746.5	703.5	682.4
30°	814.2	779.4	706.2	659.7	634.9
32.5°	784.9	742.8	667.9	612.9	590.0
35°	752.0	705.3	624.8	567.2	547.1
37.5°	720.0	669.6	584.6	521.4	498.6
40°	686.2	631.3	542.5	477.5	453.8
42.5°	651.3	592.9	500.4	432.7	409.9
45°	614.8	553.4	457.5	392.4	370.5
47.5°	580.0	515.1	416.3	351.2	331.2
50°	541.6	476.6	376.0	312.8	293.7
52.5°	504.0	435.5	337.6	277.2	259.8
55°	467.4	396.1	297.3	242.5	225.1
57.5°	430.0	356.8	261.7	210.4	195.8
60°	391.5	318.4	224.1	177.5	162.9
62.5°	354.1	280.9	192.1	148.2	141.0
65°	315.6	241.5	159.1	128.1	125.3
67.5°	279.1	204.9	128.1	112.5	109.7
70°	240.6	169.3	106.1	96.9	93.3
72.5°	204.0	136.2	88.7	81.4	79.6
75°	168.3	104.3	73.2	66.8	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.9	40.3	40.3
82.5°	69.5	35.7	30.2	28.4	28.4
85°	39.3	20.1	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	1.1	14.3	23.8	29.9	32.2
92.5°	29.9	25.1	28.6	31.1	32.2
95°	77.6	38.2	46.6	52.7	51.4
97.5°	139.7	41.8	60.8	64.6	65.7
100°	211.5	47.8	68.1	77.6	80.0
102.5°	290.2	288.0	70.5	83.6	87.2
105°	363.1	399.0	72.9	85.9	90.8
107.5°	448.0	477.8	75.3	88.4	93.2
110°	529.3	554.2	209.1	89.7	94.3

TEST NUMBER: P916527

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	605.7	627.1	606.8	91.9	95.6
115°	686.9	707.2	737.1	184.0	98.0
117.5°	757.3	781.2	801.6	630.7	317.7
120°	836.3	854.1	875.7	890.0	728.7
122.5°	903.0	922.2	946.2	953.2	954.6
125°	971.2	986.8	1009.4	1017.8	1021.3
127.5°	1033.3	1050.0	1068.0	1079.9	1081.1
130°	1091.8	1111.0	1124.1	1137.3	1136.1
132.5°	1151.6	1167.2	1180.2	1191.0	1189.8
135°	1201.8	1221.0	1231.6	1243.7	1241.2
137.5°	1254.3	1268.6	1280.7	1292.6	1289.1
140°	1305.6	1315.3	1328.4	1339.1	1333.2
142.5°	1348.7	1357.1	1372.6	1382.1	1376.1
145°	1394.2	1392.9	1413.2	1421.6	1415.6
147.5°	1433.5	1429.9	1450.2	1456.1	1451.5
150°	1471.8	1463.4	1482.5	1489.6	1483.7
152.5°	1504.0	1494.4	1512.3	1519.6	1511.2
155°	1535.0	1524.4	1538.7	1545.8	1536.3
157.5°	1560.2	1550.6	1561.4	1569.8	1560.2
160°	1581.7	1574.4	1581.7	1588.8	1580.5
162.5°	1600.7	1593.6	1599.5	1607.9	1597.2
165°	1617.5	1610.4	1613.9	1622.3	1613.9
167.5°	1630.6	1623.4	1627.1	1635.5	1624.6
170°	1641.4	1634.2	1636.6	1644.9	1634.2
172.5°	1648.5	1641.4	1643.8	1652.2	1641.4
175°	1654.5	1646.1	1648.5	1656.8	1644.9
177.5°	1656.8	1648.5	1649.8	1658.2	1647.4
180°	1650.9	1650.9	1650.9	1650.9	1650.9

TEST NUMBER: P916527

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.53	8.22	8.65	9.33	10.86	3.50	4.19	4.62	5.30	6.83
	3H	9.18	9.80	10.30	10.91	12.46	4.66	5.28	5.78	6.39	7.94
	4H	9.77	10.35	10.90	11.47	13.02	5.09	5.68	6.23	6.79	8.35
	6H	10.16	10.70	11.31	11.82	13.39	5.39	5.93	6.53	7.05	8.61
	8H	10.28	10.79	11.42	11.92	13.48	5.47	5.98	6.62	7.12	8.67
	12H	10.33	10.81	11.48	11.94	13.52	5.50	5.99	6.65	7.12	8.70
4H	2H	7.53	8.11	8.67	9.23	10.78	4.07	4.65	5.21	5.77	7.32
	3H	9.32	9.81	10.47	10.95	12.52	5.38	5.87	6.53	7.01	8.58
	4H	9.99	10.44	11.14	11.57	13.16	5.91	6.36	7.06	7.49	9.08
	6H	10.48	10.86	11.64	12.02	13.59	6.31	6.69	7.46	7.84	9.42
	8H	10.64	11.00	11.80	12.14	13.74	6.42	6.78	7.58	7.93	9.52
	12H	10.72	11.04	11.89	12.20	13.80	6.47	6.80	7.64	7.95	9.55
8H	4H	9.95	10.30	11.10	11.45	13.04	6.17	6.53	7.32	7.67	9.27
	6H	10.48	10.78	11.66	11.97	13.56	6.66	6.95	7.83	8.14	9.73
	8H	10.69	10.94	11.87	12.11	13.72	6.84	7.09	8.02	8.26	9.87
	12H	10.80	11.03	11.99	12.19	13.84	6.94	7.16	8.12	8.33	9.97
12H	4H	9.89	10.21	11.06	11.37	12.97	6.16	6.49	7.33	7.65	9.24
	6H	10.46	10.71	11.64	11.88	13.49	6.70	6.96	7.88	8.13	9.74
	8H	10.66	10.88	11.84	12.05	13.69	6.89	7.12	8.08	8.28	9.93

END OF REPORT