

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916534

Luminaire Tested: DFN2DIP-PN2F0-040D030US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916534
REPORT IS A COMBINATION OF REPORTS P899476 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D030US930-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4936.6 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916534

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916534

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2919	2919	2919
5°	2919	2867	2887
10°	2886	2804	2789
15°	2841	2705	2640
20°	2784	2572	2458
25°	2725	2423	2283
30°	2648	2272	2062
35°	2572	2109	1868
40°	2495	1942	1647
45°	2406	1757	1447
50°	2313	1570	1251
55°	2215	1372	1063
60°	2102	1166	871
65°	1972	957	779
70°	1814	763	699
75°	1614	660	628
80°	1328	537	531
85°	868	334	378

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2406 cd/sqm

TEST NUMBER: P916534

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.6
10°-20°	346.8	7.0
20°-30°	486.9	9.9
30°-40°	530.7	10.8
40°-50°	487.8	9.9
50°-60°	383.1	7.8
60°-70°	249.3	5.1
70°-80°	128.4	2.6
80°-90°	35.0	0.7
90°-100°	47.9	1.0
100°-110°	152.1	3.1
110°-120°	260.3	5.3
120°-130°	342.3	6.9
130°-140°	384.2	7.8
140°-150°	376.8	7.6
150°-160°	316.1	6.4
160°-170°	209.6	4.2
170°-180°	73.3	1.5
0°-30°	960.0	19.4
0°-40°	1490.7	30.2
0°-60°	2361.5	47.8
0°-90°	2774.2	56.2
90°-120°	460.2	9.3
90°-150°	1563.5	31.7
90°-180°	2162.0	43.8
0°-180°	4936.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	1	8	23	21	22	5
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	

TEST NUMBER: P916534

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1

TEST NUMBER: P916534

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6

TEST NUMBER: P916534

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.31	12.19	12.22	13.12	14.30	7.28	8.16	8.19	9.09	10.27
	3H	12.97	13.76	13.89	14.70	15.90	8.45	9.24	9.38	10.18	11.38
	4H	13.57	14.32	14.51	15.25	16.47	8.90	9.64	9.83	10.58	11.80
	6H	13.98	14.66	14.92	15.61	16.84	9.20	9.89	10.15	10.83	12.06
	8H	14.10	14.75	15.05	15.71	16.94	9.29	9.94	10.24	10.90	12.13
	12H	14.15	14.77	15.11	15.73	16.98	9.33	9.95	10.28	10.90	12.15
4H	2H	11.33	12.08	12.27	13.02	14.23	7.87	8.62	8.81	9.55	10.77
	3H	13.14	13.76	14.09	14.73	15.96	9.20	9.82	10.16	10.79	12.02
	4H	13.82	14.39	14.78	15.35	16.60	9.74	10.31	10.70	11.27	12.52
	6H	14.32	14.81	15.29	15.79	17.05	10.14	10.63	11.12	11.62	12.87
	8H	14.48	14.94	15.46	15.92	17.19	10.26	10.72	11.24	11.70	12.97
	12H	14.57	14.98	15.56	15.98	17.25	10.32	10.73	11.32	11.73	13.00
8H	4H	13.79	14.24	14.76	15.22	16.49	10.01	10.47	10.99	11.45	12.72
	6H	14.33	14.71	15.33	15.73	17.00	10.51	10.88	11.51	11.91	13.17
	8H	14.54	14.87	15.55	15.88	17.16	10.69	11.02	11.70	12.03	13.31
	12H	14.66	14.95	15.68	15.96	17.29	10.79	11.09	11.81	12.09	13.42
12H	4H	13.74	14.15	14.74	15.15	16.42	10.02	10.43	11.01	11.42	12.70
	6H	14.31	14.64	15.32	15.65	16.93	10.55	10.88	11.56	11.89	13.18
	8H	14.52	14.81	15.53	15.81	17.14	10.75	11.04	11.76	12.04	13.38