

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916559

Luminaire Tested: DFN2DIP-PN2F0-050D040US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916559
REPORT IS A COMBINATION OF REPORTS P901008 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-050D040US930-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6693.5 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916559

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916559

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	99	95	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43
3	83	74	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	35	32
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3649	3649	3649
5°	3649	3583	3609
10°	3607	3505	3486
15°	3552	3382	3300
20°	3480	3215	3073
25°	3407	3029	2854
30°	3310	2840	2578
35°	3216	2637	2335
40°	3119	2427	2059
45°	3007	2196	1808
50°	2891	1963	1564
55°	2769	1716	1329
60°	2628	1458	1089
65°	2464	1197	974
70°	2267	953	874
75°	2018	825	784
80°	1661	670	664
85°	1085	416	471

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3007 cd/sqm

TEST NUMBER: P916559

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	2.4
10°-20°	433.5	6.5
20°-30°	608.6	9.1
30°-40°	663.4	9.9
40°-50°	609.7	9.1
50°-60°	478.8	7.2
60°-70°	311.7	4.7
70°-80°	160.4	2.4
80°-90°	42.9	0.6
90°-100°	36.3	0.5
100°-110°	135.3	2.0
110°-120°	358.8	5.4
120°-130°	595.1	8.9
130°-140°	632.1	9.4
140°-150°	587.5	8.8
150°-160°	472.3	7.1
160°-170°	304.4	4.5
170°-180°	104.8	1.6
0°-30°	1200.0	17.9
0°-40°	1863.4	27.8
0°-60°	2951.9	44.1
0°-90°	3466.9	51.8
90°-120°	530.4	7.9
90°-150°	2345.2	35.0
90°-180°	3227.0	48.2
0°-180°	6693.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1685	1677	1657	1671	1667	160
15°	1602	1586	1534	1505	1490	452
25°	1455	1406	1305	1243	1220	669
35°	1253	1176	1042	945	912	784
45°	1025	922	762	654	617	791
55°	779	660	496	404	375	696
65°	526	402	265	214	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	1	10	16	20	21	6
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	

TEST NUMBER: P916559

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.8	1684.8	1684.8	1684.8	1684.8
2.5°	1692.4	1684.8	1668.0	1683.3	1680.2
5°	1684.8	1677.2	1657.3	1671.0	1666.6
7.5°	1671.0	1662.0	1640.6	1646.7	1639.0
10°	1652.8	1642.1	1611.7	1607.0	1597.9
12.5°	1629.9	1616.2	1575.0	1565.9	1549.1
15°	1602.5	1585.7	1533.9	1505.0	1489.7
17.5°	1570.4	1546.1	1482.0	1448.5	1424.0
20°	1533.9	1503.3	1427.1	1389.1	1355.4
22.5°	1494.3	1459.1	1370.7	1318.9	1296.1
25°	1454.6	1405.7	1305.1	1242.7	1219.7
27.5°	1407.4	1355.4	1244.1	1172.5	1137.4
30°	1357.1	1299.0	1177.0	1099.3	1058.1
32.5°	1308.2	1238.0	1113.1	1021.6	983.4
35°	1253.4	1175.6	1041.5	945.3	911.7
37.5°	1200.0	1116.1	974.4	869.0	831.0
40°	1143.5	1052.1	904.1	795.9	756.3
42.5°	1085.7	988.1	834.1	721.1	683.1
45°	1024.7	922.4	762.4	654.0	617.4
47.5°	966.7	858.5	693.8	585.5	552.0
50°	902.7	794.4	626.7	521.4	489.5
52.5°	840.1	725.7	562.6	462.0	433.1
55°	779.1	660.1	495.5	404.1	375.1
57.5°	716.6	594.7	436.1	350.7	326.3
60°	652.6	530.6	373.5	295.9	271.4
62.5°	590.1	468.1	320.2	247.0	234.9
65°	526.0	402.5	265.3	213.5	208.9
67.5°	465.0	341.5	213.5	187.5	183.0
70°	401.0	282.1	176.8	161.6	155.5
72.5°	340.1	227.1	147.9	135.7	132.6
75°	280.5	173.7	122.0	111.3	109.8
77.5°	221.1	123.4	96.1	89.9	86.8
80°	166.2	88.5	73.1	67.1	67.1
82.5°	115.9	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.5	12.1	12.1	10.7	10.7
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9



TEST NUMBER: P916559

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P916559

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.69	12.54	12.64	13.50	14.75	7.66	8.51	8.61	9.47	10.72
	3H	13.35	14.11	14.31	15.08	16.35	8.84	9.59	9.80	10.56	11.83
	4H	13.95	14.66	14.92	15.64	16.92	9.27	9.99	10.25	10.96	12.24
	6H	14.35	15.01	15.34	15.99	17.28	9.58	10.24	10.57	11.22	12.51
	8H	14.47	15.10	15.46	16.09	17.38	9.66	10.29	10.65	11.28	12.57
	12H	14.53	15.12	15.52	16.11	17.42	9.70	10.29	10.70	11.28	12.60
4H	2H	11.71	12.42	12.69	13.40	14.68	8.25	8.96	9.23	9.94	11.22
	3H	13.52	14.11	14.51	15.11	16.41	9.58	10.17	10.57	11.18	12.47
	4H	14.19	14.74	15.19	15.73	17.05	10.11	10.66	11.11	11.65	12.97
	6H	14.69	15.16	15.70	16.18	17.49	10.52	10.98	11.52	12.00	13.32
	8H	14.85	15.29	15.86	16.30	17.63	10.63	11.07	11.64	12.08	13.41
	12H	14.94	15.33	15.97	16.36	17.69	10.69	11.08	11.72	12.11	13.45
8H	4H	14.16	14.59	15.17	15.61	16.94	10.38	10.82	11.39	11.83	13.16
	6H	14.70	15.06	15.74	16.12	17.44	10.88	11.24	11.91	12.29	13.62
	8H	14.91	15.22	15.95	16.26	17.61	11.06	11.37	12.10	12.41	13.76
	12H	15.03	15.31	16.08	16.34	17.73	11.16	11.44	12.21	12.47	13.86
12H	4H	14.11	14.50	15.14	15.53	16.87	10.39	10.78	11.41	11.81	13.14
	6H	14.68	14.99	15.72	16.03	17.38	10.92	11.24	11.96	12.28	13.63
	8H	14.88	15.16	15.93	16.20	17.59	11.12	11.40	12.16	12.43	13.82