

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916571

Luminaire Tested: DFN2DIP-PN2F0-060D020US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916571
REPORT IS A COMBINATION OF REPORTS P900990 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-060D020US930-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5772.3 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 80.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916571

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916571

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	68	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	54	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	50	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	34	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4379	4379	4379
5°	4379	4300	4330
10°	4328	4207	4183
15°	4262	4058	3959
20°	4176	3858	3687
25°	4088	3635	3424
30°	3972	3407	3093
35°	3859	3164	2802
40°	3742	2912	2470
45°	3608	2635	2170
50°	3469	2356	1876
55°	3323	2059	1595
60°	3153	1750	1307
65°	2958	1436	1169
70°	2720	1144	1049
75°	2421	990	941
80°	1992	804	797
85°	1302	500	565

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3608 cd/sqm

TEST NUMBER: P916571

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	3.3
10°-20°	520.2	9.0
20°-30°	730.3	12.7
30°-40°	796.1	13.8
40°-50°	731.7	12.7
50°-60°	574.6	10.0
60°-70°	374.0	6.5
70°-80°	192.5	3.3
80°-90°	50.1	0.9
90°-100°	18.1	0.3
100°-110°	67.6	1.2
110°-120°	179.4	3.1
120°-130°	297.6	5.2
130°-140°	316.1	5.5
140°-150°	293.8	5.1
150°-160°	236.2	4.1
160°-170°	152.2	2.6
170°-180°	52.4	0.9
0°-30°	1439.9	24.9
0°-40°	2236.0	38.7
0°-60°	3542.3	61.4
0°-90°	4159.0	72.1
90°-120°	265.2	4.6
90°-150°	1172.6	20.3
90°-180°	1613.0	27.9
0°-180°	5772.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	0	5	8	10	11	5
95°	26	13	16	18	17	31
105°	121	133	24	29	30	129
115°	229	236	246	61	33	225
125°	324	329	336	339	340	289
135°	401	407	410	415	414	309
145°	465	464	471	474	472	291
155°	512	508	513	515	512	236
165°	539	537	538	541	538	152
175°	552	549	550	552	548	52
180°	550	550	550	550	550	

TEST NUMBER: P916571

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	0.4	4.8	7.9	9.9	10.8
92.5°	9.9	8.4	9.5	10.4	10.8
95°	25.8	12.7	15.5	17.5	17.1
97.5°	46.6	13.9	20.3	21.5	21.9
100°	70.5	15.9	22.7	25.8	26.7
102.5°	96.8	96.0	23.5	27.9	29.1
105°	121.1	133.0	24.3	28.6	30.2
107.5°	149.4	159.2	25.1	29.4	31.1
110°	176.4	184.7	69.7	29.9	31.5

TEST NUMBER: P916571

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.9	209.0	202.3	30.7	31.9
115°	228.9	235.7	245.7	61.3	32.7
117.5°	252.4	260.4	267.2	210.3	105.9
120°	278.8	284.7	291.9	296.7	242.9
122.5°	301.0	307.4	315.4	317.7	318.2
125°	323.8	328.9	336.5	339.2	340.5
127.5°	344.5	350.0	356.0	360.0	360.4
130°	363.9	370.3	374.7	379.1	378.7
132.5°	383.8	389.1	393.4	397.0	396.6
135°	400.6	407.0	410.5	414.6	413.8
137.5°	418.1	422.9	426.9	430.9	429.7
140°	435.2	438.5	442.8	446.4	444.4
142.5°	449.6	452.4	457.5	460.7	458.7
145°	464.7	464.3	471.1	473.9	471.9
147.5°	477.8	476.6	483.4	485.3	483.8
150°	490.6	487.8	494.2	496.5	494.6
152.5°	501.3	498.1	504.1	506.5	503.7
155°	511.7	508.1	512.9	515.3	512.1
157.5°	520.1	516.9	520.5	523.3	520.1
160°	527.3	524.8	527.3	529.6	526.8
162.5°	533.5	531.2	533.2	536.0	532.4
165°	539.2	536.8	537.9	540.8	537.9
167.5°	543.6	541.1	542.3	545.2	541.5
170°	547.1	544.7	545.5	548.3	544.7
172.5°	549.5	547.1	548.0	550.7	547.1
175°	551.5	548.7	549.5	552.3	548.3
177.5°	552.3	549.5	549.9	552.7	549.1
180°	550.3	550.3	550.3	550.3	550.3

TEST NUMBER: P916571

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.01	15.06	14.76	15.83	16.75	9.98	11.03	10.73	11.80	12.72
	3H	15.69	16.63	16.45	17.40	18.35	11.17	12.11	11.93	12.88	13.84
	4H	16.29	17.18	17.07	17.96	18.92	11.62	12.50	12.40	13.29	14.25
	6H	16.71	17.52	17.50	18.32	19.29	11.94	12.75	12.73	13.54	14.52
	8H	16.83	17.61	17.63	18.42	19.40	12.02	12.80	12.83	13.61	14.59
	12H	16.89	17.63	17.70	18.44	19.44	12.07	12.81	12.87	13.61	14.61
4H	2H	14.05	14.94	14.84	15.72	16.68	10.59	11.48	11.38	12.26	13.22
	3H	15.88	16.61	16.67	17.43	18.41	11.94	12.68	12.74	13.50	14.48
	4H	16.56	17.23	17.37	18.05	19.06	12.48	13.15	13.29	13.97	14.98
	6H	17.07	17.65	17.90	18.49	19.50	12.90	13.47	13.72	14.31	15.33
	8H	17.24	17.78	18.07	18.61	19.64	13.02	13.56	13.85	14.40	15.42
	12H	17.33	17.81	18.18	18.67	19.70	13.09	13.57	13.94	14.43	15.46
8H	4H	16.54	17.08	17.37	17.92	18.94	12.77	13.31	13.60	14.14	15.17
	6H	17.09	17.54	17.95	18.42	19.45	13.27	13.71	14.13	14.60	15.62
	8H	17.30	17.69	18.17	18.57	19.61	13.45	13.84	14.32	14.72	15.76
	12H	17.43	17.78	18.30	18.65	19.74	13.56	13.91	14.44	14.78	15.88
12H	4H	16.50	16.99	17.35	17.85	18.88	12.78	13.26	13.63	14.12	15.15
	6H	17.07	17.46	17.94	18.34	19.38	13.32	13.71	14.19	14.59	15.63
	8H	17.28	17.63	18.16	18.50	19.60	13.52	13.87	14.39	14.73	15.83