

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919222

Luminaire Tested: DFN2DIP-PN2F0-020D030US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919222
REPORT IS A COMBINATION OF REPORTS P899472 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D030US935-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3749.6 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 35.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919222
CATALOG NUMBER: DFN2DIP-PN2F0-020D030US935-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P919222

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1541	1541	1541
5°	1541	1514	1524
10°	1524	1481	1473
15°	1500	1428	1394
20°	1470	1358	1298
25°	1439	1280	1205
30°	1398	1200	1089
35°	1358	1114	986
40°	1317	1025	869
45°	1270	928	764
50°	1221	830	661
55°	1170	725	561
60°	1110	616	460
65°	1041	506	412
70°	958	402	369
75°	852	348	331
80°	702	283	280
85°	457	176	199

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1270 cd/sqm



TEST NUMBER: P919222

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.8
10°-20°	183.1	4.9
20°-30°	257.1	6.9
30°-40°	280.2	7.5
40°-50°	257.6	6.9
50°-60°	202.3	5.4
60°-70°	131.7	3.5
70°-80°	67.8	1.8
80°-90°	19.6	0.5
90°-100°	50.6	1.3
100°-110°	160.6	4.3
110°-120°	274.9	7.3
120°-130°	361.5	9.6
130°-140°	405.7	10.8
140°-150°	397.9	10.6
150°-160°	333.8	8.9
160°-170°	221.3	5.9
170°-180°	77.4	2.1
0°-30°	506.9	13.5
0°-40°	787.1	21.0
0°-60°	1247.0	33.3
0°-90°	1466.0	39.1
90°-120°	486.0	13.0
90°-150°	1651.1	44.0
90°-180°	2284.0	60.9
0°-180°	3749.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	1	9	24	23	23	4
95°	36	43	44	44	43	40
105°	148	150	152	153	153	156
115°	276	280	278	278	276	273
125°	401	407	405	403	402	358
135°	519	526	528	527	525	401
145°	630	635	639	640	637	394
155°	720	722	724	728	726	332
165°	784	783	783	788	784	221
175°	816	814	812	817	813	77
180°	817	817	817	817	817	



TEST NUMBER: P919222

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	0.8	8.9	24.1	22.6	23.4
92.5°	15.2	20.7	21.4	22.1	22.1
95°	36.0	42.9	44.1	44.1	42.9
97.5°	59.8	66.2	69.0	69.0	69.0
100°	87.4	93.1	95.1	95.1	94.4
102.5°	116.5	120.7	123.4	124.2	123.4
105°	148.3	150.2	151.7	152.9	152.9
107.5°	179.8	182.7	182.7	183.2	179.8
110°	210.3	214.3	214.3	214.3	212.3



TEST NUMBER: P919222

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US935-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.3	247.5	246.8	244.8	243.3
115°	275.9	279.7	278.5	277.8	275.9
117.5°	308.1	313.5	310.0	308.1	306.1
120°	340.6	346.0	340.6	340.6	338.4
122.5°	370.1	377.0	373.6	371.6	370.1
125°	401.2	407.3	405.4	403.1	402.4
127.5°	431.4	439.1	436.4	433.4	431.4
130°	459.8	468.6	467.4	466.0	463.2
132.5°	491.5	498.4	498.9	495.5	493.5
135°	518.9	526.5	528.0	527.3	525.3
137.5°	549.4	555.6	556.8	556.4	553.4
140°	576.3	582.5	585.9	585.9	583.2
142.5°	603.9	610.0	612.0	612.8	610.0
145°	630.0	634.9	638.9	639.5	636.9
147.5°	653.4	659.5	662.5	663.7	661.0
150°	677.5	681.7	684.4	686.6	684.4
152.5°	699.0	703.1	706.5	709.3	706.5
155°	720.4	722.3	724.5	728.0	725.8
157.5°	738.8	740.3	741.6	746.5	743.0
160°	755.4	756.8	757.6	761.7	758.8
162.5°	770.6	770.6	771.4	776.0	772.6
165°	783.7	782.9	782.9	787.8	784.4
167.5°	795.5	793.2	793.2	798.1	794.7
170°	804.3	802.4	801.7	806.6	802.4
172.5°	810.5	808.6	807.8	812.7	808.6
175°	815.5	813.5	812.0	816.9	812.7
177.5°	818.1	816.1	814.7	818.9	814.7
180°	816.9	816.9	816.9	816.9	816.9



TEST NUMBER: P919222
 CATALOG NUMBER: DFN2DIP-PN2F0-020D030US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.42	8.17	8.47	9.22	10.64	3.39	4.14	4.44	5.19	6.61
	3H	9.07	9.74	10.13	10.80	12.24	4.56	5.23	5.62	6.29	7.73
	4H	9.66	10.30	10.73	11.36	12.81	4.99	5.62	6.06	6.69	8.13
	6H	10.06	10.65	11.15	11.71	13.17	5.29	5.87	6.37	6.94	8.40
	8H	10.18	10.73	11.26	11.82	13.27	5.37	5.93	6.46	7.01	8.46
	12H	10.23	10.76	11.32	11.83	13.31	5.41	5.93	6.50	7.01	8.48
4H	2H	7.42	8.06	8.50	9.12	10.57	3.96	4.60	5.04	5.66	7.11
	3H	9.22	9.75	10.31	10.84	12.30	5.29	5.81	6.37	6.90	8.36
	4H	9.90	10.38	10.99	11.46	12.94	5.82	6.30	6.91	7.38	8.86
	6H	10.39	10.80	11.49	11.91	13.38	6.21	6.63	7.31	7.73	9.21
	8H	10.55	10.94	11.65	12.03	13.52	6.33	6.72	7.43	7.81	9.30
	12H	10.63	10.98	11.74	12.09	13.58	6.38	6.73	7.50	7.84	9.34
8H	4H	9.85	10.24	10.95	11.34	12.83	6.08	6.47	7.18	7.56	9.05
	6H	10.39	10.71	11.52	11.85	13.34	6.57	6.89	7.69	8.03	9.51
	8H	10.60	10.88	11.72	12.00	13.50	6.75	7.03	7.88	8.15	9.65
	12H	10.72	10.96	11.85	12.08	13.62	6.85	7.10	7.98	8.21	9.75
12H	4H	9.80	10.15	10.92	11.26	12.75	6.08	6.43	7.19	7.54	9.03
	6H	10.37	10.65	11.50	11.77	13.27	6.61	6.89	7.74	8.01	9.52
	8H	10.57	10.82	11.70	11.93	13.48	6.81	7.05	7.94	8.17	9.71