

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919230

Luminaire Tested: DFN2DIP-PN2F0-020D050US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919230
REPORT IS A COMBINATION OF REPORTS P899492 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D050US935-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5273.6 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919230

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919230

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	25	24	23
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	29	26	24	21	19	17
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1541	1541	1541
5°	1541	1514	1524
10°	1524	1481	1473
15°	1500	1428	1394
20°	1470	1358	1298
25°	1439	1280	1205
30°	1398	1200	1089
35°	1358	1114	986
40°	1317	1025	869
45°	1270	928	764
50°	1221	830	661
55°	1170	725	561
60°	1110	616	460
65°	1041	506	412
70°	958	402	369
75°	852	348	331
80°	702	283	280
85°	457	176	199

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1836 cd/sqm

TEST NUMBER: P919230

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.3
10°-20°	183.1	3.5
20°-30°	257.1	4.9
30°-40°	280.2	5.3
40°-50°	257.6	4.9
50°-60°	202.3	3.8
60°-70°	131.7	2.5
70°-80°	67.8	1.3
80°-90°	21.2	0.4
90°-100°	84.2	1.6
100°-110°	267.7	5.1
110°-120°	458.1	8.7
120°-130°	602.5	11.4
130°-140°	676.3	12.8
140°-150°	663.1	12.6
150°-160°	556.3	10.5
160°-170°	368.9	7.0
170°-180°	128.9	2.4
0°-30°	506.9	9.6
0°-40°	787.1	14.9
0°-60°	1247.0	23.6
0°-90°	1467.6	27.8
90°-120°	810.0	15.4
90°-150°	2751.9	52.2
90°-180°	3806.0	72.2
0°-180°	5273.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	1	15	40	38	39	5
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P919230

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8

TEST NUMBER: P919230

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5

TEST NUMBER: P919230

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US935-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.99	6.67	7.12	7.79	9.35	1.96	2.64	3.09	3.76	5.32
	3H	7.64	8.24	8.78	9.37	10.94	3.12	3.73	4.26	4.85	6.43
	4H	8.22	8.80	9.37	9.93	11.51	3.55	4.13	4.70	5.25	6.83
	6H	8.62	9.15	9.78	10.28	11.87	3.85	4.38	5.01	5.51	7.10
	8H	8.73	9.24	9.89	10.38	11.96	3.93	4.43	5.09	5.58	7.16
	12H	8.78	9.26	9.94	10.40	12.00	3.96	4.43	5.12	5.57	7.18
4H	2H	5.99	6.56	7.14	7.69	9.27	2.53	3.10	3.68	4.23	5.81
	3H	7.78	8.26	8.94	9.41	11.00	3.84	4.32	5.00	5.47	7.07
	4H	8.45	8.89	9.61	10.03	11.64	4.37	4.81	5.53	5.95	7.56
	6H	8.93	9.31	10.10	10.48	12.08	4.76	5.14	5.93	6.30	7.90
	8H	9.10	9.45	10.26	10.60	12.22	4.88	5.23	6.04	6.39	8.00
	12H	9.17	9.49	10.35	10.66	12.28	4.92	5.24	6.11	6.41	8.03
8H	4H	8.40	8.75	9.57	9.91	11.53	4.62	4.98	5.79	6.13	7.75
	6H	8.94	9.23	10.12	10.43	12.04	5.11	5.40	6.30	6.60	8.22
	8H	9.14	9.39	10.33	10.57	12.20	5.29	5.54	6.48	6.72	8.36
	12H	9.26	9.48	10.45	10.65	12.32	5.39	5.61	6.59	6.79	8.45
12H	4H	8.34	8.66	9.53	9.83	11.45	4.62	4.94	5.80	6.11	7.73
	6H	8.91	9.16	10.10	10.34	11.98	5.16	5.41	6.35	6.59	8.22
	8H	9.11	9.33	10.31	10.51	12.17	5.35	5.57	6.54	6.74	8.41

END OF REPORT