

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919258

Luminaire Tested: DFN2DIP-PN2F0-040D020US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919258
REPORT IS A COMBINATION OF REPORTS P899466 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D020US935-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4451.3 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 55.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919258

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919258

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3083	3083	3083
5°	3083	3027	3049
10°	3048	2961	2945
15°	3000	2857	2788
20°	2940	2716	2596
25°	2878	2559	2411
30°	2797	2399	2178
35°	2717	2228	1973
40°	2635	2051	1739
45°	2540	1855	1528
50°	2442	1658	1321
55°	2339	1449	1123
60°	2220	1232	920
65°	2082	1011	823
70°	1915	806	738
75°	1704	698	663
80°	1402	566	561
85°	918	353	399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2540 cd/sqm

TEST NUMBER: P919258

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	3.0
10°-20°	366.2	8.2
20°-30°	514.2	11.6
30°-40°	560.5	12.6
40°-50°	515.1	11.6
50°-60°	404.5	9.1
60°-70°	263.3	5.9
70°-80°	135.6	3.0
80°-90°	36.1	0.8
90°-100°	33.7	0.8
100°-110°	107.1	2.4
110°-120°	183.2	4.1
120°-130°	241.0	5.4
130°-140°	270.5	6.1
140°-150°	265.3	6.0
150°-160°	222.5	5.0
160°-170°	147.6	3.3
170°-180°	51.6	1.2
0°-30°	1013.8	22.8
0°-40°	1574.2	35.4
0°-60°	2493.9	56.0
0°-90°	2928.9	65.8
90°-120°	324.0	7.3
90°-150°	1100.8	24.7
90°-180°	1522.0	34.2
0°-180°	4451.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1423	1423	1423	1423	1423	
5°	1423	1417	1400	1412	1408	135
15°	1354	1340	1296	1271	1259	382
25°	1229	1188	1103	1050	1030	565
35°	1059	993	880	799	770	663
45°	866	779	644	553	522	668
55°	658	558	419	341	317	588
65°	444	340	224	180	176	441
75°	237	147	103	94	93	251
85°	55	28	24	24	24	64
90°	0	6	16	15	16	4
95°	24	29	29	29	29	27
105°	99	100	101	102	102	104
115°	184	186	186	185	184	182
125°	267	272	270	269	268	239
135°	346	351	352	352	350	267
145°	420	423	426	426	425	262
155°	480	482	483	485	484	221
165°	522	522	522	525	523	147
175°	544	542	541	545	542	52
180°	545	545	545	545	545	

TEST NUMBER: P919258

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.4	1423.4	1423.4	1423.4	1423.4
2.5°	1429.9	1423.4	1409.2	1422.2	1419.5
5°	1423.4	1416.9	1400.2	1411.8	1408.0
7.5°	1411.8	1404.1	1386.1	1391.1	1384.7
10°	1396.4	1387.3	1361.6	1357.6	1350.0
12.5°	1377.1	1365.5	1330.6	1322.9	1308.7
15°	1353.8	1339.6	1295.9	1271.4	1258.6
17.5°	1326.8	1306.1	1252.0	1223.7	1203.1
20°	1295.9	1270.1	1205.7	1173.5	1145.1
22.5°	1262.4	1232.8	1158.0	1114.2	1095.0
25°	1228.9	1187.7	1102.6	1049.9	1030.4
27.5°	1189.0	1145.1	1051.1	990.6	960.9
30°	1146.5	1097.4	994.4	928.8	894.0
32.5°	1105.3	1045.9	940.4	863.1	830.8
35°	1058.9	993.2	879.9	798.7	770.2
37.5°	1013.8	942.9	823.1	734.2	702.1
40°	966.1	888.9	763.9	672.4	638.9
42.5°	917.1	834.7	704.6	609.2	577.1
45°	865.6	779.3	644.1	552.6	521.7
47.5°	816.7	725.3	586.2	494.6	466.3
50°	762.6	671.1	529.4	440.5	413.5
52.5°	709.7	613.1	475.4	390.3	365.8
55°	658.2	557.8	418.6	341.4	316.9
57.5°	605.5	502.4	368.4	296.3	275.7
60°	551.3	448.2	315.6	249.9	229.4
62.5°	498.6	395.5	270.4	208.7	198.5
65°	444.4	340.0	224.1	180.4	176.4
67.5°	393.0	288.5	180.4	158.4	154.5
70°	338.8	238.3	149.4	136.6	131.3
72.5°	287.3	191.9	124.9	114.7	112.1
75°	236.9	146.8	103.1	94.0	92.8
77.5°	186.8	104.3	81.2	76.0	73.4
80°	140.3	74.7	61.7	56.7	56.7
82.5°	97.9	50.3	42.5	39.9	39.9
85°	55.4	28.3	24.5	24.5	24.5
87.5°	20.7	10.2	10.2	9.0	9.0
90°	0.5	5.9	16.1	15.1	15.6
92.5°	10.2	13.8	14.3	14.8	14.8
95°	23.9	28.6	29.4	29.4	28.6
97.5°	39.9	44.2	46.0	46.0	46.0
100°	58.3	62.1	63.4	63.4	62.9
102.5°	77.7	80.4	82.2	82.7	82.2
105°	98.8	100.1	101.2	101.9	101.9
107.5°	119.9	121.8	121.8	122.2	119.9
110°	140.3	142.8	142.8	142.8	141.5

TEST NUMBER: P919258

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	162.2	165.0	164.5	163.2	162.2
115°	183.9	186.5	185.7	185.2	183.9
117.5°	205.4	209.1	206.7	205.4	204.1
120°	227.0	230.7	227.0	227.0	225.6
122.5°	246.8	251.3	249.1	247.8	246.8
125°	267.4	271.6	270.3	268.8	268.3
127.5°	287.7	292.7	290.9	289.0	287.7
130°	306.5	312.5	311.6	310.6	308.8
132.5°	327.7	332.3	332.6	330.4	329.0
135°	345.9	351.0	352.0	351.5	350.2
137.5°	366.3	370.4	371.3	370.9	368.9
140°	384.2	388.3	390.6	390.6	388.8
142.5°	402.6	406.6	408.0	408.5	406.6
145°	420.0	423.3	425.9	426.4	424.6
147.5°	435.6	439.7	441.7	442.5	440.7
150°	451.7	454.4	456.2	457.7	456.2
152.5°	466.0	468.7	471.1	472.9	471.1
155°	480.3	481.6	483.0	485.3	483.9
157.5°	492.6	493.5	494.4	497.7	495.3
160°	503.6	504.5	505.1	507.8	505.8
162.5°	513.8	513.8	514.2	517.4	515.0
165°	522.5	521.9	521.9	525.2	523.0
167.5°	530.3	528.8	528.8	532.1	529.9
170°	536.2	534.9	534.4	537.7	534.9
172.5°	540.4	539.0	538.6	541.8	539.0
175°	543.6	542.3	541.3	544.6	541.8
177.5°	545.4	544.2	543.1	545.9	543.1
180°	544.6	544.6	544.6	544.6	544.6

TEST NUMBER: P919258

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.30	13.28	13.12	14.11	15.14	8.27	9.25	9.09	10.08	11.11
	3H	13.97	14.85	14.80	15.69	16.75	9.45	10.33	10.28	11.17	12.23
	4H	14.57	15.40	15.42	16.25	17.32	9.90	10.72	10.74	11.57	12.64
	6H	14.98	15.74	15.84	16.60	17.68	10.21	10.97	11.07	11.83	12.91
	8H	15.11	15.83	15.97	16.70	17.79	10.30	11.02	11.17	11.90	12.98
	12H	15.16	15.85	16.04	16.72	17.83	10.34	11.03	11.21	11.90	13.00
4H	2H	12.33	13.16	13.18	14.01	15.08	8.87	9.70	9.72	10.55	11.62
	3H	14.15	14.84	15.01	15.72	16.81	10.22	10.90	11.08	11.78	12.87
	4H	14.84	15.46	15.71	16.34	17.45	10.76	11.38	11.63	12.26	13.37
	6H	15.34	15.88	16.23	16.78	17.89	11.16	11.70	12.05	12.61	13.72
	8H	15.51	16.01	16.40	16.91	18.03	11.29	11.79	12.18	12.69	13.81
	12H	15.60	16.05	16.51	16.97	18.10	11.35	11.80	12.26	12.72	13.85
8H	4H	14.81	15.31	15.70	16.21	17.34	11.03	11.54	11.93	12.43	13.56
	6H	15.36	15.77	16.28	16.71	17.84	11.53	11.95	12.45	12.89	14.02
	8H	15.56	15.93	16.49	16.86	18.01	11.71	12.08	12.64	13.01	14.16
	12H	15.69	16.02	16.62	16.94	18.14	11.82	12.15	12.76	13.07	14.27
12H	4H	14.77	15.22	15.68	16.14	17.27	11.04	11.49	11.95	12.41	13.54
	6H	15.33	15.70	16.26	16.63	17.78	11.58	11.95	12.51	12.88	14.02
	8H	15.55	15.87	16.48	16.79	17.99	11.78	12.10	12.71	13.03	14.22

END OF REPORT