

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916676

Luminaire Tested: DFN2DIP-PN3F0-060D040US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916676
REPORT IS A COMBINATION OF REPORTS P899531 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-060D040US930-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7729.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 87
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916676

CATALOG NUMBER: DFN2DIP-PN3F0-060D040US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916676

CATALOG NUMBER: DFN2DIP-PN3F0-060D040US930-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90		79	79	79		68
1	101	96	92	89	94	90	87	84	79	77	74		69	67	66		60
2	92	84	78	72	86	79	73	69	70	65	62		61	58	55		53
3	84	74	66	60	78	70	63	58	61	56	52		54	50	46		47
4	77	66	57	51	71	62	54	49	55	49	44		48	43	40		42
5	70	58	50	44	66	55	48	42	49	43	38		43	38	35		38
6	65	53	44	38	61	50	42	37	44	38	33		39	34	30		34
7	60	48	39	34	56	45	38	32	40	34	30		36	31	27		31
8	56	43	35	30	52	41	34	29	37	31	26		33	28	24		29
9	52	40	32	27	49	38	30	26	34	28	24		30	25	22		27
10	49	36	29	24	46	35	28	23	31	25	21		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2225	2225	2225
5°	2227	2192	2208
10°	2208	2161	2177
15°	2174	2124	2129
20°	2129	2073	2081
25°	2084	2012	2024
30°	2028	1956	1953
35°	1975	1890	1878
40°	1909	1822	1806
45°	1844	1755	1733
50°	1773	1684	1648
55°	1698	1602	1569
60°	1613	1505	1480
65°	1521	1404	1374
70°	1403	1281	1260
75°	1240	1133	1153
80°	1043	945	951
85°	735	625	620

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1844 cd/sqm

TEST NUMBER: P916676

CATALOG NUMBER: DFN2DIP-PN3F0-060D040US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	2.3
10°-20°	504.1	6.5
20°-30°	740.8	9.6
30°-40°	860.4	11.1
40°-50°	859.3	11.1
50°-60°	749.3	9.7
60°-70°	553.9	7.2
70°-80°	313.4	4.1
80°-90°	85.6	1.1
90°-100°	63.8	0.8
100°-110°	202.8	2.6
110°-120°	347.0	4.5
120°-130°	456.4	5.9
130°-140°	512.3	6.6
140°-150°	502.4	6.5
150°-160°	421.4	5.5
160°-170°	279.5	3.6
170°-180°	97.7	1.3
0°-30°	1424.0	18.4
0°-40°	2284.3	29.6
0°-60°	3892.9	50.4
0°-90°	4845.8	62.7
90°-120°	613.6	7.9
90°-150°	2084.7	27.0
90°-180°	2883.0	37.3
0°-180°	7729.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1876	1891	1887	181
15°	1812	1801	1777	1785	1776	510
25°	1640	1625	1594	1598	1594	755
35°	1415	1397	1367	1356	1347	884
45°	1151	1138	1111	1091	1084	889
55°	871	860	838	816	807	779
65°	588	577	558	542	533	581
75°	307	304	295	284	287	328
85°	75	73	71	66	64	84
90°	1	11	30	29	30	7
95°	45	54	56	56	54	51
105°	187	190	192	193	193	198
115°	348	353	352	351	348	344
125°	506	514	512	509	508	453
135°	655	665	667	666	663	506
145°	795	802	807	808	804	497
155°	910	912	915	919	916	419
165°	989	988	988	995	990	279
175°	1030	1027	1025	1031	1026	98
180°	1031	1031	1031	1031	1031	

TEST NUMBER: P916676

CATALOG NUMBER: DFN2DIP-PN3F0-060D040US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1903.4	1903.4	1903.4	1903.4	1903.4
2.5°	1914.5	1905.4	1885.1	1903.4	1899.9
5°	1903.4	1896.2	1876.0	1890.6	1887.1
7.5°	1890.6	1879.8	1859.5	1874.3	1870.6
10°	1870.6	1857.8	1835.8	1850.4	1844.9
12.5°	1843.1	1832.1	1810.2	1819.3	1815.7
15°	1811.9	1801.1	1777.2	1784.6	1775.5
17.5°	1773.5	1762.7	1738.8	1747.8	1738.8
20°	1731.4	1720.5	1694.8	1700.3	1693.1
22.5°	1689.5	1672.9	1649.0	1649.0	1645.4
25°	1639.9	1625.4	1594.2	1597.7	1594.2
27.5°	1584.9	1572.1	1548.4	1543.0	1533.9
30°	1530.2	1515.4	1488.1	1482.6	1475.2
32.5°	1471.5	1460.7	1431.3	1420.2	1412.9
35°	1414.9	1396.6	1367.3	1356.2	1347.0
37.5°	1350.8	1334.2	1305.0	1292.1	1283.0
40°	1284.9	1270.2	1240.9	1224.6	1217.2
42.5°	1220.8	1206.1	1177.0	1158.5	1147.6
45°	1151.4	1138.5	1110.9	1091.0	1083.5
47.5°	1083.5	1070.7	1041.5	1021.2	1010.3
50°	1012.1	1003.0	977.4	951.7	942.6
52.5°	942.6	929.8	906.0	885.9	873.1
55°	871.3	860.2	838.3	816.4	807.2
57.5°	799.9	790.8	766.9	744.9	737.5
60°	728.4	721.2	695.6	675.4	669.9
62.5°	658.8	646.0	627.8	609.5	602.2
65°	587.6	576.6	558.3	541.8	532.6
67.5°	514.4	505.1	488.8	476.0	468.6
70°	446.6	439.3	422.7	409.9	402.8
72.5°	377.1	369.7	360.6	347.8	342.3
75°	307.4	303.9	294.6	283.7	287.4
77.5°	245.2	237.9	234.2	228.8	223.3
80°	183.1	181.2	177.5	172.0	168.4
82.5°	124.5	124.5	122.7	115.4	115.4
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.4	25.6	20.2	18.3
90°	0.9	11.2	30.5	28.6	29.5
92.5°	19.2	26.1	27.1	28.0	28.0
95°	45.4	54.1	55.7	55.7	54.1
97.5°	75.6	83.6	87.1	87.1	87.1
100°	110.4	117.6	120.0	120.0	119.1
102.5°	147.1	152.4	155.8	156.7	155.8
105°	187.2	189.6	191.5	193.1	193.1
107.5°	227.0	230.7	230.7	231.3	227.0
110°	265.5	270.5	270.5	270.5	268.1

TEST NUMBER: P916676

CATALOG NUMBER: DFN2DIP-PN3F0-060D040US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	307.2	312.5	311.5	309.1	307.2
115°	348.2	353.3	351.6	350.7	348.2
117.5°	389.0	395.8	391.5	389.0	386.5
120°	430.1	436.8	430.1	430.1	427.2
122.5°	467.3	476.1	471.7	469.2	467.3
125°	506.5	514.3	511.8	509.0	508.1
127.5°	544.8	554.4	551.0	547.2	544.8
130°	580.5	591.7	590.2	588.3	584.9
132.5°	620.6	629.3	630.0	625.6	623.1
135°	655.2	664.8	666.7	665.7	663.2
137.5°	693.7	701.5	703.0	702.4	698.7
140°	727.6	735.4	739.7	739.7	736.3
142.5°	762.5	770.2	772.7	773.6	770.2
145°	795.4	801.6	806.6	807.6	804.1
147.5°	824.9	832.7	836.4	838.0	834.5
150°	855.4	860.7	864.1	866.9	864.1
152.5°	882.5	887.7	892.1	895.5	892.1
155°	909.5	912.0	914.8	919.2	916.3
157.5°	932.9	934.7	936.2	942.5	938.1
160°	953.7	955.5	956.4	961.7	958.0
162.5°	972.9	972.9	973.9	979.7	975.4
165°	989.4	988.5	988.5	994.7	990.3
167.5°	1004.4	1001.5	1001.5	1007.8	1003.4
170°	1015.5	1013.0	1012.1	1018.3	1013.0
172.5°	1023.3	1020.8	1019.9	1026.1	1020.8
175°	1029.6	1027.0	1025.2	1031.4	1026.1
177.5°	1033.0	1030.5	1028.6	1033.9	1028.6
180°	1031.4	1031.4	1031.4	1031.4	1031.4

TEST NUMBER: P916676

CATALOG NUMBER: DFN2DIP-PN3F0-060D040US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.11	12.09	11.95	12.96	14.03	10.67	11.66	11.51	12.52	13.60
	3H	12.77	13.66	13.62	14.53	15.63	12.29	13.17	13.14	14.05	15.15
	4H	13.36	14.20	14.23	15.08	16.19	12.87	13.71	13.74	14.59	15.71
	6H	13.76	14.53	14.64	15.42	16.55	13.27	14.05	14.15	14.93	16.06
	8H	13.87	14.60	14.76	15.51	16.64	13.38	14.11	14.27	15.02	16.15
	12H	13.92	14.62	14.81	15.52	16.67	13.42	14.12	14.32	15.02	16.17
4H	2H	11.58	12.42	12.45	13.30	14.41	11.23	12.07	12.10	12.95	14.06
	3H	13.45	14.15	14.33	15.06	16.19	13.05	13.75	13.93	14.66	15.79
	4H	14.16	14.80	15.06	15.71	16.87	13.75	14.39	14.64	15.29	16.45
	6H	14.68	15.23	15.59	16.16	17.32	14.26	14.81	15.17	15.74	16.90
	8H	14.83	15.35	15.74	16.27	17.44	14.40	14.92	15.32	15.84	17.02
	12H	14.91	15.37	15.84	16.31	17.49	14.47	14.93	15.40	15.88	17.05
8H	4H	14.37	14.88	15.28	15.81	16.98	14.00	14.51	14.91	15.44	16.61
	6H	15.00	15.42	15.94	16.39	17.56	14.62	15.05	15.56	16.01	17.18
	8H	15.21	15.59	16.16	16.55	17.74	14.83	15.21	15.78	16.17	17.35
	12H	15.35	15.68	16.30	16.63	17.87	14.95	15.28	15.90	16.23	17.47
12H	4H	14.36	14.82	15.29	15.77	16.94	14.00	14.46	14.93	15.40	16.58
	6H	15.03	15.40	15.98	16.36	17.55	14.66	15.04	15.61	16.00	17.19
	8H	15.27	15.60	16.22	16.55	17.79	14.90	15.23	15.85	16.18	17.42

END OF REPORT