

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919279

Luminaire Tested: DFN2DIP-PN2F0-050D020US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919279
REPORT IS A COMBINATION OF REPORTS P900988 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-050D020US935-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5364.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919279

CATALOG NUMBER: DFN2DIP-PN2F0-050D020US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919279

CATALOG NUMBER: DFN2DIP-PN2F0-050D020US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73
1	103	98	95	91	97	93	90	87	83	81	78	74	72	70	65	64	63
2	94	87	81	76	88	82	77	72	74	69	66	66	63	60	58	56	54
3	86	77	70	64	81	73	66	61	66	60	56	59	55	51	52	49	47
4	79	69	61	55	75	65	58	53	59	53	49	53	48	45	47	44	41
5	73	62	53	48	69	59	51	46	53	47	42	48	43	39	43	39	36
6	68	56	47	42	64	53	46	40	48	42	38	43	39	35	39	35	32
7	63	50	43	37	59	48	41	36	44	38	33	40	35	31	36	32	29
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26
9	55	42	35	30	52	41	34	29	37	31	27	34	29	25	31	27	24
10	51	39	32	27	48	37	31	26	34	29	25	31	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3854	3854	3854
5°	3854	3784	3811
10°	3809	3702	3681
15°	3751	3572	3485
20°	3675	3395	3245
25°	3598	3199	3014
30°	3496	2999	2722
35°	3396	2784	2467
40°	3293	2563	2174
45°	3176	2319	1909
50°	3053	2073	1651
55°	2924	1811	1404
60°	2775	1539	1150
65°	2603	1264	1029
70°	2394	1007	923
75°	2132	871	829
80°	1754	708	701
85°	1146	441	498

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3176 cd/sqm

TEST NUMBER: P919279

CATALOG NUMBER: DFN2DIP-PN2F0-050D020US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	3.1
10°-20°	457.8	8.5
20°-30°	642.7	12.0
30°-40°	700.6	13.1
40°-50°	643.9	12.0
50°-60°	505.7	9.4
60°-70°	329.2	6.1
70°-80°	169.5	3.2
80°-90°	44.3	0.8
90°-100°	19.2	0.4
100°-110°	71.4	1.3
110°-120°	189.5	3.5
120°-130°	314.2	5.9
130°-140°	333.8	6.2
140°-150°	310.2	5.8
150°-160°	249.4	4.6
160°-170°	160.7	3.0
170°-180°	55.3	1.0
0°-30°	1267.2	23.6
0°-40°	1967.8	36.7
0°-60°	3117.4	58.1
0°-90°	3660.3	68.2
90°-120°	280.0	5.2
90°-150°	1238.3	23.1
90°-180°	1704.0	31.8
0°-180°	5364.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1779	1779	1779	1779	1779	
5°	1779	1771	1750	1765	1760	169
15°	1692	1675	1620	1589	1573	477
25°	1536	1484	1378	1312	1288	706
35°	1324	1242	1100	998	963	828
45°	1082	974	805	691	652	836
55°	823	697	523	427	396	735
65°	556	425	280	226	221	551
75°	296	184	129	118	116	313
85°	69	35	31	31	31	79
90°	0	5	8	10	11	5
95°	27	13	16	18	18	32
105°	128	140	26	30	32	137
115°	242	249	260	65	34	238
125°	342	347	355	358	360	305
135°	423	430	434	438	437	327
145°	491	490	498	500	498	307
155°	540	537	542	544	541	249
165°	569	567	568	571	568	161
175°	582	580	580	583	579	55
180°	581	581	581	581	581	

TEST NUMBER: P919279

CATALOG NUMBER: DFN2DIP-PN2F0-050D020US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1779.3	1779.3	1779.3	1779.3	1779.3
2.5°	1787.3	1779.3	1761.5	1777.7	1774.4
5°	1779.3	1771.2	1750.2	1764.7	1760.0
7.5°	1764.7	1755.1	1732.6	1739.0	1730.9
10°	1745.4	1734.1	1702.0	1697.1	1687.5
12.5°	1721.3	1706.8	1663.3	1653.7	1635.9
15°	1692.3	1674.6	1619.9	1589.3	1573.2
17.5°	1658.5	1632.7	1565.0	1529.6	1503.8
20°	1619.9	1587.6	1507.1	1467.0	1431.4
22.5°	1578.0	1540.9	1447.5	1392.8	1368.7
25°	1536.1	1484.5	1378.3	1312.3	1288.1
27.5°	1486.3	1431.4	1313.9	1238.2	1201.2
30°	1433.1	1371.8	1243.0	1161.0	1117.4
32.5°	1381.6	1307.4	1175.5	1078.8	1038.5
35°	1323.6	1241.5	1099.8	998.3	962.9
37.5°	1267.2	1178.6	1029.0	917.7	877.6
40°	1207.6	1111.1	954.8	840.5	798.7
42.5°	1146.5	1043.4	880.8	761.6	721.4
45°	1082.1	974.1	805.1	690.7	652.0
47.5°	1020.9	906.6	732.7	618.3	582.9
50°	953.3	839.0	661.8	550.6	516.9
52.5°	887.2	766.4	594.2	487.9	457.4
55°	822.8	697.1	523.2	426.7	396.1
57.5°	756.8	628.0	460.5	370.4	344.6
60°	689.1	560.3	394.4	312.5	286.6
62.5°	623.2	494.4	338.1	260.9	248.1
65°	555.5	425.1	280.2	225.5	220.6
67.5°	491.1	360.7	225.5	198.0	193.2
70°	423.5	297.9	186.8	170.6	164.2
72.5°	359.1	239.9	156.2	143.4	140.1
75°	296.3	183.5	128.8	117.5	116.0
77.5°	233.5	130.4	101.5	95.0	91.7
80°	175.5	93.4	77.2	70.9	70.9
82.5°	122.3	62.9	53.1	49.9	49.9
85°	69.2	35.4	30.6	30.6	30.6
87.5°	25.8	12.8	12.8	11.3	11.3
90°	0.4	5.1	8.4	10.5	11.4
92.5°	10.5	8.9	10.1	10.9	11.4
95°	27.3	13.4	16.4	18.5	18.1
97.5°	49.2	14.7	21.4	22.7	23.2
100°	74.5	16.8	23.9	27.3	28.2
102.5°	102.2	101.3	24.8	29.4	30.7
105°	127.9	140.4	25.7	30.2	31.9
107.5°	157.7	168.2	26.5	31.1	32.8
110°	186.3	195.1	73.6	31.6	33.2



TEST NUMBER: P919279

CATALOG NUMBER: DFN2DIP-PN2F0-050D020US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.2	220.8	213.6	32.4	33.7
115°	241.8	248.9	259.5	64.7	34.5
117.5°	266.6	275.0	282.1	222.1	111.8
120°	294.4	300.7	308.2	313.3	256.5
122.5°	317.9	324.6	333.0	335.5	336.0
125°	341.9	347.3	355.3	358.3	359.6
127.5°	363.8	369.6	376.0	380.1	380.6
130°	384.3	391.1	395.7	400.4	399.9
132.5°	405.4	410.9	415.4	419.2	418.9
135°	423.1	429.8	433.5	437.8	437.0
137.5°	441.5	446.6	450.8	455.0	453.7
140°	459.6	463.0	467.6	471.4	469.3
142.5°	474.8	477.8	483.2	486.5	484.4
145°	490.8	490.3	497.5	500.4	498.3
147.5°	504.6	503.3	510.5	512.6	510.9
150°	518.1	515.1	521.9	524.3	522.3
152.5°	529.4	526.1	532.4	534.9	531.9
155°	540.4	536.6	541.7	544.2	540.8
157.5°	549.2	545.9	549.7	552.6	549.2
160°	556.8	554.2	556.8	559.3	556.4
162.5°	563.4	560.9	563.1	566.0	562.2
165°	569.4	566.9	568.1	571.1	568.1
167.5°	574.0	571.4	572.7	575.7	571.9
170°	577.8	575.2	576.1	579.0	575.2
172.5°	580.3	577.8	578.7	581.6	577.8
175°	582.4	579.5	580.3	583.2	579.0
177.5°	583.2	580.3	580.7	583.7	579.9
180°	581.2	581.2	581.2	581.2	581.2

TEST NUMBER: P919279

CATALOG NUMBER: DFN2DIP-PN2F0-050D020US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.27	14.28	14.06	15.08	16.07	9.24	10.25	10.03	11.05	12.04
	3H	14.94	15.84	15.75	16.66	17.68	10.43	11.32	11.23	12.14	13.16
	4H	15.55	16.39	16.37	17.22	18.25	10.87	11.72	11.69	12.54	13.57
	6H	15.96	16.74	16.79	17.57	18.61	11.19	11.97	12.02	12.80	13.84
	8H	16.08	16.82	16.92	17.68	18.72	11.27	12.02	12.12	12.87	13.91
	12H	16.14	16.85	16.99	17.69	18.76	11.32	12.02	12.16	12.87	13.94
4H	2H	13.31	14.15	14.13	14.98	16.01	9.85	10.69	10.67	11.52	12.55
	3H	15.13	15.83	15.97	16.69	17.74	11.19	11.90	12.03	12.75	13.80
	4H	15.81	16.45	16.66	17.31	18.38	11.73	12.37	12.58	13.23	14.30
	6H	16.32	16.87	17.18	17.75	18.83	12.14	12.69	13.01	13.58	14.65
	8H	16.48	17.00	17.35	17.88	18.96	12.27	12.78	13.13	13.66	14.74
	12H	16.58	17.04	17.46	17.93	19.03	12.33	12.79	13.22	13.69	14.78
8H	4H	15.79	16.30	16.66	17.18	18.27	12.01	12.53	12.88	13.40	14.49
	6H	16.34	16.76	17.23	17.68	18.77	12.51	12.94	13.41	13.86	14.95
	8H	16.54	16.92	17.45	17.83	18.94	12.69	13.07	13.60	13.98	15.09
	12H	16.67	17.01	17.58	17.91	19.07	12.81	13.14	13.71	14.04	15.20
12H	4H	15.75	16.21	16.64	17.11	18.20	12.02	12.49	12.91	13.38	14.47
	6H	16.31	16.69	17.22	17.60	18.71	12.56	12.94	13.47	13.85	14.95
	8H	16.53	16.86	17.44	17.76	18.92	12.76	13.09	13.67	14.00	15.16