

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919299

Luminaire Tested: DFN2DIP-PN2F0-060D020US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919299
REPORT IS A COMBINATION OF REPORTS P900990 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-060D020US935-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6095.8 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 80.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919299

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919299

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	68	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	54	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	50	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	34	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4624	4624	4624
5°	4624	4541	4573
10°	4571	4442	4418
15°	4501	4286	4181
20°	4410	4074	3894
25°	4317	3839	3616
30°	4195	3599	3267
35°	4075	3341	2960
40°	3952	3076	2609
45°	3811	2783	2291
50°	3663	2488	1981
55°	3509	2174	1685
60°	3330	1848	1380
65°	3124	1517	1235
70°	2873	1208	1108
75°	2557	1045	994
80°	2104	849	842
85°	1375	529	598

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3811 cd/sqm

TEST NUMBER: P919299

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	3.3
10°-20°	549.3	9.0
20°-30°	771.2	12.7
30°-40°	840.7	13.8
40°-50°	772.7	12.7
50°-60°	606.8	10.0
60°-70°	395.0	6.5
70°-80°	203.3	3.3
80°-90°	52.9	0.9
90°-100°	19.2	0.3
100°-110°	71.4	1.2
110°-120°	189.5	3.1
120°-130°	314.2	5.2
130°-140°	333.8	5.5
140°-150°	310.2	5.1
150°-160°	249.4	4.1
160°-170°	160.7	2.6
170°-180°	55.3	0.9
0°-30°	1520.7	24.9
0°-40°	2361.4	38.7
0°-60°	3740.9	61.4
0°-90°	4392.1	72.1
90°-120°	280.0	4.6
90°-150°	1238.3	20.3
90°-180°	1704.0	28.0
0°-180°	6095.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	0	5	8	10	11	6
95°	27	13	16	18	18	32
105°	128	140	26	30	32	137
115°	242	249	260	65	34	238
125°	342	347	355	358	360	305
135°	423	430	434	438	437	327
145°	491	490	498	500	498	307
155°	540	537	542	544	541	249
165°	569	567	568	571	568	161
175°	582	580	580	583	579	55
180°	581	581	581	581	581	

TEST NUMBER: P919299

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.4	5.1	8.4	10.5	11.4
92.5°	10.5	8.9	10.1	10.9	11.4
95°	27.3	13.4	16.4	18.5	18.1
97.5°	49.2	14.7	21.4	22.7	23.2
100°	74.5	16.8	23.9	27.3	28.2
102.5°	102.2	101.3	24.8	29.4	30.7
105°	127.9	140.4	25.7	30.2	31.9
107.5°	157.7	168.2	26.5	31.1	32.8
110°	186.3	195.1	73.6	31.6	33.2



TEST NUMBER: P919299

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.2	220.8	213.6	32.4	33.7
115°	241.8	248.9	259.5	64.7	34.5
117.5°	266.6	275.0	282.1	222.1	111.8
120°	294.4	300.7	308.2	313.3	256.5
122.5°	317.9	324.6	333.0	335.5	336.0
125°	341.9	347.3	355.3	358.3	359.6
127.5°	363.8	369.6	376.0	380.1	380.6
130°	384.3	391.1	395.7	400.4	399.9
132.5°	405.4	410.9	415.4	419.2	418.9
135°	423.1	429.8	433.5	437.8	437.0
137.5°	441.5	446.6	450.8	455.0	453.7
140°	459.6	463.0	467.6	471.4	469.3
142.5°	474.8	477.8	483.2	486.5	484.4
145°	490.8	490.3	497.5	500.4	498.3
147.5°	504.6	503.3	510.5	512.6	510.9
150°	518.1	515.1	521.9	524.3	522.3
152.5°	529.4	526.1	532.4	534.9	531.9
155°	540.4	536.6	541.7	544.2	540.8
157.5°	549.2	545.9	549.7	552.6	549.2
160°	556.8	554.2	556.8	559.3	556.4
162.5°	563.4	560.9	563.1	566.0	562.2
165°	569.4	566.9	568.1	571.1	568.1
167.5°	574.0	571.4	572.7	575.7	571.9
170°	577.8	575.2	576.1	579.0	575.2
172.5°	580.3	577.8	578.7	581.6	577.8
175°	582.4	579.5	580.3	583.2	579.0
177.5°	583.2	580.3	580.7	583.7	579.9
180°	581.2	581.2	581.2	581.2	581.2

TEST NUMBER: P919299

CATALOG NUMBER: DFN2DIP-PN2F0-060D020US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.20	15.25	14.95	16.02	16.94	10.17	11.22	10.92	11.98	12.90
	3H	15.88	16.81	16.64	17.59	18.54	11.36	12.30	12.12	13.07	14.02
	4H	16.48	17.37	17.26	18.15	19.11	11.81	12.69	12.59	13.48	14.44
	6H	16.90	17.71	17.69	18.50	19.48	12.12	12.94	12.92	13.73	14.71
	8H	17.02	17.80	17.82	18.61	19.59	12.21	12.99	13.02	13.80	14.78
	12H	17.08	17.82	17.89	18.62	19.63	12.26	12.99	13.06	13.80	14.80
4H	2H	14.24	15.13	15.03	15.91	16.87	10.78	11.67	11.57	12.45	13.41
	3H	16.07	16.80	16.86	17.62	18.60	12.13	12.87	12.93	13.68	14.66
	4H	16.75	17.42	17.56	18.24	19.25	12.67	13.34	13.48	14.16	15.17
	6H	17.26	17.84	18.09	18.68	19.69	13.09	13.66	13.91	14.50	15.52
	8H	17.43	17.97	18.26	18.80	19.83	13.21	13.75	14.04	14.58	15.61
	12H	17.52	18.00	18.37	18.86	19.89	13.27	13.76	14.12	14.62	15.65
8H	4H	16.73	17.27	17.56	18.11	19.13	12.96	13.49	13.79	14.33	15.36
	6H	17.28	17.73	18.14	18.61	19.63	13.46	13.90	14.32	14.78	15.81
	8H	17.49	17.88	18.36	18.76	19.80	13.64	14.03	14.51	14.91	15.95
	12H	17.62	17.97	18.49	18.84	19.93	13.75	14.10	14.62	14.97	16.07
12H	4H	16.69	17.18	17.54	18.04	19.07	12.97	13.45	13.82	14.31	15.34
	6H	17.26	17.65	18.13	18.53	19.57	13.50	13.90	14.37	14.78	15.82
	8H	17.47	17.82	18.35	18.69	19.79	13.71	14.06	14.58	14.92	16.02