

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916707

Luminaire Tested: DFN2DIP-PN3F0-070D040US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916707
REPORT IS A COMBINATION OF REPORTS P901054 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D040US930-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8079.5 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 99.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916707

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916707

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		65
1	101	96	93	89	94	90	87	84	79	77	74		68	67	65		59
2	92	85	79	74	86	80	74	70	70	66	62		61	58	55		52
3	84	75	68	62	79	71	64	59	62	57	53		54	51	47		47
4	78	67	59	53	72	63	56	51	56	50	46		49	45	41		42
5	71	60	52	46	67	57	49	44	50	44	40		44	40	36		38
6	66	54	46	40	62	51	44	39	45	40	35		40	35	32		35
7	61	49	41	36	57	46	39	34	41	36	31		37	32	29		32
8	57	45	37	32	53	42	35	31	38	32	28		34	29	26		30
9	53	41	34	29	50	39	32	28	35	29	25		31	27	23		28
10	50	38	31	26	47	36	29	25	32	27	23		29	24	21		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2757	2757	2757
5°	2760	2712	2730
10°	2731	2656	2640
15°	2692	2567	2501
20°	2640	2444	2332
25°	2588	2307	2168
30°	2518	2166	1961
35°	2449	2015	1779
40°	2379	1859	1571
45°	2298	1686	1382
50°	2213	1511	1198
55°	2125	1326	1021
60°	2023	1131	839
65°	1906	934	754
70°	1763	750	681
75°	1584	657	617
80°	1324	545	531
85°	900	354	392

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2298 cd/sqm

TEST NUMBER: P916707

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	2.7
10°-20°	606.9	7.5
20°-30°	852.0	10.5
30°-40°	928.8	11.5
40°-50°	853.6	10.6
50°-60°	670.4	8.3
60°-70°	436.4	5.4
70°-80°	224.6	2.8
80°-90°	59.3	0.7
90°-100°	36.3	0.4
100°-110°	135.3	1.7
110°-120°	358.8	4.4
120°-130°	595.1	7.4
130°-140°	632.1	7.8
140°-150°	587.5	7.3
150°-160°	472.3	5.8
160°-170°	304.4	3.8
170°-180°	104.8	1.3
0°-30°	1679.9	20.8
0°-40°	2608.7	32.3
0°-60°	4132.7	51.2
0°-90°	4852.9	60.1
90°-120°	530.4	6.6
90°-150°	2345.2	29.0
90°-180°	3227.0	39.9
0°-180°	8079.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2359	2359	2359	2359	2359	
5°	2359	2348	2320	2340	2333	224
15°	2244	2220	2147	2107	2086	632
25°	2036	1968	1827	1740	1708	937
35°	1755	1646	1458	1324	1276	1098
45°	1434	1291	1067	916	864	1108
55°	1091	924	694	566	525	975
65°	736	564	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	1	10	16	20	21	8
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	

TEST NUMBER: P916707

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2358.7	2358.7	2358.7	2358.7	2358.7
2.5°	2369.3	2358.7	2335.2	2356.7	2352.4
5°	2358.7	2348.1	2320.3	2339.5	2333.1
7.5°	2339.5	2326.8	2296.9	2305.3	2294.7
10°	2313.9	2299.0	2256.3	2249.8	2237.1
12.5°	2281.9	2262.7	2205.0	2192.3	2168.7
15°	2243.5	2219.9	2147.4	2106.9	2085.6
17.5°	2198.6	2164.5	2074.8	2027.8	1993.6
20°	2147.4	2104.6	1998.0	1944.7	1897.6
22.5°	2092.0	2042.8	1918.9	1846.4	1814.5
25°	2036.5	1968.0	1827.2	1739.8	1707.6
27.5°	1970.3	1897.6	1741.8	1641.5	1592.4
30°	1899.9	1818.6	1647.8	1539.1	1481.4
32.5°	1831.5	1733.2	1558.4	1430.2	1376.7
35°	1754.7	1645.8	1458.1	1323.6	1276.4
37.5°	1680.0	1562.4	1364.1	1216.6	1163.4
40°	1600.9	1473.0	1265.8	1114.3	1058.7
42.5°	1519.9	1383.3	1167.7	1009.6	956.4
45°	1434.5	1291.4	1067.4	915.7	864.5
47.5°	1353.4	1201.9	971.3	819.6	772.7
50°	1263.7	1112.2	877.3	729.9	685.3
52.5°	1176.1	1015.9	787.7	646.8	606.3
55°	1090.7	924.2	693.7	565.7	525.2
57.5°	1003.3	832.5	610.6	491.0	456.8
60°	913.6	742.8	522.9	414.3	380.0
62.5°	826.1	655.4	448.2	345.8	328.8
65°	736.5	563.5	371.4	299.0	292.4
67.5°	651.1	478.1	299.0	262.4	256.2
70°	561.4	394.9	247.5	226.2	217.6
72.5°	476.1	318.0	207.0	190.0	185.7
75°	392.7	243.2	170.7	155.8	153.8
77.5°	309.6	172.8	134.5	125.9	121.6
80°	232.6	123.8	102.4	94.0	94.0
82.5°	162.2	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.2	17.0	17.0	14.9	14.9
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9



TEST NUMBER: P916707

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P916707

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.52	12.44	12.40	13.33	14.45	7.49	8.41	8.36	9.30	10.42
	3H	13.20	14.02	14.09	14.92	16.07	8.68	9.50	9.56	10.40	11.55
	4H	13.81	14.59	14.71	15.49	16.65	9.13	9.91	10.03	10.81	11.97
	6H	14.23	14.95	15.14	15.86	17.03	9.45	10.16	10.36	11.07	12.25
	8H	14.36	15.04	15.28	15.97	17.14	9.54	10.22	10.46	11.15	12.32
	12H	14.42	15.07	15.35	15.99	17.18	9.58	10.23	10.51	11.15	12.35
4H	2H	11.55	12.33	12.46	13.23	14.39	8.09	8.87	9.00	9.77	10.93
	3H	13.38	14.03	14.30	14.96	16.13	9.44	10.09	10.36	11.02	12.20
	4H	14.07	14.66	15.00	15.59	16.79	9.99	10.58	10.92	11.51	12.71
	6H	14.59	15.09	15.53	16.05	17.25	10.41	10.91	11.35	11.87	13.07
	8H	14.76	15.23	15.70	16.18	17.39	10.53	11.01	11.48	11.96	13.17
	12H	14.86	15.28	15.82	16.25	17.46	10.60	11.02	11.56	11.99	13.21
8H	4H	14.04	14.52	14.99	15.47	16.68	10.27	10.74	11.22	11.69	12.91
	6H	14.61	15.00	15.58	15.99	17.20	10.79	11.18	11.76	12.17	13.38
	8H	14.82	15.16	15.80	16.14	17.37	10.97	11.32	11.95	12.30	13.53
	12H	14.96	15.26	15.94	16.23	17.51	11.09	11.39	12.07	12.37	13.65
12H	4H	14.00	14.43	14.96	15.39	16.61	10.28	10.71	11.24	11.67	12.89
	6H	14.58	14.93	15.56	15.91	17.14	10.83	11.18	11.81	12.16	13.39
	8H	14.80	15.11	15.78	16.08	17.36	11.04	11.35	12.02	12.32	13.60