

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919314

Luminaire Tested: DFN2DIP-PN2F0-060D060US935-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P919314  
REPORT IS A COMBINATION OF REPORTS P899510 AND P896349  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN2F0-060D060US935-RLLFLL  
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8963.0 lumens  
Efficiency: N/A  
Efficacy: 76.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 117.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.946  
Total Harmonic Distortion (THDi): 0.132  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P919314  
CATALOG NUMBER: DFN2DIP-PN2F0-060D060US935-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P919314

CATALOG NUMBER: DFN2DIP-PN2F0-060D060US935-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31				31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4624	4624	4624
5°	4624	4541	4573
10°	4571	4442	4418
15°	4501	4286	4181
20°	4410	4074	3894
25°	4317	3839	3616
30°	4195	3599	3267
35°	4075	3341	2960
40°	3952	3076	2609
45°	3811	2783	2291
50°	3663	2488	1981
55°	3509	2174	1685
60°	3330	1848	1380
65°	3124	1517	1235
70°	2873	1208	1108
75°	2557	1045	994
80°	2104	849	842
85°	1375	529	598

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3811 cd/sqm



TEST NUMBER: P919314

CATALOG NUMBER: DFN2DIP-PN2F0-060D060US935-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.1	2.2
10°-20°	549.3	6.1
20°-30°	771.2	8.6
30°-40°	840.7	9.4
40°-50°	772.7	8.6
50°-60°	606.8	6.8
60°-70°	395.0	4.4
70°-80°	203.3	2.3
80°-90°	56.5	0.6
90°-100°	101.1	1.1
100°-110°	321.2	3.6
110°-120°	549.7	6.1
120°-130°	723.0	8.1
130°-140°	811.5	9.1
140°-150°	795.8	8.9
150°-160°	667.5	7.4
160°-170°	442.7	4.9
170°-180°	154.7	1.7
0°-30°	1520.7	17.0
0°-40°	2361.4	26.3
0°-60°	3740.9	41.7
0°-90°	4395.7	49.0
90°-120°	972.0	10.8
90°-150°	3302.3	36.8
90°-180°	4567.0	51.0
0°-180°	8963.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	2	18	48	45	47	9
95°	72	86	88	88	86	80
105°	296	300	303	306	306	313
115°	552	560	557	556	552	546
125°	802	815	811	806	805	717
135°	1038	1053	1056	1055	1051	802
145°	1260	1270	1278	1279	1274	787
155°	1441	1445	1449	1456	1452	663
165°	1567	1566	1566	1576	1569	442
175°	1631	1627	1624	1634	1625	155
180°	1634	1634	1634	1634	1634	



TEST NUMBER: P919314

CATALOG NUMBER: DFN2DIP-PN2F0-060D060US935-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	1.5	17.7	48.3	45.3	46.8
92.5°	30.6	41.4	42.9	44.3	44.3
95°	71.9	85.7	88.2	88.2	85.7
97.5°	119.7	132.5	137.9	137.9	137.9
100°	174.9	186.1	190.1	190.1	188.6
102.5°	233.0	241.3	246.8	248.2	246.8
105°	296.5	300.5	303.4	305.9	305.9
107.5°	359.6	365.5	365.5	366.4	359.6
110°	420.7	428.5	428.5	428.5	424.6



TEST NUMBER: P919314

CATALOG NUMBER: DFN2DIP-PN2F0-060D060US935-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	486.6	495.0	493.5	489.6	486.6
115°	551.6	559.6	557.1	555.6	551.6
117.5°	616.2	627.1	620.1	616.2	612.3
120°	681.2	692.1	681.2	681.2	676.7
122.5°	740.3	754.1	747.2	743.3	740.3
125°	802.4	814.7	810.7	806.3	804.9
127.5°	863.0	878.2	872.8	866.9	863.0
130°	919.6	937.4	934.9	931.9	926.5
132.5°	983.2	996.9	997.9	991.0	987.0
135°	1037.8	1053.1	1056.0	1054.6	1050.6
137.5°	1098.9	1111.2	1113.7	1112.7	1106.8
140°	1152.6	1164.9	1171.8	1171.8	1166.4
142.5°	1207.7	1220.0	1224.0	1225.5	1220.0
145°	1260.0	1269.8	1277.7	1279.2	1273.8
147.5°	1306.7	1319.0	1325.0	1327.4	1322.0
150°	1355.0	1363.4	1368.8	1373.2	1368.8
152.5°	1397.8	1406.3	1413.2	1418.6	1413.2
155°	1440.7	1444.7	1449.1	1456.0	1451.6
157.5°	1477.6	1480.7	1483.1	1493.0	1486.1
160°	1510.7	1513.6	1515.1	1523.4	1517.6
162.5°	1541.2	1541.2	1542.6	1552.0	1545.1
165°	1567.3	1565.8	1565.8	1575.7	1568.8
167.5°	1591.0	1586.6	1586.6	1596.4	1589.5
170°	1608.7	1604.7	1603.3	1613.1	1604.7
172.5°	1621.0	1617.0	1615.6	1625.4	1617.0
175°	1630.8	1626.9	1623.9	1633.8	1625.4
177.5°	1636.2	1632.4	1629.4	1637.7	1629.4
180°	1633.8	1633.8	1633.8	1633.8	1633.8



TEST NUMBER: P919314  
 CATALOG NUMBER: DFN2DIP-PN2F0-060D060US935-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.26	13.08	13.23	14.06	15.35	8.23	9.05	9.20	10.03	11.32
	3H	13.92	14.65	14.90	15.64	16.95	9.40	10.13	10.38	11.12	12.43
	4H	14.51	15.21	15.51	16.20	17.52	9.84	10.53	10.83	11.53	12.84
	6H	14.91	15.55	15.92	16.55	17.88	10.14	10.78	11.15	11.78	13.11
	8H	15.03	15.64	16.04	16.66	17.98	10.22	10.83	11.24	11.85	13.17
	12H	15.08	15.66	16.10	16.67	18.02	10.26	10.84	11.28	11.85	13.20
4H	2H	12.27	12.97	13.27	13.96	15.28	8.81	9.51	9.81	10.50	11.82
	3H	14.08	14.65	15.09	15.68	17.01	10.14	10.72	11.15	11.74	13.07
	4H	14.75	15.28	15.77	16.30	17.65	10.67	11.20	11.69	12.22	13.57
	6H	15.25	15.70	16.28	16.74	18.09	11.07	11.53	12.10	12.57	13.92
	8H	15.41	15.84	16.44	16.87	18.23	11.19	11.62	12.22	12.65	14.01
	12H	15.49	15.88	16.54	16.92	18.29	11.25	11.63	12.30	12.68	14.05
8H	4H	14.72	15.14	15.75	16.17	17.54	10.94	11.36	11.97	12.40	13.76
	6H	15.26	15.61	16.31	16.68	18.05	11.44	11.78	12.49	12.86	14.22
	8H	15.46	15.77	16.52	16.83	18.21	11.61	11.92	12.67	12.98	14.36
	12H	15.59	15.86	16.65	16.91	18.33	11.72	11.99	12.78	13.04	14.47
12H	4H	14.67	15.05	15.71	16.10	17.47	10.94	11.32	11.99	12.37	13.74
	6H	15.23	15.54	16.29	16.60	17.98	11.48	11.79	12.54	12.85	14.23
	8H	15.44	15.71	16.50	16.76	18.19	11.67	11.94	12.74	13.00	14.42