

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921953

Luminaire Tested: DFN2DIP-PN2F0-020D040US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921953
REPORT IS A COMBINATION OF REPORTS P901001 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D040US940-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5296.8 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 47.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921953

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921953

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1503	1503	1503
5°	1503	1479	1490
10°	1488	1456	1467
15°	1464	1428	1434
20°	1432	1392	1399
25°	1400	1349	1360
30°	1361	1309	1310
35°	1324	1262	1258
40°	1277	1214	1208
45°	1232	1166	1157
50°	1182	1116	1098
55°	1129	1058	1043
60°	1069	990	980
65°	1004	918	906
70°	920	831	826
75°	806	727	749
80°	668	593	606
85°	452	374	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1232 cd/sqm

TEST NUMBER: P921953

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	1.2
10°-20°	183.8	3.5
20°-30°	270.1	5.1
30°-40°	313.7	5.9
40°-50°	313.3	5.9
50°-60°	273.2	5.2
60°-70°	201.9	3.8
70°-80°	114.2	2.2
80°-90°	32.3	0.6
90°-100°	39.7	0.7
100°-110°	148.0	2.8
110°-120°	392.4	7.4
120°-130°	650.9	12.3
130°-140°	691.4	13.1
140°-150°	642.6	12.1
150°-160°	516.6	9.8
160°-170°	332.9	6.3
170°-180°	114.6	2.2
0°-30°	519.1	9.8
0°-40°	832.8	15.7
0°-60°	1419.3	26.8
0°-90°	1767.7	33.4
90°-120°	580.1	11.0
90°-150°	2565.0	48.4
90°-180°	3529.0	66.6
0°-180°	5296.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	694	691	684	689	688	66
15°	661	657	648	651	647	186
25°	598	592	581	582	581	275
35°	516	509	498	494	491	322
45°	420	415	405	398	395	324
55°	318	314	306	298	294	284
65°	214	210	204	198	194	212
75°	112	111	107	103	105	120
85°	27	27	26	24	23	30
90°	1	10	17	22	24	5
95°	56	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	537	134	72	493
125°	708	720	736	742	745	632
135°	876	890	898	907	905	677
145°	1016	1016	1030	1036	1032	636
155°	1119	1112	1122	1127	1120	516
165°	1179	1174	1177	1183	1177	333
175°	1206	1200	1202	1208	1199	115
180°	1204	1204	1204	1204	1204	

TEST NUMBER: P921953

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	693.9	693.9	693.9	693.9	693.9
2.5°	697.9	694.6	687.2	693.9	692.7
5°	693.9	691.3	683.9	689.3	688.0
7.5°	689.3	685.3	678.0	683.3	682.0
10°	682.0	677.3	669.3	674.6	672.6
12.5°	671.9	668.0	660.0	663.3	661.9
15°	660.6	656.7	647.9	650.6	647.3
17.5°	646.6	642.7	633.9	637.2	633.9
20°	631.2	627.2	617.9	619.9	617.2
22.5°	615.9	609.9	601.2	601.2	599.9
25°	597.9	592.5	581.2	582.5	581.2
27.5°	577.8	573.2	564.5	562.6	559.2
30°	557.9	552.5	542.5	540.6	537.8
32.5°	536.5	532.5	521.8	517.8	515.1
35°	515.9	509.2	498.5	494.5	491.1
37.5°	492.5	486.4	475.7	471.1	467.7
40°	468.4	463.1	452.4	446.5	443.7
42.5°	445.1	439.7	429.1	422.4	418.4
45°	419.7	415.1	405.0	397.7	395.0
47.5°	395.0	390.4	379.7	372.3	368.4
50°	369.0	365.7	356.3	347.0	343.7
52.5°	343.7	338.9	330.3	323.0	318.3
55°	317.6	313.6	305.6	297.7	294.3
57.5°	291.6	288.3	279.6	271.6	268.9
60°	265.6	263.0	253.6	246.2	244.2
62.5°	240.2	235.5	228.9	222.2	219.5
65°	214.2	210.2	203.6	197.5	194.2
67.5°	187.5	184.1	178.2	173.5	170.9
70°	162.8	160.2	154.1	149.5	146.9
72.5°	137.5	134.8	131.4	126.8	124.8
75°	112.1	110.8	107.4	103.4	104.8
77.5°	89.4	86.8	85.3	83.4	81.4
80°	66.8	66.1	64.7	62.7	61.3
82.5°	45.4	45.4	44.8	42.1	42.1
85°	27.3	26.7	26.0	24.0	23.4
87.5°	12.0	10.7	9.4	7.4	6.7
90°	0.8	10.4	17.4	21.8	23.5
92.5°	21.8	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.3	37.5
97.5°	101.9	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.5	58.3
102.5°	211.6	210.0	51.4	60.9	63.6
105°	264.7	291.0	53.1	62.7	66.2
107.5°	326.6	348.4	54.9	64.5	67.9
110°	385.9	404.1	152.5	65.4	68.8

TEST NUMBER: P921953

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.7	457.3	442.5	67.1	69.7
115°	500.8	515.6	537.4	134.1	71.5
117.5°	552.2	569.6	584.5	459.9	231.7
120°	609.8	622.8	638.5	649.0	531.4
122.5°	658.4	672.4	689.9	695.1	696.0
125°	708.1	719.5	736.0	742.2	744.8
127.5°	753.4	765.6	778.7	787.5	788.3
130°	796.1	810.1	819.6	829.2	828.4
132.5°	839.6	851.0	860.6	868.4	867.6
135°	876.3	890.3	898.0	906.8	905.1
137.5°	914.5	925.0	933.8	942.4	939.9
140°	952.0	959.0	968.6	976.4	972.1
142.5°	983.5	989.5	1000.9	1007.7	1003.4
145°	1016.5	1015.7	1030.4	1036.5	1032.2
147.5°	1045.2	1042.6	1057.4	1061.8	1058.4
150°	1073.1	1067.0	1081.0	1086.2	1081.8
152.5°	1096.6	1089.7	1102.7	1108.0	1101.9
155°	1119.3	1111.5	1121.9	1127.1	1120.2
157.5°	1137.6	1130.6	1138.5	1144.6	1137.6
160°	1153.2	1148.0	1153.2	1158.4	1152.4
162.5°	1167.2	1162.0	1166.4	1172.4	1164.6
165°	1179.4	1174.2	1176.8	1182.9	1176.8
167.5°	1189.0	1183.7	1186.4	1192.5	1184.6
170°	1196.9	1191.6	1193.3	1199.4	1191.6
172.5°	1202.0	1196.9	1198.6	1204.7	1196.9
175°	1206.3	1200.2	1202.0	1208.1	1199.4
177.5°	1208.1	1202.0	1202.9	1209.1	1201.2
180°	1203.8	1203.8	1203.8	1203.8	1203.8

TEST NUMBER: P921953

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.80	7.53	7.89	8.61	10.11	6.36	7.09	7.45	8.18	9.67
	3H	8.43	9.08	9.52	10.18	11.68	7.95	8.60	9.05	9.70	11.21
	4H	9.00	9.62	10.10	10.71	12.23	8.51	9.13	9.62	10.23	11.75
	6H	9.37	9.94	10.49	11.04	12.57	8.89	9.46	10.00	10.56	12.08
	8H	9.47	10.01	10.59	11.13	12.64	8.98	9.52	10.10	10.64	12.16
	12H	9.50	10.02	10.63	11.13	12.67	9.01	9.53	10.13	10.64	12.18
4H	2H	7.23	7.85	8.35	8.95	10.46	6.88	7.50	8.00	8.60	10.11
	3H	9.06	9.58	10.18	10.70	12.23	8.66	9.18	9.78	10.30	11.83
	4H	9.76	10.23	10.88	11.34	12.89	9.34	9.82	10.47	10.93	12.48
	6H	10.24	10.65	11.38	11.79	13.33	9.82	10.23	10.96	11.37	12.91
	8H	10.38	10.76	11.51	11.89	13.44	9.96	10.34	11.09	11.47	13.02
	12H	10.44	10.78	11.59	11.92	13.48	10.00	10.35	11.15	11.49	13.05
8H	4H	9.93	10.31	11.06	11.44	12.99	9.56	9.94	10.69	11.07	12.62
	6H	10.53	10.85	11.68	12.02	13.57	10.16	10.47	11.31	11.64	13.19
	8H	10.74	11.01	11.90	12.16	13.73	10.36	10.63	11.52	11.78	13.35
	12H	10.85	11.09	12.01	12.24	13.84	10.45	10.70	11.62	11.84	13.45
12H	4H	9.91	10.25	11.06	11.39	12.95	9.55	9.89	10.70	11.03	12.59
	6H	10.56	10.83	11.71	11.98	13.55	10.19	10.47	11.35	11.62	13.19
	8H	10.78	11.02	11.94	12.16	13.77	10.41	10.65	11.57	11.79	13.40