

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916723

Luminaire Tested: DFN2DIP-PN3F0-070D080US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916723
REPORT IS A COMBINATION OF REPORTS P901110 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D080US930-RLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11308.2 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 130.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916723
CATALOG NUMBER: DFN2DIP-PN3F0-070D080US930-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P916723

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43	43	43	43
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	44	43	37	37	37	37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32	32	32	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	27	27	27	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24	24	24	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21	21	21	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22	19	19	19	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17	17	17	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15	15	15	15
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14	14	14	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14	12	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2757	2757	2757
5°	2760	2712	2730
10°	2731	2656	2640
15°	2692	2567	2501
20°	2640	2444	2332
25°	2588	2307	2168
30°	2518	2166	1961
35°	2449	2015	1779
40°	2379	1859	1571
45°	2298	1686	1382
50°	2213	1511	1198
55°	2125	1326	1021
60°	2023	1131	839
65°	1906	934	754
70°	1763	750	681
75°	1584	657	617
80°	1324	545	531
85°	900	354	392

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2298 cd/sqm



TEST NUMBER: P916723

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	2.0
10°-20°	606.9	5.4
20°-30°	852.0	7.5
30°-40°	928.8	8.2
40°-50°	853.6	7.5
50°-60°	670.4	5.9
60°-70°	436.4	3.9
70°-80°	224.6	2.0
80°-90°	61.2	0.5
90°-100°	72.6	0.6
100°-110°	270.6	2.4
110°-120°	717.6	6.3
120°-130°	1190.2	10.5
130°-140°	1264.3	11.2
140°-150°	1175.0	10.4
150°-160°	944.7	8.4
160°-170°	608.7	5.4
170°-180°	209.5	1.9
0°-30°	1679.9	14.9
0°-40°	2608.7	23.1
0°-60°	4132.7	36.5
0°-90°	4854.9	42.9
90°-120°	1060.8	9.4
90°-150°	4690.4	41.5
90°-180°	6453.0	57.1
0°-180°	11308.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2359	2359	2359	2359	2359	
5°	2359	2348	2320	2340	2333	224
15°	2244	2220	2147	2107	2086	632
25°	2036	1968	1827	1740	1708	937
35°	1755	1646	1458	1324	1276	1098
45°	1434	1291	1067	916	864	1108
55°	1091	924	694	566	525	975
65°	736	564	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	2	19	32	40	43	11
95°	104	51	62	70	68	123
105°	484	532	97	115	121	517
115°	916	943	983	245	131	902
125°	1295	1316	1346	1357	1362	1155
135°	1602	1628	1642	1658	1655	1238
145°	1859	1857	1884	1895	1887	1163
155°	2047	2032	2052	2061	2048	943
165°	2157	2147	2152	2163	2152	609
175°	2206	2195	2198	2209	2193	210
180°	2201	2201	2201	2201	2201	



TEST NUMBER: P916723

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2358.7	2358.7	2358.7	2358.7	2358.7
2.5°	2369.3	2358.7	2335.2	2356.7	2352.4
5°	2358.7	2348.1	2320.3	2339.5	2333.1
7.5°	2339.5	2326.8	2296.9	2305.3	2294.7
10°	2313.9	2299.0	2256.3	2249.8	2237.1
12.5°	2281.9	2262.7	2205.0	2192.3	2168.7
15°	2243.5	2219.9	2147.4	2106.9	2085.6
17.5°	2198.6	2164.5	2074.8	2027.8	1993.6
20°	2147.4	2104.6	1998.0	1944.7	1897.6
22.5°	2092.0	2042.8	1918.9	1846.4	1814.5
25°	2036.5	1968.0	1827.2	1739.8	1707.6
27.5°	1970.3	1897.6	1741.8	1641.5	1592.4
30°	1899.9	1818.6	1647.8	1539.1	1481.4
32.5°	1831.5	1733.2	1558.4	1430.2	1376.7
35°	1754.7	1645.8	1458.1	1323.6	1276.4
37.5°	1680.0	1562.4	1364.1	1216.6	1163.4
40°	1600.9	1473.0	1265.8	1114.3	1058.7
42.5°	1519.9	1383.3	1167.7	1009.6	956.4
45°	1434.5	1291.4	1067.4	915.7	864.5
47.5°	1353.4	1201.9	971.3	819.6	772.7
50°	1263.7	1112.2	877.3	729.9	685.3
52.5°	1176.1	1015.9	787.7	646.8	606.3
55°	1090.7	924.2	693.7	565.7	525.2
57.5°	1003.3	832.5	610.6	491.0	456.8
60°	913.6	742.8	522.9	414.3	380.0
62.5°	826.1	655.4	448.2	345.8	328.8
65°	736.5	563.5	371.4	299.0	292.4
67.5°	651.1	478.1	299.0	262.4	256.2
70°	561.4	394.9	247.5	226.2	217.6
72.5°	476.1	318.0	207.0	190.0	185.7
75°	392.7	243.2	170.7	155.8	153.8
77.5°	309.6	172.8	134.5	125.9	121.6
80°	232.6	123.8	102.4	94.0	94.0
82.5°	162.2	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.2	17.0	17.0	14.9	14.9
90°	1.5	19.1	31.8	39.9	43.0
92.5°	39.9	33.5	38.2	41.4	43.0
95°	103.5	50.9	62.0	70.2	68.5
97.5°	186.3	55.8	81.1	86.1	87.6
100°	282.0	63.8	90.8	103.5	106.6
102.5°	387.0	383.9	94.0	111.4	116.3
105°	484.2	532.1	97.2	114.6	121.1
107.5°	597.3	637.0	100.4	117.8	124.3
110°	705.7	739.0	278.8	119.5	125.8



TEST NUMBER: P916723

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	807.6	836.2	809.2	122.5	127.5
115°	915.8	942.9	982.8	245.3	130.7
117.5°	1009.8	1041.6	1068.9	840.9	423.7
120°	1115.0	1138.8	1167.6	1186.7	971.6
122.5°	1204.0	1229.6	1261.6	1271.0	1272.8
125°	1294.9	1315.6	1345.9	1357.1	1361.8
127.5°	1377.7	1400.0	1424.1	1439.9	1441.4
130°	1455.8	1481.3	1498.8	1516.4	1514.8
132.5°	1535.5	1556.2	1573.7	1588.0	1586.5
135°	1602.4	1627.9	1642.1	1658.2	1655.0
137.5°	1672.4	1691.5	1707.6	1723.5	1718.7
140°	1740.8	1753.7	1771.2	1785.5	1777.5
142.5°	1798.4	1809.5	1830.1	1842.8	1834.8
145°	1858.9	1857.2	1884.2	1895.4	1887.4
147.5°	1911.3	1906.6	1933.6	1941.6	1935.3
150°	1962.3	1951.2	1976.7	1986.1	1978.2
152.5°	2005.3	1992.6	2016.4	2026.1	2014.9
155°	2046.7	2032.5	2051.6	2061.1	2048.4
157.5°	2080.2	2067.5	2081.9	2093.0	2080.2
160°	2108.9	2099.3	2108.9	2118.4	2107.2
162.5°	2134.3	2124.8	2132.7	2143.9	2129.6
165°	2156.6	2147.2	2151.9	2163.0	2151.9
167.5°	2174.2	2164.5	2169.4	2180.6	2166.2
170°	2188.6	2178.9	2182.1	2193.3	2178.9
172.5°	2198.0	2188.6	2191.8	2202.9	2188.6
175°	2206.0	2194.8	2198.0	2209.1	2193.3
177.5°	2209.1	2198.0	2199.7	2210.8	2196.5
180°	2201.2	2201.2	2201.2	2201.2	2201.2



TEST NUMBER: P916723
 CATALOG NUMBER: DFN2DIP-PN3F0-070D080US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.93	10.71	10.96	11.74	13.11	5.90	6.68	6.92	7.70	9.07
	3H	11.60	12.30	12.63	13.33	14.72	7.08	7.77	8.11	8.81	10.20
	4H	12.20	12.86	13.25	13.90	15.30	7.52	8.18	8.57	9.22	10.62
	6H	12.62	13.22	13.67	14.26	15.67	7.84	8.44	8.89	9.48	10.89
	8H	12.74	13.31	13.80	14.37	15.78	7.92	8.50	8.98	9.55	10.96
	12H	12.80	13.34	13.86	14.39	15.82	7.96	8.51	9.02	9.56	10.99
4H	2H	9.94	10.60	11.00	11.64	13.04	6.49	7.14	7.54	8.18	9.58
	3H	11.76	12.31	12.82	13.37	14.78	7.82	8.37	8.88	9.44	10.85
	4H	12.45	12.95	13.51	14.00	15.44	8.36	8.86	9.43	9.92	11.35
	6H	12.95	13.38	14.03	14.46	15.89	8.77	9.20	9.85	10.28	11.71
	8H	13.12	13.52	14.20	14.60	16.04	8.90	9.30	9.97	10.37	11.81
	12H	13.21	13.57	14.30	14.66	16.11	8.96	9.32	10.05	10.41	11.85
8H	4H	12.41	12.81	13.48	13.88	15.32	8.64	9.04	9.71	10.11	11.55
	6H	12.97	13.30	14.06	14.41	15.85	9.15	9.48	10.24	10.59	12.03
	8H	13.18	13.47	14.28	14.57	16.03	9.33	9.62	10.43	10.72	12.18
	12H	13.31	13.56	14.42	14.66	16.16	9.44	9.70	10.55	10.79	12.29
12H	4H	12.36	12.72	13.45	13.81	15.25	8.64	9.00	9.73	10.09	11.53
	6H	12.94	13.23	14.04	14.33	15.79	9.19	9.48	10.30	10.58	12.04
	8H	13.15	13.41	14.26	14.50	16.00	9.40	9.65	10.50	10.74	12.24