

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921954

Luminaire Tested: DFN2DIP-PN2F0-020D040US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921954
REPORT IS A COMBINATION OF REPORTS P899482 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D040US940-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4672.6 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 47.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921954

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921954

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1596	1596	1596
5°	1596	1568	1579
10°	1578	1534	1525
15°	1554	1479	1444
20°	1522	1407	1344
25°	1490	1325	1248
30°	1448	1242	1128
35°	1407	1154	1022
40°	1364	1062	901
45°	1316	961	791
50°	1265	859	684
55°	1211	751	581
60°	1150	638	477
65°	1079	524	426
70°	992	417	382
75°	883	361	344
80°	727	294	290
85°	474	183	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1521 cd/sqm

TEST NUMBER: P921954

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	1.5
10°-20°	189.6	4.1
20°-30°	266.3	5.7
30°-40°	290.2	6.2
40°-50°	266.8	5.7
50°-60°	209.5	4.5
60°-70°	136.4	2.9
70°-80°	70.2	1.5
80°-90°	21.1	0.5
90°-100°	69.8	1.5
100°-110°	221.8	4.7
110°-120°	379.5	8.1
120°-130°	499.2	10.7
130°-140°	560.3	12.0
140°-150°	549.4	11.8
150°-160°	460.9	9.9
160°-170°	305.7	6.5
170°-180°	106.8	2.3
0°-30°	525.0	11.2
0°-40°	815.2	17.4
0°-60°	1291.4	27.6
0°-90°	1519.1	32.5
90°-120°	671.2	14.4
90°-150°	2280.1	48.8
90°-180°	3153.0	67.5
0°-180°	4672.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	737	734	725	731	729	70
15°	701	694	671	658	652	198
25°	636	615	571	544	534	293
35°	548	514	456	414	399	343
45°	448	404	334	286	270	346
55°	341	289	217	177	164	305
65°	230	176	116	94	91	228
75°	123	76	53	49	48	130
85°	29	15	13	13	13	33
90°	1	12	33	31	32	5
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	

TEST NUMBER: P921954

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	737.1	737.1	737.1	737.1	737.1
2.5°	740.4	737.1	729.7	736.5	735.1
5°	737.1	733.8	725.0	731.1	729.1
7.5°	731.1	727.1	717.7	720.4	717.0
10°	723.1	718.4	705.1	703.0	699.1
12.5°	713.1	707.0	689.0	685.1	677.7
15°	701.1	693.7	671.0	658.3	651.8
17.5°	687.1	676.4	648.4	633.6	623.0
20°	671.0	657.6	624.4	607.7	593.0
22.5°	653.7	638.4	599.7	577.0	567.0
25°	636.4	615.0	571.0	543.7	533.6
27.5°	615.7	593.0	544.3	512.9	497.6
30°	593.7	568.3	515.0	481.0	462.9
32.5°	572.3	541.6	487.0	446.9	430.3
35°	548.3	514.3	455.7	413.6	398.9
37.5°	524.9	488.2	426.2	380.2	363.6
40°	500.2	460.3	395.6	348.2	330.8
42.5°	474.9	432.3	364.9	315.5	298.9
45°	448.3	403.5	333.6	286.1	270.1
47.5°	422.9	375.6	303.5	256.1	241.5
50°	394.9	347.6	274.2	228.1	214.2
52.5°	367.5	317.4	246.1	202.2	189.5
55°	340.8	288.8	216.8	176.8	164.1
57.5°	313.5	260.1	190.8	153.5	142.8
60°	285.5	232.1	163.5	129.5	118.8
62.5°	258.2	204.8	140.1	108.1	102.7
65°	230.2	176.1	116.1	93.5	91.4
67.5°	203.5	149.4	93.5	82.0	80.1
70°	175.4	123.4	77.3	70.7	68.0
72.5°	148.7	99.3	64.6	59.4	58.1
75°	122.7	76.0	53.3	48.7	48.1
77.5°	96.8	54.0	42.0	39.3	38.0
80°	72.7	38.7	32.0	29.3	29.3
82.5°	50.6	26.0	22.0	20.7	20.7
85°	28.6	14.6	12.7	12.7	12.7
87.5°	10.7	5.4	5.4	4.6	4.6
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2

TEST NUMBER: P921954

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0

TEST NUMBER: P921954

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.75	7.46	7.85	8.55	10.05	2.73	3.43	3.82	4.52	6.03
	3H	8.40	9.03	9.51	10.13	11.65	3.89	4.52	4.99	5.62	7.14
	4H	8.99	9.59	10.11	10.69	12.22	4.32	4.92	5.44	6.02	7.55
	6H	9.39	9.94	10.52	11.04	12.58	4.62	5.17	5.74	6.27	7.81
	8H	9.50	10.03	10.63	11.15	12.68	4.70	5.22	5.83	6.34	7.87
	12H	9.55	10.05	10.69	11.16	12.72	4.73	5.23	5.86	6.34	7.89
4H	2H	6.75	7.35	7.88	8.45	9.98	3.29	3.89	4.42	4.99	6.52
	3H	8.55	9.04	9.68	10.17	11.71	4.61	5.11	5.74	6.24	7.78
	4H	9.22	9.67	10.35	10.79	12.35	5.14	5.60	6.27	6.72	8.27
	6H	9.71	10.10	10.85	11.24	12.79	5.53	5.92	6.67	7.07	8.62
	8H	9.87	10.23	11.01	11.37	12.93	5.65	6.02	6.79	7.15	8.71
	12H	9.94	10.28	11.10	11.42	12.99	5.70	6.03	6.86	7.18	8.75
8H	4H	9.17	9.54	10.31	10.67	12.24	5.40	5.76	6.54	6.90	8.46
	6H	9.71	10.01	10.87	11.19	12.75	5.89	6.19	7.05	7.36	8.93
	8H	9.91	10.18	11.08	11.33	12.91	6.07	6.33	7.23	7.48	9.07
	12H	10.03	10.26	11.20	11.41	13.03	6.17	6.40	7.34	7.55	9.17
12H	4H	9.12	9.45	10.27	10.59	12.16	5.39	5.72	6.55	6.87	8.44
	6H	9.68	9.95	10.85	11.10	12.68	5.93	6.19	7.10	7.35	8.93
	8H	9.88	10.12	11.05	11.27	12.88	6.12	6.35	7.29	7.50	9.12

END OF REPORT