

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921959

Luminaire Tested: DFN2DIP-PN2F0-020D050US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921959
REPORT IS A COMBINATION OF REPORTS P901012 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D050US940-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5929.9 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921959

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921959

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	88	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	23	21
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13
8	51	39	32	27	45	36	29	25	28	24	20	21	18	16	15	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1596	1596	1596
5°	1596	1568	1579
10°	1578	1534	1525
15°	1554	1479	1444
20°	1522	1407	1344
25°	1490	1325	1248
30°	1448	1242	1128
35°	1407	1154	1022
40°	1364	1062	901
45°	1316	961	791
50°	1265	859	684
55°	1211	751	581
60°	1150	638	477
65°	1079	524	426
70°	992	417	382
75°	883	361	344
80°	727	294	290
85°	474	183	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1380 cd/sqm

TEST NUMBER: P921959

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	1.2
10°-20°	189.6	3.2
20°-30°	266.3	4.5
30°-40°	290.2	4.9
40°-50°	266.8	4.5
50°-60°	209.5	3.5
60°-70°	136.4	2.3
70°-80°	70.2	1.2
80°-90°	20.6	0.3
90°-100°	49.6	0.8
100°-110°	185.0	3.1
110°-120°	490.6	8.3
120°-130°	813.6	13.7
130°-140°	864.3	14.6
140°-150°	803.2	13.5
150°-160°	645.8	10.9
160°-170°	416.1	7.0
170°-180°	143.2	2.4
0°-30°	525.0	8.9
0°-40°	815.2	13.7
0°-60°	1291.4	21.8
0°-90°	1518.6	25.6
90°-120°	725.2	12.2
90°-150°	3206.2	54.1
90°-180°	4411.0	74.4
0°-180°	5929.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	737	734	725	731	729	70
15°	701	694	671	658	652	198
25°	636	615	571	544	534	293
35°	548	514	456	414	399	343
45°	448	404	334	286	270	346
55°	341	289	217	177	164	305
65°	230	176	116	94	91	228
75°	123	76	53	49	48	130
85°	29	15	13	13	13	33
90°	1	13	22	27	29	6
95°	71	35	42	48	47	84
105°	331	364	66	78	83	354
115°	626	644	672	168	89	616
125°	885	899	920	928	931	789
135°	1095	1113	1122	1134	1131	846
145°	1271	1270	1288	1296	1290	795
155°	1399	1389	1402	1409	1400	645
165°	1474	1468	1471	1478	1471	416
175°	1508	1500	1502	1510	1499	144
180°	1505	1505	1505	1505	1505	

TEST NUMBER: P921959

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	737.1	737.1	737.1	737.1	737.1
2.5°	740.4	737.1	729.7	736.5	735.1
5°	737.1	733.8	725.0	731.1	729.1
7.5°	731.1	727.1	717.7	720.4	717.0
10°	723.1	718.4	705.1	703.0	699.1
12.5°	713.1	707.0	689.0	685.1	677.7
15°	701.1	693.7	671.0	658.3	651.8
17.5°	687.1	676.4	648.4	633.6	623.0
20°	671.0	657.6	624.4	607.7	593.0
22.5°	653.7	638.4	599.7	577.0	567.0
25°	636.4	615.0	571.0	543.7	533.6
27.5°	615.7	593.0	544.3	512.9	497.6
30°	593.7	568.3	515.0	481.0	462.9
32.5°	572.3	541.6	487.0	446.9	430.3
35°	548.3	514.3	455.7	413.6	398.9
37.5°	524.9	488.2	426.2	380.2	363.6
40°	500.2	460.3	395.6	348.2	330.8
42.5°	474.9	432.3	364.9	315.5	298.9
45°	448.3	403.5	333.6	286.1	270.1
47.5°	422.9	375.6	303.5	256.1	241.5
50°	394.9	347.6	274.2	228.1	214.2
52.5°	367.5	317.4	246.1	202.2	189.5
55°	340.8	288.8	216.8	176.8	164.1
57.5°	313.5	260.1	190.8	153.5	142.8
60°	285.5	232.1	163.5	129.5	118.8
62.5°	258.2	204.8	140.1	108.1	102.7
65°	230.2	176.1	116.1	93.5	91.4
67.5°	203.5	149.4	93.5	82.0	80.1
70°	175.4	123.4	77.3	70.7	68.0
72.5°	148.7	99.3	64.6	59.4	58.1
75°	122.7	76.0	53.3	48.7	48.1
77.5°	96.8	54.0	42.0	39.3	38.0
80°	72.7	38.7	32.0	29.3	29.3
82.5°	50.6	26.0	22.0	20.7	20.7
85°	28.6	14.6	12.7	12.7	12.7
87.5°	10.7	5.4	5.4	4.6	4.6
90°	1.1	13.0	21.8	27.3	29.3
92.5°	27.3	22.9	26.1	28.4	29.3
95°	70.7	34.8	42.4	48.0	46.8
97.5°	127.3	38.2	55.5	58.9	59.8
100°	192.8	43.6	62.1	70.7	72.9
102.5°	264.6	262.4	64.3	76.2	79.5
105°	331.0	363.7	66.4	78.4	82.8
107.5°	408.3	435.4	68.7	80.5	85.0
110°	482.4	505.2	190.6	81.7	86.0

TEST NUMBER: P921959

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	552.1	571.6	553.1	83.8	87.1
115°	626.1	644.5	671.8	167.7	89.3
117.5°	690.3	712.0	730.7	574.8	289.6
120°	762.1	778.5	798.1	811.2	664.1
122.5°	823.0	840.5	862.4	868.9	870.0
125°	885.1	899.4	920.1	927.6	930.9
127.5°	941.7	957.0	973.5	984.3	985.3
130°	995.1	1012.6	1024.5	1036.5	1035.5
132.5°	1049.6	1063.8	1075.7	1085.6	1084.5
135°	1095.4	1112.9	1122.5	1133.5	1131.3
137.5°	1143.2	1156.3	1167.2	1178.1	1174.9
140°	1190.0	1198.8	1210.7	1220.5	1215.1
142.5°	1229.3	1237.0	1251.1	1259.7	1254.3
145°	1270.7	1269.5	1288.0	1295.7	1290.2
147.5°	1306.5	1303.2	1321.8	1327.2	1322.9
150°	1341.4	1333.8	1351.2	1357.7	1352.3
152.5°	1370.7	1362.1	1378.4	1385.0	1377.3
155°	1399.1	1389.4	1402.4	1408.9	1400.3
157.5°	1421.9	1413.3	1423.1	1430.7	1421.9
160°	1441.6	1435.0	1441.6	1448.0	1440.5
162.5°	1458.9	1452.5	1457.9	1465.5	1455.7
165°	1474.2	1467.8	1471.0	1478.5	1471.0
167.5°	1486.2	1479.6	1483.0	1490.6	1480.8
170°	1496.0	1489.4	1491.7	1499.2	1489.4
172.5°	1502.5	1496.0	1498.3	1505.8	1496.0
175°	1508.0	1500.3	1502.5	1510.1	1499.2
177.5°	1510.1	1502.5	1503.7	1511.3	1501.5
180°	1504.7	1504.7	1504.7	1504.7	1504.7

TEST NUMBER: P921959

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.78	6.44	6.93	7.58	9.16	1.75	2.42	2.90	3.55	5.13
	3H	7.42	8.02	8.58	9.16	10.76	2.91	3.50	4.06	4.64	6.24
	4H	8.01	8.57	9.17	9.72	11.32	3.34	3.90	4.50	5.04	6.65
	6H	8.41	8.93	9.58	10.07	11.68	3.64	4.16	4.81	5.30	6.91
	8H	8.52	9.01	9.69	10.17	11.78	3.71	4.21	4.89	5.37	6.97
	12H	8.57	9.04	9.74	10.19	11.82	3.75	4.21	4.92	5.36	6.99
4H	2H	5.77	6.34	6.94	7.48	9.08	2.31	2.88	3.49	4.02	5.62
	3H	7.56	8.03	8.74	9.20	10.81	3.63	4.10	4.80	5.26	6.88
	4H	8.23	8.66	9.41	9.82	11.45	4.16	4.59	5.33	5.74	7.38
	6H	8.72	9.09	9.90	10.27	11.89	4.55	4.92	5.73	6.09	7.72
	8H	8.88	9.22	10.06	10.39	12.03	4.66	5.01	5.84	6.18	7.82
	12H	8.96	9.27	10.15	10.45	12.09	4.71	5.02	5.91	6.20	7.85
8H	4H	8.18	8.53	9.36	9.70	11.34	4.41	4.76	5.59	5.92	7.56
	6H	8.72	9.01	9.92	10.22	11.85	4.90	5.18	6.10	6.39	8.03
	8H	8.92	9.17	10.13	10.36	12.02	5.08	5.32	6.28	6.51	8.17
	12H	9.04	9.26	10.25	10.44	12.13	5.17	5.39	6.38	6.58	8.27
12H	4H	8.13	8.44	9.32	9.62	11.26	4.40	4.72	5.60	5.90	7.54
	6H	8.70	8.94	9.90	10.13	11.79	4.94	5.19	6.15	6.38	8.04
	8H	8.89	9.11	10.10	10.30	11.99	5.13	5.35	6.34	6.53	8.22