

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916754

Luminaire Tested: DFN2DIP-PN3F0-080D090US930-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P916754  
REPORT IS A COMBINATION OF REPORTS P899606 AND P896399  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-080D090US930-RLLFLL  
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12037.8 lumens  
Efficiency: N/A  
Efficacy: 79.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 151.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9967  
Total Harmonic Distortion (THDi): 0.063  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P916754  
CATALOG NUMBER: DFN2DIP-PN3F0-080D090US930-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P916754

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US930-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46				46
1	97	93	90	86	89	86	83	80	72	70	68	59	57	56	47	46	45	40				40
2	89	82	76	71	82	75	70	66	63	60	57	52	50	47	42	40	39	34				34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33	29				29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	26				26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22				22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20				20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16				16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15				15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15	13				13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3151	3151	3151
5°	3154	3099	3120
10°	3121	3036	3017
15°	3076	2933	2859
20°	3018	2793	2665
25°	2958	2636	2478
30°	2877	2475	2242
35°	2799	2303	2034
40°	2719	2124	1796
45°	2626	1927	1580
50°	2530	1728	1369
55°	2429	1515	1167
60°	2312	1293	959
65°	2178	1067	862
70°	2015	857	778
75°	1810	751	705
80°	1513	623	607
85°	1028	405	448

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2626 cd/sqm



TEST NUMBER: P916754

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US930-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	252.6	2.1
10°-20°	693.6	5.8
20°-30°	973.7	8.1
30°-40°	1061.4	8.8
40°-50°	975.6	8.1
50°-60°	766.2	6.4
60°-70°	498.7	4.1
70°-80°	256.7	2.1
80°-90°	72.1	0.6
90°-100°	143.6	1.2
100°-110°	456.3	3.8
110°-120°	780.8	6.5
120°-130°	1026.9	8.5
130°-140°	1152.6	9.6
140°-150°	1130.3	9.4
150°-160°	948.2	7.9
160°-170°	628.8	5.2
170°-180°	219.8	1.8
0°-30°	1919.9	15.9
0°-40°	2981.4	24.8
0°-60°	4723.1	39.2
0°-90°	5550.6	46.1
90°-120°	1380.7	11.5
90°-150°	4690.5	39.0
90°-180°	6487.0	53.9
0°-180°	12037.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2696	2696	2696	2696	2696	
5°	2696	2684	2652	2674	2666	256
15°	2564	2537	2454	2408	2384	722
25°	2327	2249	2088	1988	1952	1070
35°	2005	1881	1666	1513	1459	1255
45°	1639	1476	1220	1046	988	1266
55°	1246	1056	793	646	600	1114
65°	842	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	2	25	69	64	66	12
95°	102	122	125	125	122	114
105°	421	427	431	434	434	444
115°	784	795	791	789	784	775
125°	1140	1157	1152	1145	1143	1018
135°	1474	1496	1500	1498	1492	1139
145°	1790	1804	1815	1817	1809	1118
155°	2046	2052	2058	2068	2062	942
165°	2226	2224	2224	2238	2228	628
175°	2316	2311	2307	2321	2309	220
180°	2321	2321	2321	2321	2321	



TEST NUMBER: P916754

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US930-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2695.7	2695.7	2695.7	2695.7	2695.7
2.5°	2707.9	2695.7	2668.8	2693.3	2688.4
5°	2695.7	2683.6	2651.7	2673.7	2666.4
7.5°	2673.7	2659.2	2625.0	2634.6	2622.4
10°	2644.4	2627.4	2578.7	2571.2	2556.7
12.5°	2608.0	2586.0	2519.9	2505.4	2478.5
15°	2563.9	2537.0	2454.2	2407.9	2383.5
17.5°	2512.7	2473.6	2371.1	2317.6	2278.4
20°	2454.2	2405.3	2283.4	2222.6	2168.7
22.5°	2390.8	2334.6	2193.1	2110.2	2073.7
25°	2327.4	2249.2	2088.2	1988.3	1951.6
27.5°	2251.8	2168.7	1990.6	1876.0	1819.8
30°	2171.3	2078.4	1883.3	1759.0	1693.0
32.5°	2093.1	1980.8	1781.0	1634.5	1573.4
35°	2005.4	1880.9	1666.3	1512.6	1458.7
37.5°	1919.9	1785.7	1558.9	1390.4	1329.6
40°	1829.7	1683.4	1446.6	1273.4	1210.0
42.5°	1737.0	1580.9	1334.5	1153.9	1093.0
45°	1639.4	1475.9	1219.8	1046.4	988.0
47.5°	1546.8	1373.6	1110.1	936.7	883.1
50°	1444.2	1271.1	1002.7	834.2	783.2
52.5°	1344.1	1161.1	900.2	739.2	692.9
55°	1246.5	1056.3	792.8	646.5	600.2
57.5°	1146.6	951.5	697.8	561.2	522.0
60°	1044.1	849.0	597.6	473.4	434.3
62.5°	944.2	749.0	512.3	395.3	375.9
65°	841.7	643.9	424.4	341.7	334.1
67.5°	744.1	546.4	341.7	299.9	292.8
70°	641.6	451.4	282.9	258.5	248.7
72.5°	544.0	363.4	236.6	217.2	212.2
75°	448.8	278.0	195.2	178.1	175.8
77.5°	353.8	197.5	153.8	143.9	139.0
80°	265.8	141.6	117.0	107.4	107.4
82.5°	185.3	95.2	80.5	75.6	75.6
85°	104.8	53.6	46.3	46.3	46.3
87.5°	39.1	19.4	19.4	17.1	17.1
90°	2.1	25.2	68.6	64.3	66.4
92.5°	43.4	58.8	60.9	62.9	62.9
95°	102.2	121.7	125.2	125.2	121.7
97.5°	170.0	188.2	195.9	195.9	195.9
100°	248.3	264.5	270.0	270.0	268.0
102.5°	330.9	342.8	350.5	352.6	350.5
105°	421.2	426.7	431.0	434.5	434.5
107.5°	510.7	519.1	519.1	520.5	510.7
110°	597.5	608.7	608.7	608.7	603.1



TEST NUMBER: P916754

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US930-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	691.2	703.1	701.0	695.4	691.2
115°	783.6	794.8	791.2	789.2	783.6
117.5°	875.2	890.6	880.8	875.2	869.6
120°	967.6	982.9	967.6	967.6	961.2
122.5°	1051.5	1071.1	1061.4	1055.7	1051.5
125°	1139.7	1157.2	1151.6	1145.2	1143.2
127.5°	1225.7	1247.4	1239.7	1231.3	1225.7
130°	1306.2	1331.4	1327.9	1323.6	1316.0
132.5°	1396.4	1416.0	1417.4	1407.6	1402.1
135°	1474.1	1495.7	1500.0	1497.9	1492.3
137.5°	1560.8	1578.3	1581.8	1580.5	1572.1
140°	1637.1	1654.6	1664.3	1664.3	1656.7
142.5°	1715.5	1732.9	1738.5	1740.7	1732.9
145°	1789.7	1803.6	1814.8	1816.9	1809.2
147.5°	1856.1	1873.6	1882.0	1885.5	1877.8
150°	1924.7	1936.6	1944.2	1950.5	1944.2
152.5°	1985.5	1997.4	2007.2	2014.9	2007.2
155°	2046.4	2051.9	2058.3	2068.1	2061.8
157.5°	2098.8	2103.1	2106.6	2120.5	2110.7
160°	2145.7	2149.9	2152.1	2163.9	2155.5
162.5°	2189.1	2189.1	2191.2	2204.5	2194.7
165°	2226.2	2224.1	2224.1	2238.1	2228.3
167.5°	2259.8	2253.5	2253.5	2267.4	2257.6
170°	2285.0	2279.3	2277.3	2291.2	2279.3
172.5°	2302.4	2296.9	2294.7	2308.8	2296.9
175°	2316.4	2310.8	2306.6	2320.7	2308.8
177.5°	2324.1	2318.5	2314.3	2326.2	2314.3
180°	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P916754  
 CATALOG NUMBER: DFN2DIP-PN3F0-080D090US930-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.72	11.52	11.72	12.52	13.85	6.69	7.49	7.68	8.49	9.82
	3H	12.39	13.10	13.40	14.12	15.47	7.87	8.58	8.87	9.59	10.94
	4H	12.99	13.67	14.01	14.68	16.04	8.31	8.99	9.33	10.00	11.36
	6H	13.41	14.03	14.44	15.05	16.42	8.62	9.25	9.65	10.27	11.64
	8H	13.53	14.12	14.56	15.16	16.52	8.71	9.30	9.75	10.34	11.70
	12H	13.59	14.15	14.63	15.18	16.57	8.75	9.31	9.79	10.34	11.73
4H	2H	10.73	11.41	11.76	12.42	13.78	7.27	7.95	8.30	8.97	10.32
	3H	12.55	13.11	13.59	14.16	15.53	8.61	9.18	9.65	10.22	11.59
	4H	13.24	13.75	14.28	14.79	16.18	9.16	9.67	10.20	10.71	12.10
	6H	13.75	14.19	14.80	15.25	16.64	9.57	10.01	10.62	11.07	12.46
	8H	13.92	14.33	14.97	15.38	16.78	9.69	10.10	10.74	11.16	12.56
	12H	14.01	14.38	15.08	15.44	16.85	9.75	10.12	10.82	11.19	12.60
8H	4H	13.20	13.61	14.25	14.67	16.07	9.43	9.84	10.48	10.89	12.30
	6H	13.76	14.10	14.83	15.19	16.60	9.94	10.28	11.01	11.37	12.77
	8H	13.97	14.27	15.05	15.35	16.77	10.13	10.42	11.21	11.50	12.92
	12H	14.11	14.37	15.19	15.44	16.90	10.24	10.50	11.32	11.57	13.04
12H	4H	13.15	13.52	14.22	14.59	16.00	9.43	9.80	10.50	10.87	12.28
	6H	13.73	14.03	14.82	15.11	16.53	9.99	10.29	11.07	11.36	12.78
	8H	13.95	14.21	15.03	15.28	16.75	10.19	10.45	11.28	11.53	12.99