

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921980

Luminaire Tested: DFN2DIP-PN2F0-030D060US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921980
REPORT IS A COMBINATION OF REPORTS P899503 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D060US940-FLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7383.4 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 80.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921980

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921980

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2254	2254	2254
5°	2254	2218	2235
10°	2233	2184	2201
15°	2196	2143	2151
20°	2148	2088	2099
25°	2100	2024	2040
30°	2041	1963	1965
35°	1985	1893	1887
40°	1916	1822	1812
45°	1848	1750	1735
50°	1773	1674	1647
55°	1693	1587	1564
60°	1604	1485	1470
65°	1506	1377	1359
70°	1380	1247	1239
75°	1209	1090	1123
80°	1000	890	911
85°	679	563	570

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2279 cd/sqm

TEST NUMBER: P921980

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	1.3
10°-20°	275.6	3.7
20°-30°	405.1	5.5
30°-40°	470.5	6.4
40°-50°	469.9	6.4
50°-60°	409.8	5.5
60°-70°	302.9	4.1
70°-80°	171.4	2.3
80°-90°	50.0	0.7
90°-100°	104.7	1.4
100°-110°	332.7	4.5
110°-120°	569.3	7.7
120°-130°	748.8	10.1
130°-140°	840.5	11.4
140°-150°	824.2	11.2
150°-160°	691.4	9.4
160°-170°	458.5	6.2
170°-180°	160.3	2.2
0°-30°	778.7	10.5
0°-40°	1249.2	16.9
0°-60°	2128.9	28.8
0°-90°	2653.2	35.9
90°-120°	1006.7	13.6
90°-150°	3420.1	46.3
90°-180°	4730.0	64.1
0°-180°	7383.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1041	1041	1041	1041	1041	
5°	1041	1037	1026	1034	1032	99
15°	991	985	972	976	971	279
25°	897	889	872	874	872	413
35°	774	764	748	742	737	483
45°	630	623	608	597	592	486
55°	476	470	458	446	442	426
65°	321	315	305	296	291	318
75°	168	166	161	155	157	179
85°	41	40	39	36	35	46
90°	2	18	50	47	48	7
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	

TEST NUMBER: P921980

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1040.9	1040.9	1040.9	1040.9	1040.9
2.5°	1047.0	1042.0	1030.9	1040.9	1039.0
5°	1040.9	1037.0	1025.9	1033.9	1032.0
7.5°	1033.9	1028.0	1016.9	1025.0	1023.0
10°	1023.0	1015.9	1004.0	1011.9	1009.0
12.5°	1007.9	1001.9	990.0	994.9	992.9
15°	990.9	985.0	971.9	975.9	970.9
17.5°	969.8	963.9	950.8	955.8	950.8
20°	946.8	940.8	926.8	929.8	925.9
22.5°	923.9	914.9	901.8	901.8	899.7
25°	896.8	888.9	871.8	873.8	871.8
27.5°	866.7	859.7	846.8	843.8	838.8
30°	836.8	828.8	813.8	810.7	806.7
32.5°	804.8	798.8	782.7	776.7	772.7
35°	773.7	763.7	747.7	741.6	736.6
37.5°	738.7	729.7	713.6	706.6	701.6
40°	702.7	694.6	678.6	669.7	665.7
42.5°	667.6	659.6	643.6	633.6	627.6
45°	629.6	622.6	607.5	596.6	592.5
47.5°	592.5	585.6	569.5	558.5	552.5
50°	553.5	548.5	534.5	520.5	515.5
52.5°	515.5	508.5	495.5	484.5	477.4
55°	476.5	470.5	458.4	446.5	441.5
57.5°	437.4	432.4	419.4	407.3	403.3
60°	398.3	394.4	380.4	369.3	366.4
62.5°	360.3	353.3	343.3	333.3	329.3
65°	321.4	315.3	305.3	296.3	291.3
67.5°	281.3	276.3	267.2	260.3	256.3
70°	244.2	240.2	231.2	224.2	220.3
72.5°	206.3	202.2	197.2	190.2	187.3
75°	168.1	166.2	161.1	155.2	157.2
77.5°	134.1	130.1	128.0	125.1	122.2
80°	100.1	99.1	97.0	94.1	92.1
82.5°	68.0	68.0	67.1	63.0	63.0
85°	41.0	40.0	39.1	36.0	35.0
87.5°	18.0	16.1	14.0	11.1	10.0
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7

TEST NUMBER: P921980

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1

TEST NUMBER: P921980

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.52	9.26	9.58	10.33	11.79	8.08	8.83	9.15	9.90	11.35
	3H	10.15	10.82	11.23	11.90	13.37	9.67	10.34	10.74	11.42	12.89
	4H	10.72	11.35	11.81	12.43	13.92	10.23	10.87	11.32	11.95	13.43
	6H	11.09	11.68	12.19	12.76	14.26	10.61	11.19	11.71	12.28	13.77
	8H	11.19	11.74	12.29	12.84	14.33	10.70	11.26	11.80	12.36	13.85
	12H	11.22	11.75	12.33	12.85	14.36	10.73	11.26	11.84	12.35	13.87
4H	2H	8.95	9.59	10.05	10.67	12.15	8.60	9.24	9.70	10.32	11.80
	3H	10.78	11.31	11.89	12.42	13.92	10.38	10.91	11.49	12.02	13.52
	4H	11.48	11.96	12.59	13.06	14.58	11.06	11.55	12.17	12.65	14.17
	6H	11.97	12.38	13.08	13.51	15.02	11.55	11.97	12.66	13.09	14.60
	8H	12.10	12.49	13.22	13.61	15.13	11.68	12.07	12.80	13.18	14.71
	12H	12.16	12.52	13.29	13.64	15.17	11.73	12.08	12.86	13.21	14.74
8H	4H	11.65	12.04	12.77	13.16	14.68	11.29	11.68	12.40	12.79	14.31
	6H	12.26	12.58	13.39	13.73	15.26	11.88	12.21	13.02	13.36	14.88
	8H	12.46	12.74	13.60	13.88	15.42	12.08	12.36	13.22	13.50	15.04
	12H	12.57	12.82	13.72	13.95	15.53	12.18	12.43	13.32	13.56	15.14
12H	4H	11.63	11.99	12.76	13.11	14.64	11.27	11.62	12.40	12.75	14.28
	6H	12.28	12.56	13.42	13.70	15.24	11.92	12.20	13.06	13.34	14.88
	8H	12.50	12.75	13.65	13.88	15.46	12.13	12.38	13.28	13.51	15.09