

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916776

Luminaire Tested: DFN2DIP-PN3F0-090D080US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916776
REPORT IS A COMBINATION OF REPORTS P899593 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D080US930-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13036.7 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 154.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916776

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916776

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US930-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		73	73	73		61	61	61
1	99	95	91	87		92	88	85	82		76	73	71		65	63	61		54	53	52
2	90	83	77	71		84	77	72	67		67	62	59		57	54	51		48	46	44
3	82	73	65	59		76	68	61	56		59	54	50		50	46	43		42	40	37
4	75	64	56	50		70	60	53	48		52	47	42		45	41	37		38	35	32
5	69	57	49	43		64	54	46	41		47	41	36		40	36	32		34	31	28
6	64	52	43	37		59	48	41	36		42	36	32		36	32	28		31	27	25
7	59	47	39	33		55	44	36	31		38	32	28		33	28	25		28	25	22
8	55	42	35	29		51	40	33	28		35	29	25		30	26	22		26	22	20
9	51	39	31	26		47	36	30	25		32	26	22		28	23	20		24	20	18
10	48	36	28	23		44	33	27	22		30	24	20		26	21	18		22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3338	3338	3338
5°	3341	3289	3312
10°	3312	3242	3265
15°	3261	3186	3194
20°	3193	3110	3121
25°	3126	3019	3037
30°	3042	2934	2930
35°	2962	2834	2817
40°	2864	2733	2709
45°	2766	2632	2599
50°	2659	2526	2472
55°	2547	2403	2354
60°	2420	2257	2220
65°	2281	2106	2061
70°	2104	1921	1889
75°	1860	1700	1729
80°	1564	1417	1427
85°	1103	938	930

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2766 cd/sqm

TEST NUMBER: P916776

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.7	2.1
10°-20°	756.1	5.8
20°-30°	1111.2	8.5
30°-40°	1290.5	9.9
40°-50°	1288.9	9.9
50°-60°	1123.9	8.6
60°-70°	830.8	6.4
70°-80°	470.1	3.6
80°-90°	129.9	1.0
90°-100°	127.6	1.0
100°-110°	405.6	3.1
110°-120°	694.1	5.3
120°-130°	912.8	7.0
130°-140°	1024.6	7.9
140°-150°	1004.7	7.7
150°-160°	842.8	6.5
160°-170°	558.9	4.3
170°-180°	195.4	1.5
0°-30°	2136.0	16.4
0°-40°	3426.5	26.3
0°-60°	5839.4	44.8
0°-90°	7270.2	55.8
90°-120°	1227.3	9.4
90°-150°	4169.4	32.0
90°-180°	5766.0	44.2
0°-180°	13036.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2855	2855	2855	2855	2855	
5°	2855	2844	2814	2836	2831	271
15°	2718	2702	2666	2677	2663	765
25°	2460	2438	2391	2397	2391	1132
35°	2122	2095	2051	2034	2021	1325
45°	1727	1708	1666	1636	1625	1333
55°	1307	1290	1257	1225	1211	1169
65°	881	865	837	813	799	871
75°	461	456	442	426	431	492
85°	112	110	107	99	96	125
90°	2	22	61	57	59	13
95°	91	108	111	111	108	101
105°	374	379	383	386	386	395
115°	696	706	703	702	696	689
125°	1013	1029	1024	1018	1016	905
135°	1310	1330	1333	1332	1326	1013
145°	1591	1603	1613	1615	1608	994
155°	1819	1824	1830	1838	1833	837
165°	1979	1977	1977	1989	1981	558
175°	2059	2054	2050	2063	2052	196
180°	2063	2063	2063	2063	2063	

TEST NUMBER: P916776

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2855.1	2855.1	2855.1	2855.1	2855.1
2.5°	2871.7	2858.0	2827.8	2855.1	2849.9
5°	2855.1	2844.3	2814.1	2835.9	2830.6
7.5°	2835.9	2819.6	2789.3	2811.5	2805.9
10°	2805.9	2786.7	2753.8	2775.6	2767.4
12.5°	2764.5	2748.2	2715.4	2729.0	2723.5
15°	2718.0	2701.7	2665.8	2676.9	2663.2
17.5°	2660.2	2643.9	2608.1	2621.8	2608.1
20°	2597.1	2580.7	2542.3	2550.4	2539.7
22.5°	2534.1	2509.4	2473.5	2473.5	2468.0
25°	2459.8	2438.0	2391.4	2396.7	2391.4
27.5°	2377.4	2358.2	2322.7	2314.6	2300.9
30°	2295.3	2273.1	2232.0	2223.9	2212.9
32.5°	2207.3	2191.0	2147.0	2130.5	2119.4
35°	2122.3	2094.9	2050.9	2034.3	2020.6
37.5°	2026.2	2001.4	1957.4	1938.2	1924.5
40°	1927.4	1905.3	1861.2	1836.8	1825.8
42.5°	1831.2	1809.1	1765.4	1737.8	1721.5
45°	1727.0	1707.8	1666.4	1636.4	1625.4
47.5°	1625.4	1606.1	1562.1	1531.9	1515.6
50°	1518.2	1504.5	1466.0	1427.6	1413.9
52.5°	1413.9	1394.6	1359.1	1328.9	1309.6
55°	1307.0	1290.4	1257.4	1224.6	1210.9
57.5°	1199.8	1186.1	1150.3	1117.4	1106.3
60°	1092.6	1081.8	1043.3	1013.1	1004.9
62.5°	988.3	969.1	941.7	914.4	903.3
65°	881.4	864.8	837.4	812.7	799.0
67.5°	771.6	757.7	733.1	714.0	702.9
70°	669.9	658.8	634.1	614.9	604.1
72.5°	565.7	554.6	540.9	521.7	513.6
75°	461.1	455.8	441.9	425.6	431.1
77.5°	367.9	356.9	351.3	343.2	335.0
80°	274.7	271.7	266.2	258.0	252.6
82.5°	186.7	186.7	184.1	173.0	173.0
85°	112.4	109.8	107.2	98.7	96.1
87.5°	49.5	43.9	38.5	30.3	27.4
90°	1.9	22.4	61.0	57.2	59.1
92.5°	38.6	52.3	54.1	55.9	55.9
95°	90.8	108.2	111.3	111.3	108.2
97.5°	151.2	167.3	174.1	174.1	174.1
100°	220.8	235.1	240.0	240.0	238.1
102.5°	294.2	304.8	311.5	313.4	311.5
105°	374.4	379.4	383.1	386.2	386.2
107.5°	454.0	461.5	461.5	462.7	454.0
110°	531.1	541.0	541.0	541.0	536.1

TEST NUMBER: P916776

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	614.4	625.0	623.1	618.2	614.4
115°	696.5	706.5	703.4	701.5	696.5
117.5°	778.0	791.7	782.9	778.0	773.0
120°	860.1	873.8	860.1	860.1	854.4
122.5°	934.7	952.1	943.4	938.4	934.7
125°	1013.0	1028.6	1023.6	1018.0	1016.2
127.5°	1089.6	1108.8	1102.0	1094.5	1089.6
130°	1161.1	1183.4	1180.3	1176.6	1169.8
132.5°	1241.3	1258.7	1260.0	1251.2	1246.3
135°	1310.3	1329.6	1333.3	1331.5	1326.5
137.5°	1387.4	1403.0	1406.1	1404.8	1397.3
140°	1455.2	1470.7	1479.4	1479.4	1472.6
142.5°	1524.9	1540.4	1545.4	1547.3	1540.4
145°	1590.8	1603.2	1613.1	1615.0	1608.2
147.5°	1649.8	1665.4	1672.8	1676.0	1669.2
150°	1710.8	1721.3	1728.2	1733.8	1728.2
152.5°	1764.9	1775.5	1784.2	1791.0	1784.2
155°	1819.0	1824.0	1829.6	1838.3	1832.7
157.5°	1865.6	1869.4	1872.5	1884.9	1876.2
160°	1907.3	1911.1	1912.9	1923.5	1916.0
162.5°	1945.9	1945.9	1947.7	1959.6	1950.8
165°	1978.8	1976.9	1976.9	1989.4	1980.7
167.5°	2008.7	2003.1	2003.1	2015.5	2006.8
170°	2031.1	2026.1	2024.2	2036.7	2026.1
172.5°	2046.6	2041.7	2039.8	2052.2	2041.7
175°	2059.0	2054.1	2050.3	2062.8	2052.2
177.5°	2065.9	2060.9	2057.2	2067.8	2057.2
180°	2062.8	2062.8	2062.8	2062.8	2062.8

TEST NUMBER: P916776

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.94	12.85	12.84	13.78	14.96	11.50	12.41	12.40	13.34	14.52
	3H	13.59	14.42	14.51	15.35	16.56	13.11	13.93	14.03	14.87	16.08
	4H	14.18	14.96	15.11	15.90	17.12	13.70	14.47	14.63	15.41	16.63
	6H	14.58	15.29	15.52	16.24	17.47	14.09	14.81	15.03	15.75	16.98
	8H	14.68	15.36	15.63	16.33	17.56	14.19	14.87	15.14	15.84	17.07
	12H	14.73	15.38	15.69	16.34	17.59	14.23	14.88	15.19	15.84	17.10
4H	2H	12.40	13.18	13.34	14.12	15.34	12.05	12.83	12.99	13.77	14.99
	3H	14.26	14.91	15.21	15.88	17.12	13.86	14.51	14.81	15.48	16.72
	4H	14.98	15.57	15.93	16.53	17.79	14.56	15.15	15.52	16.12	17.38
	6H	15.49	16.00	16.46	16.99	18.25	15.07	15.58	16.04	16.56	17.82
	8H	15.64	16.11	16.61	17.09	18.37	15.21	15.69	16.18	16.67	17.94
	12H	15.71	16.14	16.70	17.14	18.42	15.27	15.70	16.26	16.70	17.98
8H	4H	15.17	15.65	16.15	16.63	17.90	14.80	15.28	15.78	16.26	17.53
	6H	15.80	16.19	16.80	17.22	18.49	15.42	15.82	16.42	16.84	18.11
	8H	16.02	16.36	17.02	17.38	18.66	15.63	15.98	16.64	16.99	18.28
	12H	16.15	16.45	17.16	17.46	18.79	15.75	16.05	16.76	17.06	18.39
12H	4H	15.16	15.59	16.15	16.59	17.87	14.80	15.23	15.79	16.23	17.51
	6H	15.83	16.18	16.83	17.19	18.48	15.46	15.81	16.47	16.82	18.11
	8H	16.07	16.37	17.08	17.38	18.71	15.70	16.00	16.71	17.01	18.34