

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919343

Luminaire Tested: DFN2DIP-PN3F0-030D090US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919343
REPORT IS A COMBINATION OF REPORTS P901116 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D090US935-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9867.0 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 95.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919343

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919343

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26			19
2	84	77	71	66	74	68	64	60	52	49	47	38	36	34	24	23	22			16
3	76	68	61	55	68	60	55	50	46	43	39	34	31	29	22	20	19			14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17			12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15			11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13			10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12			9
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	10			8
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9			7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1248	1248	1248
5°	1249	1227	1235
10°	1236	1202	1195
15°	1218	1162	1132
20°	1195	1106	1055
25°	1171	1044	981
30°	1140	980	888
35°	1108	912	805
40°	1077	841	711
45°	1040	763	626
50°	1002	684	542
55°	962	600	462
60°	916	512	380
65°	862	423	341
70°	798	339	308
75°	717	297	279
80°	600	247	240
85°	407	160	177

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1764 cd/sqm

TEST NUMBER: P919343

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	1.0
10°-20°	274.7	2.8
20°-30°	385.6	3.9
30°-40°	420.3	4.3
40°-50°	386.3	3.9
50°-60°	303.4	3.1
60°-70°	197.5	2.0
70°-80°	101.7	1.0
80°-90°	30.6	0.3
90°-100°	86.2	0.9
100°-110°	321.5	3.3
110°-120°	852.6	8.6
120°-130°	1414.1	14.3
130°-140°	1502.1	15.2
140°-150°	1396.0	14.1
150°-160°	1122.4	11.4
160°-170°	723.2	7.3
170°-180°	248.9	2.5
0°-30°	760.3	7.7
0°-40°	1180.7	12.0
0°-60°	1870.4	19.0
0°-90°	2200.1	22.3
90°-120°	1260.3	12.8
90°-150°	5572.4	56.5
90°-180°	7667.0	77.7
0°-180°	9867.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1068	1063	1050	1059	1056	101
15°	1015	1005	972	954	944	286
25°	922	891	827	787	773	424
35°	794	745	660	599	578	497
45°	649	584	483	414	391	501
55°	494	418	314	256	238	441
65°	333	255	168	135	132	330
75°	178	110	77	70	70	188
85°	42	21	18	18	18	48
90°	2	23	38	47	51	9
95°	123	60	74	83	81	146
105°	575	632	116	136	144	615
115°	1088	1120	1168	291	155	1071
125°	1538	1563	1599	1612	1618	1372
135°	1904	1934	1951	1970	1966	1471
145°	2208	2206	2239	2252	2242	1381
155°	2432	2415	2437	2449	2434	1121
165°	2562	2551	2557	2570	2557	724
175°	2621	2608	2611	2625	2606	249
180°	2615	2615	2615	2615	2615	

TEST NUMBER: P919343

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.6	1067.6	1067.6	1067.6	1067.6
2.5°	1072.4	1067.6	1056.9	1066.6	1064.7
5°	1067.6	1062.7	1050.2	1058.9	1055.9
7.5°	1058.9	1053.1	1039.6	1043.4	1038.5
10°	1047.2	1040.5	1021.2	1018.2	1012.5
12.5°	1032.8	1024.1	998.0	992.2	981.5
15°	1015.4	1004.7	971.9	953.6	943.9
17.5°	995.1	979.6	939.0	917.8	902.3
20°	971.9	952.5	904.2	880.2	858.8
22.5°	946.8	924.5	868.5	835.7	821.2
25°	921.7	890.7	827.0	787.4	772.8
27.5°	891.7	858.8	788.3	743.0	720.7
30°	859.9	823.1	745.8	696.6	670.5
32.5°	828.9	784.5	705.3	647.3	623.1
35°	794.2	744.8	659.9	599.0	577.7
37.5°	760.3	707.1	617.3	550.6	526.6
40°	724.6	666.7	572.9	504.3	479.2
42.5°	687.9	626.1	528.5	456.9	432.8
45°	649.3	584.4	483.1	414.4	391.2
47.5°	612.5	544.0	439.6	370.9	349.7
50°	572.0	503.3	397.1	330.4	310.1
52.5°	532.3	459.9	356.5	292.7	274.4
55°	493.6	418.3	313.9	256.1	237.7
57.5°	454.1	376.8	276.4	222.2	206.7
60°	413.5	336.2	236.7	187.4	172.0
62.5°	373.9	296.6	202.9	156.5	148.9
65°	333.3	255.0	168.1	135.3	132.3
67.5°	294.7	216.4	135.3	118.8	115.9
70°	254.1	178.7	112.0	102.4	98.5
72.5°	215.4	143.9	93.7	86.0	84.0
75°	177.7	110.1	77.3	70.5	69.6
77.5°	140.1	78.2	60.9	57.0	55.0
80°	105.3	56.1	46.3	42.5	42.5
82.5°	73.4	37.7	31.9	30.0	30.0
85°	41.5	21.2	18.3	18.3	18.3
87.5°	15.5	7.7	7.7	6.8	6.8
90°	1.8	22.7	37.7	47.4	51.0
92.5°	47.4	39.8	45.4	49.2	51.0
95°	123.0	60.4	73.7	83.3	81.4
97.5°	221.4	66.3	96.4	102.2	104.0
100°	335.0	75.8	107.9	123.0	126.7
102.5°	459.8	456.2	111.7	132.3	138.2
105°	575.2	632.1	115.5	136.2	143.8
107.5°	709.6	756.8	119.3	140.0	147.7
110°	838.4	878.0	331.2	142.0	149.5

TEST NUMBER: P919343

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	959.5	993.4	961.3	145.6	151.4
115°	1088.0	1120.2	1167.6	291.4	155.2
117.5°	1199.7	1237.5	1269.8	999.1	503.3
120°	1324.6	1353.0	1387.2	1409.8	1154.3
122.5°	1430.5	1460.9	1498.8	1510.0	1512.1
125°	1538.3	1563.1	1599.0	1612.3	1617.9
127.5°	1636.8	1663.3	1691.9	1710.7	1712.5
130°	1729.6	1760.0	1780.6	1801.5	1799.7
132.5°	1824.2	1848.9	1869.6	1886.7	1884.9
135°	1903.8	1934.1	1950.9	1970.0	1966.3
137.5°	1986.9	2009.6	2028.7	2047.5	2041.9
140°	2068.2	2083.5	2104.2	2121.2	2111.9
142.5°	2136.6	2149.8	2174.3	2189.3	2180.0
145°	2208.5	2206.4	2238.6	2251.9	2242.4
147.5°	2270.7	2265.1	2297.2	2306.7	2299.2
150°	2331.4	2318.2	2348.5	2359.7	2350.3
152.5°	2382.4	2367.3	2395.6	2407.1	2393.8
155°	2431.6	2414.8	2437.4	2448.7	2433.6
157.5°	2471.4	2456.3	2473.4	2486.6	2471.4
160°	2505.5	2494.1	2505.5	2516.8	2503.5
162.5°	2535.6	2524.4	2533.8	2547.1	2530.0
165°	2562.2	2550.9	2556.6	2569.8	2556.6
167.5°	2583.1	2571.6	2577.4	2590.7	2573.6
170°	2600.1	2588.7	2592.5	2605.7	2588.7
172.5°	2611.4	2600.1	2603.9	2617.2	2600.1
175°	2620.8	2607.5	2611.4	2624.6	2605.7
177.5°	2624.6	2611.4	2613.4	2626.6	2609.6
180°	2615.2	2615.2	2615.2	2615.2	2615.2

TEST NUMBER: P919343

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.45	5.10	5.62	6.25	7.87	0.42	1.06	1.59	2.21	3.83
	3H	6.11	6.69	7.28	7.84	9.48	1.59	2.16	2.76	3.32	4.96
	4H	6.71	7.25	7.89	8.41	10.05	2.02	2.57	3.21	3.73	5.37
	6H	7.11	7.62	8.30	8.78	10.43	2.33	2.83	3.52	3.99	5.64
	8H	7.23	7.71	8.42	8.88	10.53	2.41	2.89	3.60	4.07	5.71
	12H	7.28	7.74	8.48	8.91	10.57	2.45	2.90	3.64	4.07	5.73
4H	2H	4.45	4.99	5.64	6.15	7.79	0.99	1.54	2.18	2.69	4.33
	3H	6.25	6.71	7.45	7.89	9.54	2.31	2.77	3.51	3.95	5.60
	4H	6.93	7.35	8.13	8.52	10.19	2.85	3.27	4.04	4.44	6.11
	6H	7.43	7.79	8.63	8.98	10.64	3.25	3.61	4.45	4.80	6.46
	8H	7.60	7.93	8.80	9.12	10.79	3.37	3.71	4.57	4.89	6.57
	12H	7.68	7.99	8.89	9.18	10.86	3.43	3.73	4.64	4.93	6.60
8H	4H	6.88	7.22	8.08	8.40	10.08	3.11	3.45	4.31	4.63	6.31
	6H	7.44	7.71	8.65	8.94	10.61	3.61	3.89	4.83	5.12	6.79
	8H	7.65	7.89	8.87	9.09	10.78	3.80	4.04	5.02	5.24	6.94
	12H	7.77	7.98	9.00	9.19	10.91	3.91	4.12	5.13	5.32	7.04
12H	4H	6.83	7.13	8.04	8.33	10.01	3.11	3.41	4.32	4.61	6.29
	6H	7.41	7.65	8.63	8.85	10.55	3.66	3.90	4.88	5.11	6.80
	8H	7.62	7.83	8.84	9.03	10.75	3.86	4.07	5.08	5.27	6.99