

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924672

Luminaire Tested: DFN2DIP-PN2F0-020D020US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924672
REPORT IS A COMBINATION OF REPORTS P899461 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D020US950-FLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3577.5 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924672
CATALOG NUMBER: DFN2DIP-PN2F0-020D020US950-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P924672

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1608	1608	1608
5°	1608	1582	1594
10°	1592	1557	1570
15°	1566	1528	1534
20°	1532	1489	1497
25°	1498	1443	1455
30°	1456	1400	1402
35°	1416	1350	1346
40°	1367	1299	1292
45°	1318	1248	1238
50°	1264	1194	1175
55°	1208	1132	1115
60°	1144	1059	1048
65°	1074	982	969
70°	985	889	883
75°	863	777	801
80°	715	636	649
85°	484	402	407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1318 cd/sqm



TEST NUMBER: P924672

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.9	2.0
10°-20°	196.6	5.5
20°-30°	288.9	8.1
30°-40°	335.6	9.4
40°-50°	335.2	9.4
50°-60°	292.2	8.2
60°-70°	216.0	6.0
70°-80°	122.2	3.4
80°-90°	34.0	1.0
90°-100°	37.3	1.0
100°-110°	118.7	3.3
110°-120°	203.0	5.7
120°-130°	267.0	7.5
130°-140°	299.7	8.4
140°-150°	293.9	8.2
150°-160°	246.5	6.9
160°-170°	163.5	4.6
170°-180°	57.1	1.6
0°-30°	555.4	15.5
0°-40°	891.0	24.9
0°-60°	1518.4	42.4
0°-90°	1890.6	52.8
90°-120°	359.0	10.0
90°-150°	1219.7	34.1
90°-180°	1687.0	47.2
0°-180°	3577.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	742	742	742	742	742	
5°	742	740	732	737	736	70
15°	707	702	693	696	692	199
25°	640	634	622	623	622	294
35°	552	545	533	529	525	345
45°	449	444	433	426	423	347
55°	340	336	327	318	315	304
65°	229	225	218	211	208	227
75°	120	119	115	111	112	128
85°	29	28	28	26	25	33
90°	1	7	18	17	17	3
95°	26	32	32	32	32	30
105°	110	111	112	113	113	116
115°	204	207	206	205	204	202
125°	296	301	300	298	297	265
135°	383	389	390	390	388	296
145°	465	469	472	472	470	291
155°	532	534	535	538	536	245
165°	579	578	578	582	580	163
175°	602	601	600	603	600	57
180°	603	603	603	603	603	



TEST NUMBER: P924672

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	742.4	742.4	742.4	742.4	742.4
2.5°	746.7	743.2	735.2	742.4	741.1
5°	742.4	739.6	731.7	737.4	736.0
7.5°	737.4	733.1	725.3	731.1	729.6
10°	729.6	724.7	716.1	721.7	719.6
12.5°	718.8	714.6	706.1	709.6	708.2
15°	706.7	702.5	693.2	696.0	692.5
17.5°	691.7	687.5	678.2	681.7	678.2
20°	675.3	671.0	661.0	663.2	660.4
22.5°	658.9	652.5	643.2	643.2	641.8
25°	639.7	633.9	621.8	623.2	621.8
27.5°	618.2	613.2	604.0	601.9	598.3
30°	596.8	591.1	580.4	578.3	575.4
32.5°	573.9	569.7	558.3	554.0	551.1
35°	551.9	544.7	533.3	529.0	525.4
37.5°	526.9	520.4	509.0	504.0	500.4
40°	501.1	495.4	484.0	477.7	474.7
42.5°	476.1	470.4	459.1	451.9	447.6
45°	449.0	444.1	433.3	425.5	422.6
47.5°	422.6	417.7	406.2	398.3	394.1
50°	394.8	391.2	381.2	371.2	367.7
52.5°	367.7	362.6	353.4	345.5	340.6
55°	339.8	335.5	326.9	318.4	314.8
57.5°	312.0	308.4	299.1	290.6	287.6
60°	284.1	281.3	271.3	263.4	261.3
62.5°	257.0	252.0	244.9	237.7	234.9
65°	229.2	224.9	217.8	211.3	207.8
67.5°	200.6	197.0	190.6	185.6	182.8
70°	174.2	171.3	164.9	159.9	157.1
72.5°	147.1	144.2	140.6	135.7	133.6
75°	119.9	118.6	114.9	110.7	112.1
77.5°	95.7	92.8	91.3	89.2	87.1
80°	71.5	70.7	69.3	67.1	65.6
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.2	28.5	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	0.6	6.6	17.8	16.7	17.3
92.5°	11.3	15.3	15.8	16.4	16.4
95°	26.5	31.7	32.5	32.5	31.7
97.5°	44.2	48.9	50.9	50.9	50.9
100°	64.6	68.8	70.2	70.2	69.6
102.5°	86.1	89.1	91.1	91.7	91.1
105°	109.5	111.0	112.1	113.0	113.0
107.5°	132.8	135.0	135.0	135.4	132.8
110°	155.4	158.3	158.3	158.3	156.8



TEST NUMBER: P924672

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	179.7	182.8	182.3	180.8	179.7
115°	203.8	206.6	205.8	205.2	203.8
117.5°	227.6	231.6	229.1	227.6	226.1
120°	251.6	255.6	251.6	251.6	249.9
122.5°	273.4	278.5	276.0	274.6	273.4
125°	296.3	300.9	299.5	297.8	297.3
127.5°	318.7	324.4	322.4	320.2	318.7
130°	339.6	346.2	345.3	344.2	342.2
132.5°	363.1	368.2	368.5	366.0	364.5
135°	383.3	388.9	390.0	389.5	388.0
137.5°	405.8	410.4	411.4	411.0	408.8
140°	425.7	430.3	432.8	432.8	430.8
142.5°	446.1	450.6	452.1	452.6	450.6
145°	465.4	469.0	471.9	472.4	470.4
147.5°	482.6	487.2	489.4	490.3	488.3
150°	500.5	503.5	505.5	507.1	505.5
152.5°	516.3	519.4	521.9	523.9	521.9
155°	532.1	533.6	535.2	537.8	536.1
157.5°	545.8	546.8	547.8	551.4	548.8
160°	558.0	559.0	559.6	562.7	560.5
162.5°	569.3	569.3	569.7	573.3	570.7
165°	578.9	578.3	578.3	581.9	579.5
167.5°	587.6	585.9	585.9	589.6	587.1
170°	594.2	592.7	592.1	595.8	592.7
172.5°	598.7	597.2	596.7	600.4	597.2
175°	602.4	600.9	599.8	603.4	600.4
177.5°	604.4	602.9	601.8	604.8	601.8
180°	603.4	603.4	603.4	603.4	603.4



TEST NUMBER: P924672
 CATALOG NUMBER: DFN2DIP-PN2F0-020D020US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.06	9.95	10.00	10.90	12.13	8.63	9.51	9.56	10.46	11.69
	3H	10.71	11.50	11.65	12.46	13.71	10.23	11.02	11.17	11.98	13.23
	4H	11.28	12.03	12.24	13.00	14.26	10.80	11.55	11.76	12.52	13.78
	6H	11.67	12.36	12.64	13.33	14.61	11.18	11.88	12.15	12.84	14.12
	8H	11.76	12.43	12.74	13.41	14.68	11.28	11.94	12.25	12.93	14.20
	12H	11.81	12.44	12.79	13.42	14.71	11.31	11.94	12.29	12.92	14.22
4H	2H	9.52	10.27	10.48	11.24	12.50	9.17	9.92	10.13	10.89	12.15
	3H	11.36	11.99	12.34	12.98	14.26	10.96	11.59	11.94	12.59	13.86
	4H	12.06	12.64	13.04	13.62	14.92	11.65	12.22	12.63	13.21	14.51
	6H	12.56	13.06	13.55	14.07	15.36	12.14	12.64	13.13	13.65	14.94
	8H	12.70	13.16	13.70	14.17	15.48	12.28	12.74	13.27	13.74	15.06
	12H	12.77	13.18	13.78	14.20	15.52	12.33	12.75	13.35	13.77	15.09
8H	4H	12.25	12.71	13.25	13.72	15.03	11.88	12.34	12.88	13.35	14.66
	6H	12.86	13.24	13.88	14.29	15.60	12.48	12.87	13.51	13.91	15.22
	8H	13.07	13.40	14.10	14.44	15.76	12.68	13.02	13.71	14.05	15.38
	12H	13.18	13.48	14.22	14.51	15.88	12.79	13.09	13.82	14.11	15.49
12H	4H	12.23	12.65	13.25	13.67	14.99	11.87	12.29	12.89	13.31	14.63
	6H	12.88	13.22	13.91	14.25	15.58	12.52	12.86	13.55	13.89	15.22
	8H	13.11	13.41	14.14	14.43	15.81	12.74	13.04	13.77	14.06	15.44