

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919376

Luminaire Tested: DFN2DIP-PN3F0-050D040US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919376
REPORT IS A COMBINATION OF REPORTS P899529 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-050D040US935-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7309.9 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919376

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919376

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US935-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54
2	91	83	77	72	84	78	72	68	68	64	60	58	55	52	50	47	45
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1958	1958	1958
5°	1960	1929	1943
10°	1943	1902	1916
15°	1913	1869	1874
20°	1874	1825	1831
25°	1834	1771	1782
30°	1785	1721	1719
35°	1738	1663	1653
40°	1680	1604	1590
45°	1623	1544	1525
50°	1560	1482	1450
55°	1494	1410	1381
60°	1420	1324	1302
65°	1338	1235	1209
70°	1234	1127	1109
75°	1091	997	1015
80°	918	832	837
85°	647	550	546

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1623 cd/sqm

TEST NUMBER: P919376

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.2
10°-20°	443.6	6.1
20°-30°	651.9	8.9
30°-40°	757.2	10.4
40°-50°	756.2	10.3
50°-60°	659.4	9.0
60°-70°	487.4	6.7
70°-80°	275.8	3.8
80°-90°	75.9	1.0
90°-100°	67.4	0.9
100°-110°	214.2	2.9
110°-120°	366.5	5.0
120°-130°	482.0	6.6
130°-140°	541.0	7.4
140°-150°	530.5	7.3
150°-160°	445.0	6.1
160°-170°	295.1	4.0
170°-180°	103.2	1.4
0°-30°	1253.2	17.1
0°-40°	2010.3	27.5
0°-60°	3425.9	46.9
0°-90°	4265.0	58.3
90°-120°	648.0	8.9
90°-150°	2201.5	30.1
90°-180°	3045.0	41.7
0°-180°	7309.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1651	1664	1661	159
15°	1595	1585	1564	1570	1562	449
25°	1443	1430	1403	1406	1403	664
35°	1245	1229	1203	1194	1186	778
45°	1013	1002	978	960	954	782
55°	767	757	738	718	710	686
65°	517	507	491	477	469	511
75°	270	267	259	250	253	289
85°	66	64	63	58	56	74
90°	1	12	32	30	31	7
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	



TEST NUMBER: P919376

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US935-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.1	1675.1	1675.1	1675.1	1675.1
2.5°	1684.8	1676.8	1659.1	1675.1	1672.1
5°	1675.1	1668.8	1651.0	1663.8	1660.8
7.5°	1663.8	1654.2	1636.5	1649.5	1646.2
10°	1646.2	1634.9	1615.7	1628.4	1623.7
12.5°	1621.9	1612.4	1593.1	1601.1	1597.8
15°	1594.6	1585.0	1564.0	1570.5	1562.5
17.5°	1560.7	1551.2	1530.2	1538.2	1530.2
20°	1523.7	1514.2	1491.6	1496.3	1490.0
22.5°	1486.8	1472.2	1451.2	1451.2	1447.9
25°	1443.2	1430.4	1403.0	1406.1	1403.0
27.5°	1394.8	1383.5	1362.7	1357.9	1349.9
30°	1346.6	1333.7	1309.6	1304.8	1298.3
32.5°	1295.0	1285.5	1259.6	1249.9	1243.5
35°	1245.1	1229.1	1203.2	1193.5	1185.5
37.5°	1188.7	1174.2	1148.4	1137.1	1129.1
40°	1130.8	1117.8	1092.0	1077.6	1071.2
42.5°	1074.4	1061.4	1035.8	1019.5	1010.0
45°	1013.2	1001.9	977.7	960.1	953.6
47.5°	953.6	942.3	916.5	898.7	889.2
50°	890.7	882.7	860.1	837.6	829.5
52.5°	829.5	818.2	797.4	779.6	768.4
55°	766.8	757.1	737.7	718.4	710.4
57.5°	703.9	695.9	674.9	655.6	649.0
60°	641.0	634.7	612.2	594.3	589.6
62.5°	579.9	568.6	552.5	536.4	529.9
65°	517.1	507.4	491.3	476.8	468.7
67.5°	452.7	444.5	430.2	418.9	412.3
70°	393.0	386.6	372.0	360.8	354.5
72.5°	331.9	325.4	317.4	306.1	301.3
75°	270.5	267.4	259.2	249.7	253.0
77.5°	215.9	209.3	206.1	201.3	196.6
80°	161.2	159.5	156.2	151.4	148.2
82.5°	109.5	109.5	108.0	101.5	101.5
85°	66.0	64.4	62.9	57.9	56.4
87.5°	29.0	25.8	22.6	17.7	16.1
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1

TEST NUMBER: P919376

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2

TEST NUMBER: P919376

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.30	11.24	11.19	12.15	13.29	9.86	10.81	10.75	11.71	12.86
	3H	11.96	12.81	12.86	13.72	14.89	11.48	12.33	12.38	13.24	14.41
	4H	12.55	13.35	13.46	14.27	15.45	12.07	12.87	12.98	13.78	14.96
	6H	12.95	13.69	13.87	14.61	15.81	12.46	13.20	13.38	14.12	15.32
	8H	13.06	13.76	13.98	14.70	15.89	12.57	13.27	13.49	14.21	15.40
	12H	13.10	13.77	14.04	14.71	15.93	12.61	13.28	13.54	14.21	15.43
4H	2H	10.77	11.57	11.69	12.49	13.67	10.42	11.22	11.33	12.14	13.32
	3H	12.64	13.30	13.56	14.25	15.45	12.24	12.90	13.16	13.85	15.05
	4H	13.35	13.96	14.29	14.90	16.12	12.93	13.54	13.87	14.49	15.71
	6H	13.86	14.39	14.81	15.36	16.58	13.44	13.97	14.39	14.93	16.16
	8H	14.01	14.50	14.96	15.46	16.70	13.59	14.08	14.54	15.04	16.27
	12H	14.09	14.53	15.06	15.51	16.75	13.65	14.09	14.62	15.07	16.31
8H	4H	13.55	14.04	14.50	15.00	16.24	13.18	13.67	14.13	14.63	15.87
	6H	14.18	14.58	15.15	15.59	16.82	13.80	14.21	14.78	15.21	16.44
	8H	14.39	14.75	15.38	15.74	17.00	14.01	14.37	15.00	15.36	16.61
	12H	14.52	14.84	15.51	15.83	17.13	14.12	14.44	15.11	15.43	16.73
12H	4H	13.54	13.98	14.51	14.96	16.20	13.18	13.62	14.15	14.60	15.84
	6H	14.20	14.56	15.19	15.56	16.81	13.84	14.20	14.83	15.19	16.44
	8H	14.45	14.76	15.44	15.75	17.05	14.07	14.39	15.06	15.38	16.68

END OF REPORT