

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924712

Luminaire Tested: DFN2DIP-PN2F0-040D020US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924712
REPORT IS A COMBINATION OF REPORTS P899465 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D020US950-FLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5466.4 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 55.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924712

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924712

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US950-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30
7	61	48	40	34	58	46	39	33	42	35	31	38	33	29	34	30	26
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3216	3216	3216
5°	3216	3164	3188
10°	3185	3115	3140
15°	3133	3057	3068
20°	3064	2978	2994
25°	2996	2887	2910
30°	2912	2800	2804
35°	2831	2700	2692
40°	2734	2598	2585
45°	2636	2496	2475
50°	2528	2388	2349
55°	2416	2264	2231
60°	2288	2118	2097
65°	2148	1965	1939
70°	1970	1778	1766
75°	1725	1555	1601
80°	1427	1269	1300
85°	969	802	814

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2636 cd/sqm

TEST NUMBER: P924712

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.8	2.6
10°-20°	393.2	7.2
20°-30°	577.9	10.6
30°-40°	671.2	12.3
40°-50°	670.3	12.3
50°-60°	584.5	10.7
60°-70°	432.1	7.9
70°-80°	244.5	4.5
80°-90°	66.2	1.2
90°-100°	37.3	0.7
100°-110°	118.7	2.2
110°-120°	203.0	3.7
120°-130°	267.0	4.9
130°-140°	299.7	5.5
140°-150°	293.9	5.4
150°-160°	246.5	4.5
160°-170°	163.5	3.0
170°-180°	57.1	1.0
0°-30°	1110.8	20.3
0°-40°	1782.0	32.6
0°-60°	3036.8	55.6
0°-90°	3779.5	69.1
90°-120°	359.0	6.6
90°-150°	1219.7	22.3
90°-180°	1687.0	30.9
0°-180°	5466.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	1	7	18	17	17	5
95°	26	32	32	32	32	30
105°	110	111	112	113	113	116
115°	204	207	206	205	204	202
125°	296	301	300	298	297	265
135°	383	389	390	390	388	296
145°	465	469	472	472	470	291
155°	532	534	535	538	536	245
165°	579	578	578	582	580	163
175°	602	601	600	603	600	57
180°	603	603	603	603	603	

TEST NUMBER: P924712

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	0.6	6.6	17.8	16.7	17.3
92.5°	11.3	15.3	15.8	16.4	16.4
95°	26.5	31.7	32.5	32.5	31.7
97.5°	44.2	48.9	50.9	50.9	50.9
100°	64.6	68.8	70.2	70.2	69.6
102.5°	86.1	89.1	91.1	91.7	91.1
105°	109.5	111.0	112.1	113.0	113.0
107.5°	132.8	135.0	135.0	135.4	132.8
110°	155.4	158.3	158.3	158.3	156.8



TEST NUMBER: P924712

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	179.7	182.8	182.3	180.8	179.7
115°	203.8	206.6	205.8	205.2	203.8
117.5°	227.6	231.6	229.1	227.6	226.1
120°	251.6	255.6	251.6	251.6	249.9
122.5°	273.4	278.5	276.0	274.6	273.4
125°	296.3	300.9	299.5	297.8	297.3
127.5°	318.7	324.4	322.4	320.2	318.7
130°	339.6	346.2	345.3	344.2	342.2
132.5°	363.1	368.2	368.5	366.0	364.5
135°	383.3	388.9	390.0	389.5	388.0
137.5°	405.8	410.4	411.4	411.0	408.8
140°	425.7	430.3	432.8	432.8	430.8
142.5°	446.1	450.6	452.1	452.6	450.6
145°	465.4	469.0	471.9	472.4	470.4
147.5°	482.6	487.2	489.4	490.3	488.3
150°	500.5	503.5	505.5	507.1	505.5
152.5°	516.3	519.4	521.9	523.9	521.9
155°	532.1	533.6	535.2	537.8	536.1
157.5°	545.8	546.8	547.8	551.4	548.8
160°	558.0	559.0	559.6	562.7	560.5
162.5°	569.3	569.3	569.7	573.3	570.7
165°	578.9	578.3	578.3	581.9	579.5
167.5°	587.6	585.9	585.9	589.6	587.1
170°	594.2	592.7	592.1	595.8	592.7
172.5°	598.7	597.2	596.7	600.4	597.2
175°	602.4	600.9	599.8	603.4	600.4
177.5°	604.4	602.9	601.8	604.8	601.8
180°	603.4	603.4	603.4	603.4	603.4

TEST NUMBER: P924712

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.82	13.88	13.59	14.68	15.65	12.38	13.44	13.15	14.24	15.21
	3H	14.47	15.43	15.26	16.23	17.23	13.99	14.95	14.78	15.75	16.75
	4H	15.06	15.96	15.86	16.77	17.78	14.57	15.48	15.38	16.29	17.30
	6H	15.45	16.28	16.27	17.10	18.13	14.96	15.80	15.78	16.62	17.64
	8H	15.55	16.35	16.38	17.19	18.21	15.07	15.86	15.89	16.70	17.72
	12H	15.60	16.36	16.43	17.19	18.24	15.11	15.86	15.94	16.70	17.75
4H	2H	13.29	14.20	14.10	15.01	16.02	12.94	13.84	13.75	14.66	15.67
	3H	15.15	15.91	15.97	16.75	17.78	14.75	15.51	15.57	16.35	17.38
	4H	15.86	16.55	16.69	17.39	18.44	15.44	16.13	16.28	16.98	18.03
	6H	16.37	16.96	17.22	17.83	18.89	15.95	16.54	16.80	17.41	18.47
	8H	16.51	17.07	17.36	17.93	19.00	16.09	16.64	16.94	17.51	18.58
	12H	16.58	17.08	17.46	17.97	19.05	16.15	16.65	17.02	17.54	18.61
8H	4H	16.06	16.62	16.91	17.48	18.55	15.69	16.25	16.55	17.11	18.18
	6H	16.68	17.14	17.56	18.04	19.11	16.30	16.76	17.18	17.67	18.74
	8H	16.88	17.29	17.78	18.19	19.28	16.50	16.91	17.40	17.81	18.90
	12H	17.01	17.37	17.91	18.27	19.41	16.62	16.98	17.51	17.87	19.01
12H	4H	16.05	16.55	16.93	17.44	18.52	15.69	16.19	16.57	17.08	18.15
	6H	16.70	17.11	17.59	18.01	19.10	16.34	16.75	17.23	17.65	18.74
	8H	16.94	17.30	17.83	18.19	19.33	16.57	16.93	17.46	17.82	18.96