

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919419

Luminaire Tested: DFN2DIP-PN3F0-060D070US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919419
REPORT IS A COMBINATION OF REPORTS P901094 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-060D070US935-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10357.8 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 111.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919419

CATALOG NUMBER: DFN2DIP-PN3F0-060D070US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919419

CATALOG NUMBER: DFN2DIP-PN3F0-060D070US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	89	85	88	85	81	79	70	68	66	56	55	54	44	43	42
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	32	29	27
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	29	26	24
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	27	24	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16
10	47	35	28	24	43	33	26	22	28	23	20	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2496	2496	2496
5°	2498	2454	2471
10°	2472	2405	2389
15°	2437	2323	2264
20°	2390	2212	2111
25°	2343	2088	1963
30°	2279	1961	1775
35°	2217	1824	1611
40°	2153	1683	1422
45°	2080	1526	1251
50°	2004	1368	1084
55°	1924	1200	924
60°	1832	1024	760
65°	1725	845	683
70°	1596	679	616
75°	1434	594	558
80°	1199	493	481
85°	814	321	355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2080 cd/sqm

TEST NUMBER: P919419

CATALOG NUMBER: DFN2DIP-PN3F0-060D070US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	1.9
10°-20°	549.3	5.3
20°-30°	771.2	7.4
30°-40°	840.7	8.1
40°-50°	772.7	7.5
50°-60°	606.8	5.9
60°-70°	395.0	3.8
70°-80°	203.3	2.0
80°-90°	55.5	0.5
90°-100°	67.1	0.6
100°-110°	250.0	2.4
110°-120°	663.1	6.4
120°-130°	1099.8	10.6
130°-140°	1168.3	11.3
140°-150°	1085.8	10.5
150°-160°	872.9	8.4
160°-170°	562.5	5.4
170°-180°	193.6	1.9
0°-30°	1520.7	14.7
0°-40°	2361.4	22.8
0°-60°	3740.9	36.1
0°-90°	4394.7	42.4
90°-120°	980.2	9.5
90°-150°	4334.1	41.8
90°-180°	5963.0	57.6
0°-180°	10357.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	1	18	29	37	40	10
95°	96	47	57	65	63	113
105°	448	492	90	106	112	478
115°	846	871	908	227	121	833
125°	1196	1216	1244	1254	1258	1067
135°	1481	1504	1517	1532	1529	1144
145°	1718	1716	1741	1751	1744	1074
155°	1891	1878	1896	1904	1893	872
165°	1993	1984	1988	1999	1988	563
175°	2038	2028	2031	2041	2027	194
180°	2034	2034	2034	2034	2034	

TEST NUMBER: P919419

CATALOG NUMBER: DFN2DIP-PN3F0-060D070US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	1.4	17.7	29.4	36.9	39.7
92.5°	36.9	30.9	35.3	38.3	39.7
95°	95.6	47.0	57.3	64.8	63.3
97.5°	172.1	51.6	75.0	79.6	80.9
100°	260.6	58.9	83.9	95.6	98.6
102.5°	357.6	354.8	86.9	103.0	107.5
105°	447.5	491.6	89.8	105.9	111.8
107.5°	551.9	588.7	92.8	108.9	114.9
110°	652.1	682.9	257.6	110.5	116.2

TEST NUMBER: P919419

CATALOG NUMBER: DFN2DIP-PN3F0-060D070US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	746.3	772.7	747.7	113.2	117.8
115°	846.3	871.2	908.1	226.7	120.8
117.5°	933.1	962.5	987.7	777.1	391.5
120°	1030.3	1052.3	1078.9	1096.6	897.8
122.5°	1112.6	1136.2	1165.8	1174.5	1176.0
125°	1196.5	1215.7	1243.7	1254.0	1258.3
127.5°	1273.1	1293.6	1315.9	1330.6	1332.0
130°	1345.2	1368.8	1384.9	1401.2	1399.8
132.5°	1418.8	1438.0	1454.1	1467.4	1466.0
135°	1480.7	1504.2	1517.4	1532.2	1529.3
137.5°	1545.3	1563.1	1577.9	1592.6	1588.2
140°	1608.6	1620.5	1636.6	1649.8	1642.5
142.5°	1661.7	1672.1	1691.1	1702.8	1695.5
145°	1717.7	1716.1	1741.1	1751.4	1744.1
147.5°	1766.1	1761.8	1786.7	1794.1	1788.3
150°	1813.3	1803.0	1826.6	1835.3	1828.0
152.5°	1853.0	1841.2	1863.3	1872.2	1861.9
155°	1891.3	1878.1	1895.7	1904.5	1892.8
157.5°	1922.2	1910.5	1923.7	1934.1	1922.2
160°	1948.8	1939.8	1948.8	1957.5	1947.1
162.5°	1972.2	1963.4	1970.7	1981.1	1967.8
165°	1992.8	1984.1	1988.4	1998.7	1988.4
167.5°	2009.1	2000.1	2004.7	2015.0	2001.7
170°	2022.3	2013.4	2016.4	2026.7	2013.4
172.5°	2031.1	2022.3	2025.3	2035.6	2022.3
175°	2038.4	2028.1	2031.1	2041.3	2026.7
177.5°	2041.3	2031.1	2032.6	2043.0	2029.6
180°	2034.0	2034.0	2034.0	2034.0	2034.0

TEST NUMBER: P919419

CATALOG NUMBER: DFN2DIP-PN3F0-060D070US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.54	10.31	10.56	11.34	12.71	5.50	6.27	6.53	7.30	8.68
	3H	11.20	11.89	12.24	12.93	14.33	6.68	7.37	7.72	8.41	9.81
	4H	11.80	12.46	12.85	13.50	14.90	7.12	7.78	8.17	8.82	10.22
	6H	12.22	12.82	13.28	13.86	15.28	7.44	8.04	8.49	9.08	10.50
	8H	12.34	12.91	13.40	13.97	15.38	7.52	8.09	8.58	9.15	10.57
	12H	12.40	12.94	13.46	13.99	15.43	7.56	8.10	8.63	9.16	10.59
4H	2H	9.54	10.20	10.60	11.24	12.64	6.09	6.74	7.14	7.78	9.19
	3H	11.36	11.91	12.42	12.97	14.39	7.42	7.97	8.49	9.04	10.45
	4H	12.05	12.54	13.11	13.60	15.04	7.97	8.46	9.03	9.52	10.96
	6H	12.55	12.98	13.63	14.06	15.50	8.38	8.80	9.45	9.88	11.32
	8H	12.72	13.12	13.80	14.20	15.65	8.50	8.90	9.58	9.97	11.42
	12H	12.81	13.17	13.91	14.26	15.72	8.56	8.92	9.65	10.01	11.46
8H	4H	12.01	12.41	13.09	13.48	14.93	8.24	8.64	9.31	9.71	11.16
	6H	12.57	12.89	13.67	14.01	15.46	8.75	9.07	9.85	10.19	11.64
	8H	12.78	13.07	13.88	14.17	15.63	8.93	9.22	10.04	10.32	11.79
	12H	12.91	13.16	14.02	14.26	15.76	9.04	9.30	10.15	10.39	11.90
12H	4H	11.96	12.32	13.05	13.41	14.86	8.24	8.60	9.33	9.69	11.14
	6H	12.54	12.83	13.65	13.93	15.40	8.79	9.08	9.90	10.18	11.65
	8H	12.75	13.01	13.86	14.10	15.61	9.00	9.25	10.10	10.34	11.85

END OF REPORT