

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919438

Luminaire Tested: DFN2DIP-PN3F0-070D050US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919438
REPORT IS A COMBINATION OF REPORTS P899548 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D050US935-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8932.8 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 107.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919438
CATALOG NUMBER: DFN2DIP-PN3F0-070D050US935-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P919438
 CATALOG NUMBER: DFN2DIP-PN3F0-070D050US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57	57
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54	49	49	49	49
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42	42	42	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36	36	36	36
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32	32	32	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28	28	28	28
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25	25	25	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22	22	22	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18	18	18	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2912	2912	2912
5°	2915	2864	2883
10°	2884	2805	2788
15°	2843	2711	2642
20°	2789	2581	2463
25°	2733	2436	2290
30°	2659	2287	2071
35°	2586	2128	1879
40°	2512	1963	1659
45°	2426	1780	1460
50°	2337	1596	1265
55°	2244	1400	1078
60°	2137	1195	886
65°	2012	986	796
70°	1862	792	719
75°	1672	694	651
80°	1398	576	561
85°	951	374	414

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2426 cd/sqm



TEST NUMBER: P919438

CATALOG NUMBER: DFN2DIP-PN3F0-070D050US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	2.6
10°-20°	640.9	7.2
20°-30°	899.8	10.1
30°-40°	980.8	11.0
40°-50°	901.5	10.1
50°-60°	708.0	7.9
60°-70°	460.8	5.2
70°-80°	237.2	2.7
80°-90°	64.4	0.7
90°-100°	84.2	0.9
100°-110°	267.7	3.0
110°-120°	458.1	5.1
120°-130°	602.5	6.7
130°-140°	676.3	7.6
140°-150°	663.1	7.4
150°-160°	556.3	6.2
160°-170°	368.9	4.1
170°-180°	128.9	1.4
0°-30°	1774.1	19.9
0°-40°	2754.9	30.8
0°-60°	4364.3	48.9
0°-90°	5126.8	57.4
90°-120°	810.0	9.1
90°-150°	2751.9	30.8
90°-180°	3806.0	42.6
0°-180°	8932.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	1	15	40	38	39	9
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	



TEST NUMBER: P919438

CATALOG NUMBER: DFN2DIP-PN3F0-070D050US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8



TEST NUMBER: P919438

CATALOG NUMBER: DFN2DIP-PN3F0-070D050US935-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5



TEST NUMBER: P919438
 CATALOG NUMBER: DFN2DIP-PN3F0-070D050US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.48	12.38	12.38	13.29	14.46	7.45	8.34	8.35	9.26	10.42
	3H	13.16	13.96	14.07	14.88	16.07	8.64	9.44	9.55	10.36	11.55
	4H	13.77	14.52	14.69	15.45	16.65	9.09	9.84	10.01	10.77	11.97
	6H	14.19	14.88	15.12	15.82	17.03	9.41	10.10	10.34	11.04	12.25
	8H	14.31	14.97	15.26	15.93	17.14	9.50	10.16	10.44	11.11	12.32
	12H	14.37	15.00	15.32	15.95	17.18	9.54	10.17	10.49	11.11	12.35
4H	2H	11.51	12.26	12.44	13.19	14.39	8.05	8.81	8.98	9.73	10.93
	3H	13.34	13.96	14.28	14.92	16.14	9.40	10.03	10.34	10.99	12.20
	4H	14.03	14.60	14.98	15.55	16.79	9.94	10.52	10.90	11.47	12.71
	6H	14.54	15.03	15.50	16.01	17.25	10.36	10.85	11.32	11.83	13.07
	8H	14.71	15.17	15.68	16.14	17.39	10.49	10.95	11.45	11.92	13.17
	12H	14.81	15.22	15.79	16.21	17.47	10.55	10.97	11.54	11.95	13.21
8H	4H	14.00	14.46	14.96	15.43	16.68	10.23	10.69	11.19	11.66	12.91
	6H	14.56	14.94	15.55	15.95	17.20	10.74	11.12	11.73	12.13	13.38
	8H	14.77	15.11	15.77	16.11	17.38	10.93	11.26	11.92	12.26	13.53
	12H	14.91	15.20	15.91	16.20	17.51	11.04	11.34	12.04	12.33	13.65
12H	4H	13.95	14.37	14.94	15.35	16.61	10.23	10.65	11.22	11.63	12.89
	6H	14.53	14.87	15.53	15.87	17.14	10.79	11.12	11.79	12.12	13.39
	8H	14.75	15.05	15.76	16.04	17.36	10.99	11.29	12.00	12.28	13.60