

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919442

Luminaire Tested: DFN2DIP-PN3F0-070D060US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919442
REPORT IS A COMBINATION OF REPORTS P899562 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D060US935-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9694.8 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 115.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919442
CATALOG NUMBER: DFN2DIP-PN3F0-070D060US935-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P919442

CATALOG NUMBER: DFN2DIP-PN3F0-070D060US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	43	47	45	43	39
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	34	31	29	34	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	31	28	26	31	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2912	2912	2912
5°	2915	2864	2883
10°	2884	2805	2788
15°	2843	2711	2642
20°	2789	2581	2463
25°	2733	2436	2290
30°	2659	2287	2071
35°	2586	2128	1879
40°	2512	1963	1659
45°	2426	1780	1460
50°	2337	1596	1265
55°	2244	1400	1078
60°	2137	1195	886
65°	2012	986	796
70°	1862	792	719
75°	1672	694	651
80°	1398	576	561
85°	951	374	414

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2426 cd/sqm



TEST NUMBER: P919442

CATALOG NUMBER: DFN2DIP-PN3F0-070D060US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	2.4
10°-20°	640.9	6.6
20°-30°	899.8	9.3
30°-40°	980.8	10.1
40°-50°	901.5	9.3
50°-60°	708.0	7.3
60°-70°	460.8	4.8
70°-80°	237.2	2.4
80°-90°	65.2	0.7
90°-100°	101.1	1.0
100°-110°	321.2	3.3
110°-120°	549.7	5.7
120°-130°	723.0	7.5
130°-140°	811.5	8.4
140°-150°	795.8	8.2
150°-160°	667.5	6.9
160°-170°	442.7	4.6
170°-180°	154.7	1.6
0°-30°	1774.1	18.3
0°-40°	2754.9	28.4
0°-60°	4364.3	45.0
0°-90°	5127.5	52.9
90°-120°	972.0	10.0
90°-150°	3302.3	34.1
90°-180°	4567.0	47.1
0°-180°	9694.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	2	18	48	45	47	10
95°	72	86	88	88	86	80
105°	296	300	303	306	306	313
115°	552	560	557	556	552	546
125°	802	815	811	806	805	717
135°	1038	1053	1056	1055	1051	802
145°	1260	1270	1278	1279	1274	787
155°	1441	1445	1449	1456	1452	663
165°	1567	1566	1566	1576	1569	442
175°	1631	1627	1624	1634	1625	155
180°	1634	1634	1634	1634	1634	



TEST NUMBER: P919442

CATALOG NUMBER: DFN2DIP-PN3F0-070D060US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	1.5	17.7	48.3	45.3	46.8
92.5°	30.6	41.4	42.9	44.3	44.3
95°	71.9	85.7	88.2	88.2	85.7
97.5°	119.7	132.5	137.9	137.9	137.9
100°	174.9	186.1	190.1	190.1	188.6
102.5°	233.0	241.3	246.8	248.2	246.8
105°	296.5	300.5	303.4	305.9	305.9
107.5°	359.6	365.5	365.5	366.4	359.6
110°	420.7	428.5	428.5	428.5	424.6



TEST NUMBER: P919442

CATALOG NUMBER: DFN2DIP-PN3F0-070D060US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.6	495.0	493.5	489.6	486.6
115°	551.6	559.6	557.1	555.6	551.6
117.5°	616.2	627.1	620.1	616.2	612.3
120°	681.2	692.1	681.2	681.2	676.7
122.5°	740.3	754.1	747.2	743.3	740.3
125°	802.4	814.7	810.7	806.3	804.9
127.5°	863.0	878.2	872.8	866.9	863.0
130°	919.6	937.4	934.9	931.9	926.5
132.5°	983.2	996.9	997.9	991.0	987.0
135°	1037.8	1053.1	1056.0	1054.6	1050.6
137.5°	1098.9	1111.2	1113.7	1112.7	1106.8
140°	1152.6	1164.9	1171.8	1171.8	1166.4
142.5°	1207.7	1220.0	1224.0	1225.5	1220.0
145°	1260.0	1269.8	1277.7	1279.2	1273.8
147.5°	1306.7	1319.0	1325.0	1327.4	1322.0
150°	1355.0	1363.4	1368.8	1373.2	1368.8
152.5°	1397.8	1406.3	1413.2	1418.6	1413.2
155°	1440.7	1444.7	1449.1	1456.0	1451.6
157.5°	1477.6	1480.7	1483.1	1493.0	1486.1
160°	1510.7	1513.6	1515.1	1523.4	1517.6
162.5°	1541.2	1541.2	1542.6	1552.0	1545.1
165°	1567.3	1565.8	1565.8	1575.7	1568.8
167.5°	1591.0	1586.6	1586.6	1596.4	1589.5
170°	1608.7	1604.7	1603.3	1613.1	1604.7
172.5°	1621.0	1617.0	1615.6	1625.4	1617.0
175°	1630.8	1626.9	1623.9	1633.8	1625.4
177.5°	1636.2	1632.4	1629.4	1637.7	1629.4
180°	1633.8	1633.8	1633.8	1633.8	1633.8



TEST NUMBER: P919442
 CATALOG NUMBER: DFN2DIP-PN3F0-070D060US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.09	11.94	12.03	12.89	14.12	7.05	7.91	7.99	8.86	10.09
	3H	12.76	13.52	13.71	14.48	15.74	8.24	9.00	9.19	9.96	11.22
	4H	13.37	14.09	14.33	15.05	16.32	8.68	9.41	9.65	10.37	11.64
	6H	13.78	14.45	14.76	15.42	16.69	9.00	9.67	9.98	10.64	11.91
	8H	13.91	14.54	14.89	15.53	16.80	9.09	9.72	10.07	10.71	11.98
	12H	13.97	14.57	14.95	15.55	16.85	9.13	9.73	10.12	10.71	12.01
4H	2H	11.11	11.83	12.08	12.79	14.06	7.65	8.37	8.62	9.33	10.60
	3H	12.93	13.53	13.91	14.53	15.80	8.99	9.59	9.97	10.59	11.87
	4H	13.62	14.17	14.61	15.15	16.46	9.54	10.08	10.53	11.07	12.37
	6H	14.13	14.60	15.13	15.61	16.91	9.95	10.42	10.95	11.43	12.73
	8H	14.30	14.74	15.30	15.75	17.06	10.08	10.52	11.08	11.52	12.84
	12H	14.39	14.79	15.41	15.81	17.13	10.14	10.54	11.16	11.56	12.88
8H	4H	13.59	14.03	14.59	15.03	16.35	9.82	10.25	10.82	11.26	12.57
	6H	14.15	14.51	15.17	15.56	16.87	10.33	10.69	11.35	11.74	13.05
	8H	14.36	14.68	15.39	15.71	17.04	10.51	10.83	11.55	11.87	13.20
	12H	14.49	14.78	15.53	15.80	17.18	10.63	10.91	11.66	11.94	13.31
12H	4H	13.54	13.94	14.56	14.96	16.28	9.82	10.22	10.84	11.24	12.56
	6H	14.12	14.44	15.16	15.47	16.81	10.37	10.69	11.41	11.73	13.06
	8H	14.34	14.62	15.38	15.65	17.02	10.58	10.86	11.62	11.89	13.26