

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919451

Luminaire Tested: DFN2DIP-PN3F0-070D080US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919451
REPORT IS A COMBINATION OF REPORTS P901110 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D080US935-RLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11942.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 130.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919451
CATALOG NUMBER: DFN2DIP-PN3F0-070D080US935-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P919451
 CATALOG NUMBER: DFN2DIP-PN3F0-070D080US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	50	50	50	43
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	44	43	44	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	36	33	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	29	26	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22	26	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	24	21	19	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	22	20	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2912	2912	2912
5°	2915	2864	2883
10°	2884	2805	2788
15°	2843	2711	2642
20°	2789	2581	2463
25°	2733	2436	2290
30°	2659	2287	2071
35°	2586	2128	1879
40°	2512	1963	1659
45°	2426	1780	1460
50°	2337	1596	1265
55°	2244	1400	1078
60°	2137	1195	886
65°	2012	986	796
70°	1862	792	719
75°	1672	694	651
80°	1398	576	561
85°	951	374	414

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2426 cd/sqm



TEST NUMBER: P919451

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	2.0
10°-20°	640.9	5.4
20°-30°	899.8	7.5
30°-40°	980.8	8.2
40°-50°	901.5	7.5
50°-60°	708.0	5.9
60°-70°	460.8	3.9
70°-80°	237.2	2.0
80°-90°	64.6	0.5
90°-100°	76.7	0.6
100°-110°	285.7	2.4
110°-120°	757.9	6.3
120°-130°	1256.9	10.5
130°-140°	1335.2	11.2
140°-150°	1240.9	10.4
150°-160°	997.6	8.4
160°-170°	642.8	5.4
170°-180°	221.3	1.9
0°-30°	1774.1	14.9
0°-40°	2754.9	23.1
0°-60°	4364.3	36.5
0°-90°	5127.0	42.9
90°-120°	1120.2	9.4
90°-150°	4953.3	41.5
90°-180°	6815.0	57.1
0°-180°	11942.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	2	20	34	42	45	11
95°	109	54	66	74	72	129
105°	511	562	103	121	128	546
115°	967	996	1038	259	138	952
125°	1367	1389	1421	1433	1438	1220
135°	1692	1719	1734	1751	1748	1307
145°	1963	1961	1990	2002	1993	1228
155°	2161	2146	2167	2177	2163	996
165°	2278	2268	2272	2284	2272	643
175°	2330	2318	2321	2333	2316	222
180°	2325	2325	2325	2325	2325	



TEST NUMBER: P919451
 CATALOG NUMBER: DFN2DIP-PN3F0-070D080US935-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	1.6	20.1	33.6	42.1	45.4
92.5°	42.1	35.4	40.4	43.7	45.4
95°	109.3	53.7	65.5	74.1	72.3
97.5°	196.7	58.9	85.7	90.9	92.5
100°	297.8	67.3	95.9	109.3	112.6
102.5°	408.7	405.4	99.3	117.6	122.9
105°	511.3	561.9	102.6	121.1	127.9
107.5°	630.8	672.7	106.1	124.4	131.2
110°	745.3	780.4	294.5	126.2	132.9



TEST NUMBER: P919451
 CATALOG NUMBER: DFN2DIP-PN3F0-070D080US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	852.9	883.0	854.5	129.4	134.7
115°	967.2	995.7	1037.8	259.1	138.0
117.5°	1066.4	1100.0	1128.8	888.0	447.5
120°	1177.5	1202.6	1233.0	1253.2	1026.1
122.5°	1271.5	1298.6	1332.3	1342.3	1344.1
125°	1367.4	1389.4	1421.3	1433.1	1438.1
127.5°	1454.9	1478.5	1503.9	1520.6	1522.2
130°	1537.4	1564.3	1582.8	1601.4	1599.7
132.5°	1621.5	1643.5	1661.9	1677.1	1675.4
135°	1692.2	1719.2	1734.1	1751.2	1747.7
137.5°	1766.2	1786.3	1803.3	1820.1	1815.1
140°	1838.4	1852.0	1870.4	1885.6	1877.1
142.5°	1899.2	1910.9	1932.7	1946.1	1937.7
145°	1963.1	1961.3	1989.9	2001.6	1993.2
147.5°	2018.4	2013.4	2041.9	2050.4	2043.8
150°	2072.3	2060.5	2087.5	2097.5	2089.1
152.5°	2117.7	2104.3	2129.4	2139.7	2127.9
155°	2161.4	2146.5	2166.6	2176.6	2163.3
157.5°	2196.7	2183.4	2198.6	2210.4	2196.7
160°	2227.1	2217.0	2227.1	2237.1	2225.3
162.5°	2253.9	2243.9	2252.3	2264.1	2248.9
165°	2277.5	2267.5	2272.5	2284.2	2272.5
167.5°	2296.0	2285.9	2291.0	2302.8	2287.7
170°	2311.3	2301.0	2304.5	2316.3	2301.0
172.5°	2321.3	2311.3	2314.6	2326.4	2311.3
175°	2329.6	2317.8	2321.3	2333.0	2316.3
177.5°	2333.0	2321.3	2323.0	2334.8	2319.6
180°	2324.6	2324.6	2324.6	2324.6	2324.6



TEST NUMBER: P919451
 CATALOG NUMBER: DFN2DIP-PN3F0-070D080US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.12	10.90	11.15	11.93	13.30	6.09	6.87	7.11	7.89	9.26
	3H	11.79	12.48	12.82	13.52	14.91	7.27	7.96	8.30	9.00	10.39
	4H	12.39	13.05	13.44	14.09	15.49	7.71	8.37	8.76	9.41	10.80
	6H	12.81	13.41	13.86	14.45	15.86	8.03	8.63	9.08	9.67	11.08
	8H	12.93	13.50	13.99	14.56	15.97	8.11	8.69	9.17	9.74	11.15
	12H	12.99	13.53	14.05	14.58	16.01	8.15	8.70	9.21	9.75	11.18
4H	2H	10.13	10.79	11.18	11.83	13.23	6.68	7.33	7.73	8.37	9.77
	3H	11.95	12.50	13.01	13.56	14.97	8.01	8.56	9.07	9.63	11.04
	4H	12.64	13.14	13.70	14.19	15.63	8.55	9.05	9.62	10.11	11.54
	6H	13.14	13.57	14.22	14.65	16.08	8.96	9.39	10.04	10.47	11.90
	8H	13.31	13.71	14.39	14.79	16.23	9.09	9.49	10.16	10.56	12.00
	12H	13.40	13.76	14.49	14.85	16.30	9.15	9.51	10.24	10.60	12.04
8H	4H	12.60	13.00	13.67	14.07	15.51	8.83	9.23	9.90	10.30	11.74
	6H	13.16	13.49	14.25	14.60	16.04	9.34	9.67	10.43	10.78	12.22
	8H	13.37	13.66	14.47	14.75	16.21	9.52	9.81	10.62	10.91	12.37
	12H	13.50	13.75	14.61	14.85	16.35	9.63	9.89	10.74	10.98	12.48
12H	4H	12.55	12.91	13.64	14.00	15.44	8.83	9.19	9.92	10.28	11.72
	6H	13.13	13.42	14.23	14.52	15.98	9.38	9.67	10.49	10.77	12.23
	8H	13.34	13.60	14.45	14.69	16.19	9.59	9.84	10.69	10.93	12.43