

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902972

Luminaire Tested: DFN2DIP-PN3F0-030D090US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902972
REPORT IS A COMBINATION OF REPORTS P899595 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D090US830-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10306.7 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 95.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902972

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902972

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1286	1286	1286
5°	1287	1267	1276
10°	1276	1249	1258
15°	1257	1228	1231
20°	1231	1198	1203
25°	1205	1163	1170
30°	1172	1131	1129
35°	1141	1092	1085
40°	1104	1053	1044
45°	1066	1014	1002
50°	1025	973	953
55°	982	926	907
60°	932	870	855
65°	879	811	794
70°	811	740	728
75°	717	655	667
80°	602	546	550
85°	426	361	358

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2657 cd/sqm

TEST NUMBER: P902972

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.0
10°-20°	291.4	2.8
20°-30°	428.2	4.2
30°-40°	497.3	4.8
40°-50°	496.7	4.8
50°-60°	433.1	4.2
60°-70°	320.2	3.1
70°-80°	181.1	1.8
80°-90°	55.4	0.5
90°-100°	166.0	1.6
100°-110°	527.5	5.1
110°-120°	902.7	8.8
120°-130°	1187.2	11.5
130°-140°	1332.5	12.9
140°-150°	1306.7	12.7
150°-160°	1096.1	10.6
160°-170°	726.9	7.1
170°-180°	254.1	2.5
0°-30°	823.1	8.0
0°-40°	1320.4	12.8
0°-60°	2250.3	21.8
0°-90°	2807.0	27.2
90°-120°	1596.2	15.5
90°-150°	5422.6	52.6
90°-180°	7500.0	72.8
0°-180°	10306.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1100	1096	1084	1093	1091	104
15°	1047	1041	1027	1032	1026	295
25°	948	940	922	924	922	436
35°	818	807	790	784	779	511
45°	666	658	642	631	626	514
55°	504	497	485	472	467	450
65°	340	333	323	313	308	336
75°	178	176	170	164	166	190
85°	43	42	41	38	37	48
90°	2	29	79	74	77	10
95°	118	141	145	145	141	131
105°	487	493	498	502	502	514
115°	906	919	915	912	906	896
125°	1318	1338	1331	1324	1322	1177
135°	1704	1729	1734	1732	1725	1317
145°	2069	2085	2098	2100	2092	1293
155°	2366	2372	2380	2391	2384	1089
165°	2574	2571	2571	2587	2576	726
175°	2678	2671	2667	2683	2669	254
180°	2683	2683	2683	2683	2683	

TEST NUMBER: P902972

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1100.2	1100.2	1100.2	1100.2	1100.2
2.5°	1106.6	1101.4	1089.7	1100.2	1098.3
5°	1100.2	1096.1	1084.4	1092.9	1090.8
7.5°	1092.9	1086.6	1074.9	1083.5	1081.3
10°	1081.3	1073.8	1061.2	1069.6	1066.5
12.5°	1065.4	1059.0	1046.4	1051.6	1049.5
15°	1047.4	1041.1	1027.3	1031.5	1026.2
17.5°	1025.1	1018.9	1005.0	1010.3	1005.0
20°	1000.8	994.5	979.7	982.8	978.6
22.5°	976.6	967.0	953.2	953.2	951.0
25°	947.9	939.5	921.5	923.6	921.5
27.5°	916.2	908.7	895.0	891.9	886.6
30°	884.5	876.0	860.2	857.0	852.7
32.5°	850.6	844.3	827.4	821.0	816.7
35°	817.8	807.3	790.3	783.9	778.6
37.5°	780.8	771.3	754.3	746.9	741.6
40°	742.7	734.2	717.3	707.8	703.6
42.5°	705.7	697.2	680.3	669.7	663.4
45°	665.5	658.1	642.2	630.6	626.3
47.5°	626.3	619.0	602.0	590.3	584.0
50°	585.0	579.8	565.0	550.2	544.9
52.5°	544.9	537.4	523.8	512.1	504.6
55°	503.7	497.3	484.6	471.9	466.7
57.5°	462.3	457.0	443.3	430.6	426.3
60°	421.0	416.9	402.1	390.4	387.3
62.5°	380.9	373.4	362.9	352.3	348.1
65°	339.7	333.3	322.7	313.2	307.9
67.5°	297.4	292.0	282.5	275.1	270.9
70°	258.2	253.9	244.4	237.0	232.8
72.5°	218.0	213.7	208.4	201.0	197.9
75°	177.7	175.7	170.3	164.0	166.2
77.5°	141.8	137.5	135.3	132.2	129.1
80°	105.8	104.7	102.5	99.4	97.4
82.5°	71.9	71.9	71.0	66.6	66.6
85°	43.4	42.3	41.3	38.1	37.0
87.5°	19.0	17.0	14.8	11.7	10.6
90°	2.5	29.1	79.3	74.4	76.8
92.5°	50.1	68.0	70.4	72.8	72.8
95°	118.1	140.7	144.8	144.8	140.7
97.5°	196.5	217.5	226.5	226.5	226.5
100°	287.1	305.8	312.2	312.2	309.8
102.5°	382.6	396.3	405.2	407.6	405.2
105°	486.9	493.3	498.2	502.3	502.3
107.5°	590.4	600.1	600.1	601.7	590.4
110°	690.7	703.7	703.7	703.7	697.2

TEST NUMBER: P902972

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	799.1	812.8	810.4	804.0	799.1
115°	905.9	918.8	914.7	912.4	905.9
117.5°	1011.8	1029.6	1018.3	1011.8	1005.3
120°	1118.6	1136.3	1118.6	1118.6	1111.3
122.5°	1215.6	1238.3	1227.0	1220.5	1215.6
125°	1317.6	1337.8	1331.3	1324.0	1321.6
127.5°	1417.0	1442.1	1433.2	1423.5	1417.0
130°	1510.0	1539.2	1535.1	1530.2	1521.4
132.5°	1614.4	1637.0	1638.6	1627.3	1620.9
135°	1704.1	1729.2	1734.1	1731.6	1725.2
137.5°	1804.4	1824.7	1828.7	1827.1	1817.4
140°	1892.6	1912.8	1924.1	1924.1	1915.2
142.5°	1983.2	2003.4	2009.9	2012.3	2003.4
145°	2069.0	2085.1	2098.0	2100.5	2091.6
147.5°	2145.8	2166.0	2175.7	2179.7	2170.9
150°	2225.1	2238.8	2247.7	2254.9	2247.7
152.5°	2295.4	2309.1	2320.4	2329.4	2320.4
155°	2365.8	2372.2	2379.5	2390.9	2383.6
157.5°	2426.4	2431.3	2435.3	2451.5	2440.1
160°	2480.6	2485.5	2487.9	2501.6	2491.9
162.5°	2530.7	2530.7	2533.2	2548.5	2537.2
165°	2573.6	2571.2	2571.2	2587.4	2576.1
167.5°	2612.4	2605.2	2605.2	2621.3	2610.0
170°	2641.6	2635.1	2632.7	2648.8	2635.1
172.5°	2661.7	2655.3	2652.9	2669.1	2655.3
175°	2678.0	2671.4	2666.6	2682.9	2669.1
177.5°	2686.8	2680.4	2675.5	2689.3	2675.5
180°	2682.9	2682.9	2682.9	2682.9	2682.9

TEST NUMBER: P902972

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.50	6.18	6.63	7.31	8.87	5.06	5.75	6.19	6.87	8.43
	3H	7.14	7.75	8.28	8.88	10.46	6.66	7.27	7.79	8.40	9.98
	4H	7.71	8.30	8.86	9.43	11.01	7.23	7.81	8.38	8.95	10.53
	6H	8.10	8.64	9.26	9.77	11.37	7.61	8.15	8.77	9.28	10.88
	8H	8.20	8.71	9.36	9.86	11.45	7.71	8.22	8.87	9.37	10.96
	12H	8.24	8.72	9.40	9.87	11.48	7.74	8.23	8.90	9.37	10.98
4H	2H	5.93	6.52	7.09	7.65	9.23	5.58	6.17	6.74	7.30	8.88
	3H	7.78	8.26	8.94	9.42	11.02	7.37	7.86	8.54	9.02	10.62
	4H	8.48	8.93	9.64	10.07	11.69	8.06	8.51	9.23	9.66	11.27
	6H	8.98	9.36	10.15	10.53	12.14	8.56	8.94	9.72	10.11	11.71
	8H	9.12	9.48	10.29	10.64	12.26	8.69	9.05	9.86	10.21	11.83
	12H	9.18	9.51	10.37	10.68	12.31	8.74	9.07	9.93	10.24	11.87
8H	4H	8.66	9.02	9.82	10.18	11.80	8.29	8.65	9.45	9.81	11.43
	6H	9.27	9.57	10.46	10.77	12.39	8.90	9.19	10.09	10.40	12.01
	8H	9.49	9.75	10.68	10.93	12.56	9.10	9.36	10.30	10.54	12.18
	12H	9.61	9.83	10.80	11.01	12.68	9.21	9.43	10.40	10.61	12.28
12H	4H	8.63	8.96	9.82	10.13	11.76	8.27	8.60	9.45	9.77	11.40
	6H	9.30	9.56	10.49	10.74	12.38	8.94	9.19	10.13	10.37	12.01
	8H	9.53	9.75	10.72	10.93	12.60	9.16	9.38	10.35	10.56	12.23

END OF REPORT