

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919495

Luminaire Tested: DFN2DIP-PN3F0-090D050US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919495
REPORT IS A COMBINATION OF REPORTS P901072 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D050US935-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10848.6 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 130.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919495

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919495

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	97	93	90	94	91	87	84	79	77	75	69	67	65	59	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49
3	85	75	68	62	79	71	65	59	62	58	53	55	51	48	47	45	42
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33
6	66	54	46	41	62	51	44	39	46	40	35	40	36	32	35	32	29
7	61	49	41	36	57	47	39	34	42	36	32	37	32	29	33	29	26
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3744	3744	3744
5°	3748	3682	3706
10°	3708	3607	3584
15°	3655	3485	3396
20°	3585	3318	3166
25°	3514	3132	2944
30°	3419	2941	2663
35°	3325	2736	2416
40°	3230	2524	2133
45°	3120	2289	1877
50°	3005	2052	1627
55°	2886	1800	1386
60°	2747	1536	1140
65°	2588	1268	1024
70°	2394	1018	924
75°	2150	892	837
80°	1798	740	721
85°	1221	481	532

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3120 cd/sqm

TEST NUMBER: P919495

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.2	2.8
10°-20°	824.0	7.6
20°-30°	1156.9	10.7
30°-40°	1261.0	11.6
40°-50°	1159.0	10.7
50°-60°	910.3	8.4
60°-70°	592.5	5.5
70°-80°	305.0	2.8
80°-90°	80.4	0.7
90°-100°	47.9	0.4
100°-110°	178.6	1.6
110°-120°	473.7	4.4
120°-130°	785.6	7.2
130°-140°	834.5	7.7
140°-150°	775.6	7.1
150°-160°	623.5	5.7
160°-170°	401.8	3.7
170°-180°	138.3	1.3
0°-30°	2281.0	21.0
0°-40°	3542.0	32.6
0°-60°	5611.3	51.7
0°-90°	6589.2	60.7
90°-120°	700.2	6.5
90°-150°	3095.8	28.5
90°-180°	4259.0	39.3
0°-180°	10848.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3203	3203	3203	3203	3203	
5°	3203	3188	3150	3176	3168	304
15°	3046	3014	2916	2861	2832	858
25°	2765	2672	2481	2362	2319	1272
35°	2383	2235	1980	1797	1733	1491
45°	1948	1753	1449	1243	1174	1504
55°	1481	1255	942	768	713	1323
65°	1000	765	504	406	397	991
75°	533	330	232	212	209	564
85°	124	64	55	55	55	143
90°	1	13	21	26	28	10
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	

TEST NUMBER: P919495

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3202.7	3202.7	3202.7	3202.7	3202.7
2.5°	3217.1	3202.7	3170.6	3199.9	3194.0
5°	3202.7	3188.2	3150.4	3176.5	3167.9
7.5°	3176.5	3159.3	3118.7	3130.1	3115.6
10°	3141.8	3121.5	3063.7	3054.7	3037.5
12.5°	3098.4	3072.3	2993.9	2976.6	2944.6
15°	3046.1	3014.2	2915.8	2860.7	2831.8
17.5°	2985.3	2938.8	2817.0	2753.4	2707.0
20°	2915.8	2857.7	2712.7	2640.5	2576.5
22.5°	2840.4	2773.7	2605.5	2507.1	2463.7
25°	2765.1	2672.2	2481.0	2362.2	2318.6
27.5°	2675.3	2576.5	2365.0	2228.8	2162.1
30°	2579.6	2469.3	2237.4	2089.8	2011.4
32.5°	2486.7	2353.3	2115.9	1941.9	1869.3
35°	2382.6	2234.6	1979.7	1797.1	1733.1
37.5°	2281.0	2121.5	1852.1	1651.9	1579.7
40°	2173.8	2000.0	1718.6	1512.9	1437.6
42.5°	2063.6	1878.3	1585.4	1370.9	1298.6
45°	1947.7	1753.4	1449.2	1243.2	1173.7
47.5°	1837.6	1631.9	1318.9	1112.8	1049.2
50°	1715.9	1510.1	1191.3	991.1	930.5
52.5°	1596.9	1379.5	1069.5	878.2	823.2
55°	1480.9	1254.9	941.8	768.2	713.1
57.5°	1362.3	1130.4	829.1	666.7	620.3
60°	1240.4	1008.6	710.1	562.4	516.0
62.5°	1121.8	889.9	608.6	469.6	446.5
65°	1000.0	765.1	504.3	405.9	397.0
67.5°	884.1	649.1	405.9	356.4	347.8
70°	762.3	536.3	336.1	307.2	295.5
72.5°	646.4	431.7	281.0	258.0	252.2
75°	533.2	330.3	231.9	211.5	208.8
77.5°	420.3	234.6	182.6	171.0	165.1
80°	315.8	168.2	139.0	127.6	127.6
82.5°	220.2	113.1	95.7	89.8	89.8
85°	124.5	63.6	55.0	55.0	55.0
87.5°	46.4	23.1	23.1	20.3	20.3
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0

TEST NUMBER: P919495

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8

TEST NUMBER: P919495

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.64	13.57	13.51	14.45	15.56	8.61	9.53	9.47	10.42	11.53
	3H	14.32	15.15	15.20	16.04	17.18	9.80	10.63	10.68	11.52	12.66
	4H	14.93	15.71	15.83	16.61	17.76	10.25	11.03	11.14	11.93	13.08
	6H	15.35	16.07	16.26	16.98	18.14	10.57	11.29	11.48	12.19	13.36
	8H	15.48	16.16	16.39	17.08	18.25	10.66	11.34	11.57	12.27	13.43
	12H	15.54	16.19	16.46	17.11	18.29	10.70	11.36	11.62	12.27	13.46
4H	2H	12.67	13.45	13.57	14.35	15.50	9.21	9.99	10.11	10.89	12.04
	3H	14.50	15.15	15.41	16.08	17.24	10.56	11.21	11.47	12.14	13.31
	4H	15.19	15.78	16.11	16.71	17.90	11.11	11.70	12.03	12.63	13.82
	6H	15.71	16.22	16.64	17.17	18.36	11.53	12.04	12.46	12.99	14.18
	8H	15.88	16.36	16.82	17.30	18.50	11.66	12.13	12.59	13.07	14.28
	12H	15.98	16.40	16.93	17.37	18.57	11.72	12.15	12.68	13.11	14.32
8H	4H	15.17	15.64	16.10	16.58	17.79	11.39	11.87	12.33	12.81	14.02
	6H	15.73	16.12	16.69	17.11	18.31	11.91	12.30	12.87	13.29	14.49
	8H	15.94	16.29	16.91	17.26	18.48	12.09	12.44	13.07	13.42	14.64
	12H	16.08	16.39	17.05	17.35	18.62	12.21	12.52	13.19	13.49	14.76
12H	4H	15.12	15.55	16.08	16.51	17.72	11.40	11.83	12.36	12.79	14.00
	6H	15.70	16.05	16.68	17.03	18.25	11.96	12.30	12.93	13.28	14.50
	8H	15.92	16.23	16.90	17.20	18.47	12.17	12.47	13.14	13.44	14.71

END OF REPORT