

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922070

Luminaire Tested: DFN2DIP-PN3F0-030D090US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922070
REPORT IS A COMBINATION OF REPORTS P899596 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D090US940-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9376.3 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 95.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922070

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922070

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1292	1292	1292
5°	1294	1271	1279
10°	1280	1245	1237
15°	1262	1203	1172
20°	1238	1146	1093
25°	1213	1081	1016
30°	1180	1015	919
35°	1148	944	834
40°	1115	871	736
45°	1077	790	648
50°	1038	709	562
55°	996	621	479
60°	948	530	394
65°	893	438	354
70°	826	351	319
75°	742	308	289
80°	621	256	249
85°	422	166	184

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2515 cd/sqm

TEST NUMBER: P922070

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.1
10°-20°	284.5	3.0
20°-30°	399.4	4.3
30°-40°	435.3	4.6
40°-50°	400.1	4.3
50°-60°	314.2	3.4
60°-70°	204.5	2.2
70°-80°	105.3	1.1
80°-90°	34.1	0.4
90°-100°	157.1	1.7
100°-110°	499.0	5.3
110°-120°	854.0	9.1
120°-130°	1123.1	12.0
130°-140°	1260.7	13.4
140°-150°	1236.2	13.2
150°-160°	1037.0	11.1
160°-170°	687.7	7.3
170°-180°	240.4	2.6
0°-30°	787.5	8.4
0°-40°	1222.8	13.0
0°-60°	1937.2	20.7
0°-90°	2281.1	24.3
90°-120°	1510.1	16.1
90°-150°	5130.1	54.7
90°-180°	7095.0	75.7
0°-180°	9376.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1106	1101	1088	1097	1094	105
15°	1052	1040	1007	988	978	296
25°	955	922	856	816	800	439
35°	822	771	683	620	598	515
45°	672	605	500	429	405	519
55°	511	433	325	265	246	457
65°	345	264	174	140	137	342
75°	184	114	80	73	72	195
85°	43	22	19	19	19	49
90°	2	28	75	70	73	9
95°	112	133	137	137	133	124
105°	461	467	471	475	475	486
115°	857	869	865	863	857	848
125°	1246	1266	1260	1253	1250	1114
135°	1612	1636	1641	1638	1632	1246
145°	1957	1973	1985	1987	1979	1223
155°	2238	2244	2251	2262	2255	1030
165°	2435	2432	2432	2448	2437	687
175°	2534	2527	2523	2538	2525	241
180°	2538	2538	2538	2538	2538	

TEST NUMBER: P922070

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1105.6	1105.6	1105.6	1105.6	1105.6
2.5°	1110.6	1105.6	1094.6	1104.7	1102.7
5°	1105.6	1100.6	1087.6	1096.6	1093.6
7.5°	1096.6	1090.7	1076.7	1080.6	1075.6
10°	1084.6	1077.6	1057.7	1054.5	1048.7
12.5°	1069.6	1060.6	1033.6	1027.6	1016.5
15°	1051.6	1040.5	1006.6	987.6	977.6
17.5°	1030.5	1014.6	972.5	950.6	934.5
20°	1006.6	986.5	936.5	911.6	889.5
22.5°	980.6	957.5	899.5	865.5	850.5
25°	954.6	922.5	856.5	815.5	800.4
27.5°	923.5	889.5	816.5	769.5	746.4
30°	890.6	852.5	772.4	721.5	694.4
32.5°	858.4	812.4	730.5	670.4	645.3
35°	822.5	771.4	683.4	620.4	598.3
37.5°	787.5	732.4	639.4	570.2	545.4
40°	750.5	690.5	593.3	522.3	496.3
42.5°	712.4	648.5	547.3	473.2	448.3
45°	672.4	605.3	500.3	429.2	405.2
47.5°	634.4	563.4	455.3	384.1	362.2
50°	592.4	521.3	411.3	342.1	321.2
52.5°	551.3	476.3	369.3	303.2	284.2
55°	511.2	433.2	325.1	265.2	246.2
57.5°	470.3	390.2	286.2	230.2	214.1
60°	428.2	348.2	245.1	194.1	178.2
62.5°	387.3	307.2	210.1	162.1	154.2
65°	345.2	264.1	174.1	140.1	137.1
67.5°	305.2	224.1	140.1	123.1	120.0
70°	263.1	185.1	116.0	106.0	102.0
72.5°	223.1	149.0	97.0	89.1	87.0
75°	184.0	114.0	80.1	73.0	72.1
77.5°	145.1	81.0	63.0	59.0	57.0
80°	109.1	58.1	48.0	44.1	44.1
82.5°	76.0	39.1	33.0	31.0	31.0
85°	43.0	21.9	19.0	19.0	19.0
87.5°	16.1	7.9	7.9	7.0	7.0
90°	2.3	27.6	75.0	70.4	72.7
92.5°	47.4	64.3	66.6	68.8	68.8
95°	111.7	133.1	137.0	137.0	133.1
97.5°	185.9	205.8	214.3	214.3	214.3
100°	271.6	289.3	295.3	295.3	293.1
102.5°	361.9	375.0	383.3	385.7	383.3
105°	460.7	466.7	471.4	475.2	475.2
107.5°	558.6	567.8	567.8	569.3	558.6
110°	653.4	665.8	665.8	665.8	659.6

TEST NUMBER: P922070

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	756.0	769.0	766.7	760.6	756.0
115°	857.0	869.2	865.4	863.2	857.0
117.5°	957.3	974.1	963.4	957.3	951.1
120°	1058.3	1075.0	1058.3	1058.3	1051.3
122.5°	1150.0	1171.5	1160.8	1154.7	1150.0
125°	1246.5	1265.6	1259.5	1252.6	1250.4
127.5°	1340.6	1364.3	1355.9	1346.8	1340.6
130°	1428.6	1456.2	1452.3	1447.7	1439.3
132.5°	1527.3	1548.7	1550.2	1539.5	1533.5
135°	1612.2	1635.9	1640.6	1638.3	1632.2
137.5°	1707.1	1726.3	1730.1	1728.6	1719.4
140°	1790.6	1809.6	1820.3	1820.3	1812.0
142.5°	1876.2	1895.3	1901.5	1903.8	1895.3
145°	1957.4	1972.6	1984.9	1987.2	1978.8
147.5°	2030.1	2049.2	2058.3	2062.2	2053.8
150°	2105.1	2118.1	2126.5	2133.3	2126.5
152.5°	2171.6	2184.6	2195.3	2203.8	2195.3
155°	2238.2	2244.3	2251.2	2261.9	2255.0
157.5°	2295.5	2300.2	2304.0	2319.2	2308.5
160°	2346.8	2351.4	2353.8	2366.7	2357.5
162.5°	2394.2	2394.2	2396.6	2411.1	2400.4
165°	2434.8	2432.5	2432.5	2447.8	2437.1
167.5°	2471.6	2464.7	2464.7	2479.9	2469.2
170°	2499.1	2493.0	2490.7	2506.0	2493.0
172.5°	2518.2	2512.1	2509.8	2525.1	2512.1
175°	2533.5	2527.4	2522.8	2538.2	2525.1
177.5°	2541.9	2535.8	2531.2	2544.2	2531.2
180°	2538.2	2538.2	2538.2	2538.2	2538.2

TEST NUMBER: P922070

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.91	5.57	6.07	6.71	8.31	0.88	1.54	2.04	2.68	4.28
	3H	6.57	7.16	7.73	8.31	9.92	2.05	2.64	3.21	3.78	5.40
	4H	7.17	7.73	8.34	8.87	10.49	2.49	3.05	3.66	4.19	5.81
	6H	7.58	8.09	8.75	9.24	10.87	2.79	3.31	3.97	4.46	6.09
	8H	7.70	8.18	8.87	9.35	10.97	2.88	3.37	4.06	4.53	6.15
	12H	7.75	8.21	8.93	9.37	11.01	2.91	3.38	4.10	4.53	6.18
4H	2H	4.91	5.47	6.09	6.61	8.23	1.45	2.01	2.63	3.16	4.77
	3H	6.72	7.18	7.90	8.35	9.98	2.78	3.24	3.96	4.42	6.04
	4H	7.40	7.82	8.58	8.98	10.63	3.31	3.74	4.50	4.90	6.55
	6H	7.90	8.26	9.08	9.44	11.08	3.72	4.08	4.91	5.27	6.90
	8H	8.06	8.41	9.25	9.58	11.23	3.84	4.18	5.03	5.36	7.01
	12H	8.15	8.46	9.35	9.64	11.30	3.89	4.20	5.10	5.39	7.05
8H	4H	7.35	7.69	8.54	8.86	10.52	3.58	3.92	4.76	5.09	6.75
	6H	7.90	8.18	9.11	9.40	11.05	4.08	4.36	5.29	5.58	7.23
	8H	8.11	8.36	9.32	9.55	11.22	4.27	4.51	5.48	5.71	7.38
	12H	8.24	8.46	9.45	9.65	11.35	4.37	4.59	5.59	5.78	7.48
12H	4H	7.29	7.60	8.49	8.79	10.45	3.57	3.88	4.78	5.07	6.73
	6H	7.88	8.12	9.09	9.32	10.99	4.13	4.37	5.34	5.57	7.24
	8H	8.08	8.30	9.30	9.49	11.19	4.33	4.54	5.54	5.73	7.44

END OF REPORT