

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903061

Luminaire Tested: DFN2DIP-PN3F0-070D030US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903061
REPORT IS A COMBINATION OF REPORTS P901039 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D030US830-FLLONL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9331.2 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903061

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P903061

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24
9	53	40	33	27	50	39	32	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3001	3001	3001
5°	3004	2957	2978
10°	2978	2915	2936
15°	2932	2865	2872
20°	2871	2796	2806
25°	2811	2715	2730
30°	2735	2638	2634
35°	2663	2548	2533
40°	2575	2458	2436
45°	2487	2367	2337
50°	2391	2271	2222
55°	2290	2161	2117
60°	2176	2030	1996
65°	2051	1894	1853
70°	1892	1727	1699
75°	1672	1529	1555
80°	1406	1275	1283
85°	992	843	836

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2487 cd/sqm

TEST NUMBER: P903061

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.6	2.6
10°-20°	679.9	7.3
20°-30°	999.1	10.7
30°-40°	1160.4	12.4
40°-50°	1159.0	12.4
50°-60°	1010.6	10.8
60°-70°	747.1	8.0
70°-80°	422.7	4.5
80°-90°	113.2	1.2
90°-100°	31.5	0.3
100°-110°	117.3	1.3
110°-120°	311.1	3.3
120°-130°	516.0	5.5
130°-140°	548.1	5.9
140°-150°	509.4	5.5
150°-160°	409.6	4.4
160°-170°	263.9	2.8
170°-180°	90.8	1.0
0°-30°	1920.6	20.6
0°-40°	3081.0	33.0
0°-60°	5250.6	56.3
0°-90°	6533.5	70.0
90°-120°	459.9	4.9
90°-150°	2033.4	21.8
90°-180°	2798.0	30.0
0°-180°	9331.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2567	2567	2567	2567	2567	
5°	2567	2558	2530	2550	2545	244
15°	2444	2429	2397	2407	2395	688
25°	2212	2192	2150	2155	2150	1018
35°	1908	1884	1844	1829	1817	1192
45°	1553	1536	1498	1471	1461	1198
55°	1175	1160	1131	1101	1089	1051
65°	793	778	753	731	718	784
75°	415	410	397	383	388	443
85°	101	99	96	89	86	113
90°	1	8	14	17	19	9
95°	45	22	27	30	30	53
105°	210	231	42	50	52	224
115°	397	409	426	106	57	391
125°	561	570	584	588	590	501
135°	695	706	712	719	718	537
145°	806	805	817	822	818	504
155°	887	881	889	894	888	409
165°	935	931	933	938	933	264
175°	956	952	953	958	951	91
180°	954	954	954	954	954	

TEST NUMBER: P903061

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2567.2	2567.2	2567.2	2567.2	2567.2
2.5°	2582.2	2569.8	2542.6	2567.2	2562.5
5°	2567.2	2557.6	2530.3	2550.0	2545.2
7.5°	2550.0	2535.3	2508.0	2528.0	2523.0
10°	2523.0	2505.7	2476.1	2495.8	2488.4
12.5°	2485.8	2471.2	2441.6	2453.8	2448.8
15°	2443.9	2429.2	2397.0	2407.0	2394.6
17.5°	2392.0	2377.4	2345.1	2357.5	2345.1
20°	2335.1	2320.5	2285.9	2293.3	2283.6
22.5°	2278.6	2256.4	2224.1	2224.1	2219.1
25°	2211.9	2192.2	2150.3	2155.0	2150.3
27.5°	2137.7	2120.4	2088.5	2081.1	2068.8
30°	2063.9	2043.9	2007.0	1999.7	1989.7
32.5°	1984.7	1970.1	1930.5	1915.6	1905.6
35°	1908.3	1883.7	1844.1	1829.2	1816.8
37.5°	1821.8	1799.6	1760.0	1742.8	1730.4
40°	1733.1	1713.2	1673.6	1651.6	1641.6
42.5°	1646.6	1626.7	1587.4	1562.5	1547.8
45°	1552.8	1535.6	1498.4	1471.4	1461.4
47.5°	1461.4	1444.2	1404.6	1377.3	1362.7
50°	1365.1	1352.7	1318.1	1283.6	1271.3
52.5°	1271.3	1254.1	1222.1	1194.9	1177.5
55°	1175.2	1160.3	1130.7	1101.1	1088.7
57.5°	1078.8	1066.5	1034.3	1004.7	994.8
60°	982.4	972.7	938.2	911.0	903.6
62.5°	888.6	871.4	846.8	822.2	812.2
65°	792.6	777.6	753.0	730.8	718.4
67.5°	693.8	681.3	659.2	642.0	632.0
70°	602.4	592.5	570.1	552.9	543.2
72.5°	508.6	498.7	486.4	469.1	461.8
75°	414.6	409.9	397.3	382.7	387.7
77.5°	330.8	320.8	315.8	308.5	301.2
80°	246.9	244.4	239.4	232.1	227.1
82.5°	167.9	167.9	165.5	155.6	155.6
85°	101.1	98.8	96.4	88.8	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	0.7	8.3	13.8	17.3	18.6
92.5°	17.3	14.5	16.6	18.0	18.6
95°	44.9	22.1	26.9	30.4	29.7
97.5°	80.8	24.2	35.2	37.3	38.0
100°	122.2	27.6	39.4	44.9	46.3
102.5°	167.8	166.5	40.7	48.3	50.4
105°	209.9	230.6	42.1	49.7	52.5
107.5°	258.9	276.2	43.5	51.1	53.9
110°	305.9	320.4	120.8	51.8	54.6

TEST NUMBER: P903061

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.2	362.5	350.8	53.2	55.2
115°	397.0	408.8	426.0	106.3	56.6
117.5°	437.8	451.6	463.4	364.6	183.7
120°	483.3	493.7	506.1	514.4	421.2
122.5°	522.0	533.1	547.0	551.0	551.8
125°	561.4	570.3	583.5	588.3	590.4
127.5°	597.3	606.9	617.4	624.2	624.9
130°	631.1	642.2	649.8	657.3	656.8
132.5°	665.6	674.7	682.2	688.4	687.8
135°	694.7	705.8	711.9	718.9	717.5
137.5°	725.0	733.3	740.3	747.2	745.1
140°	754.7	760.3	767.8	774.0	770.6
142.5°	779.7	784.5	793.4	798.9	795.5
145°	805.9	805.1	816.9	821.7	818.2
147.5°	828.6	826.5	838.3	841.7	839.0
150°	850.7	845.9	857.0	861.0	857.6
152.5°	869.3	863.8	874.2	878.4	873.5
155°	887.3	881.2	889.4	893.5	888.1
157.5°	901.8	896.4	902.6	907.4	901.8
160°	914.3	910.1	914.3	918.4	913.5
162.5°	925.3	921.1	924.6	929.4	923.2
165°	934.9	930.9	932.9	937.7	932.9
167.5°	942.5	938.4	940.5	945.4	939.1
170°	948.8	944.6	946.0	950.8	944.6
172.5°	952.9	948.8	950.2	955.0	948.8
175°	956.3	951.5	952.9	957.7	950.8
177.5°	957.7	952.9	953.7	958.5	952.3
180°	954.3	954.3	954.3	954.3	954.3

TEST NUMBER: P903061

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US830-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.72	13.80	13.49	14.58	15.54	12.28	13.36	13.05	14.14	15.10
	3H	14.39	15.36	15.17	16.15	17.14	13.91	14.88	14.69	15.67	16.66
	4H	14.99	15.90	15.78	16.70	17.70	14.50	15.41	15.30	16.22	17.21
	6H	15.39	16.23	16.20	17.05	18.06	14.90	15.74	15.71	16.56	17.57
	8H	15.50	16.30	16.32	17.13	18.14	15.01	15.81	15.83	16.64	17.65
	12H	15.55	16.32	16.38	17.14	18.18	15.06	15.82	15.88	16.65	17.68
4H	2H	13.20	14.12	14.00	14.92	15.92	12.85	13.77	13.65	14.57	15.57
	3H	15.08	15.84	15.89	16.68	17.69	14.68	15.44	15.49	16.28	17.29
	4H	15.80	16.49	16.63	17.33	18.37	15.39	16.08	16.21	16.92	17.95
	6H	16.32	16.92	17.16	17.78	18.83	15.90	16.50	16.74	17.36	18.41
	8H	16.47	17.04	17.32	17.89	18.95	16.05	16.61	16.89	17.47	18.52
	12H	16.55	17.06	17.42	17.94	19.00	16.12	16.62	16.98	17.50	18.56
8H	4H	16.01	16.57	16.86	17.43	18.49	15.64	16.20	16.49	17.06	18.12
	6H	16.64	17.11	17.52	18.01	19.06	16.27	16.73	17.14	17.63	18.69
	8H	16.86	17.27	17.75	18.17	19.24	16.48	16.89	17.36	17.79	18.86
	12H	17.00	17.36	17.89	18.25	19.38	16.60	16.96	17.49	17.85	18.98
12H	4H	16.01	16.51	16.87	17.39	18.45	15.64	16.15	16.51	17.03	18.09
	6H	16.67	17.09	17.56	17.98	19.05	16.31	16.72	17.19	17.62	18.69
	8H	16.92	17.28	17.81	18.17	19.30	16.55	16.91	17.44	17.80	18.93