

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922152

Luminaire Tested: DFN2DIP-PN3F0-060D090US940-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P922152  
REPORT IS A COMBINATION OF REPORTS P899601 AND P896399  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-060D090US940-FLLFLL  
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12399.3 lumens  
Efficiency: N/A  
Efficacy: 96.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 128.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9821  
Total Harmonic Distortion (THDi): 0.08  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P922152

CATALOG NUMBER: DFN2DIP-PN3F0-060D090US940-FLLFLL

### Luminous Intensity Polar Plot



TEST NUMBER: P922152

CATALOG NUMBER: DFN2DIP-PN3F0-060D090US940-FLLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 105 | 105 | 105 | 105 | 96 | 96 | 96 | 96 | 79 | 79 | 79 | 64 | 64 | 64 | 49 | 49 | 49 |
| 1   | 96  | 92  | 88  | 85  | 88 | 84 | 81 | 78 | 69 | 67 | 65 | 56 | 54 | 53 | 44 | 43 | 42 |
| 2   | 88  | 80  | 74  | 69  | 80 | 73 | 68 | 64 | 61 | 57 | 54 | 49 | 47 | 44 | 38 | 37 | 35 |
| 3   | 80  | 70  | 63  | 57  | 73 | 65 | 58 | 53 | 54 | 49 | 45 | 44 | 40 | 37 | 34 | 32 | 30 |
| 4   | 73  | 62  | 55  | 49  | 66 | 57 | 50 | 45 | 48 | 43 | 39 | 39 | 35 | 32 | 30 | 28 | 26 |
| 5   | 67  | 56  | 47  | 42  | 61 | 51 | 44 | 39 | 43 | 37 | 33 | 35 | 31 | 28 | 27 | 25 | 22 |
| 6   | 62  | 50  | 42  | 36  | 56 | 46 | 39 | 34 | 38 | 33 | 29 | 31 | 27 | 24 | 25 | 22 | 20 |
| 7   | 57  | 45  | 37  | 31  | 52 | 41 | 34 | 29 | 35 | 29 | 25 | 29 | 24 | 21 | 23 | 20 | 18 |
| 8   | 53  | 41  | 33  | 28  | 48 | 38 | 31 | 26 | 32 | 26 | 23 | 26 | 22 | 19 | 21 | 18 | 16 |
| 9   | 49  | 37  | 30  | 25  | 45 | 34 | 28 | 23 | 29 | 24 | 20 | 24 | 20 | 17 | 19 | 16 | 14 |
| 10  | 46  | 34  | 27  | 22  | 42 | 31 | 25 | 21 | 27 | 22 | 18 | 22 | 18 | 15 | 18 | 15 | 13 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2434 | 2434 | 2434 |
| 5°  | 2436 | 2398 | 2415 |
| 10° | 2415 | 2364 | 2381 |
| 15° | 2378 | 2323 | 2329 |
| 20° | 2328 | 2268 | 2276 |
| 25° | 2279 | 2201 | 2214 |
| 30° | 2218 | 2139 | 2136 |
| 35° | 2160 | 2067 | 2054 |
| 40° | 2088 | 1993 | 1975 |
| 45° | 2017 | 1919 | 1895 |
| 50° | 1939 | 1842 | 1802 |
| 55° | 1857 | 1752 | 1717 |
| 60° | 1764 | 1646 | 1618 |
| 65° | 1663 | 1535 | 1503 |
| 70° | 1534 | 1401 | 1378 |
| 75° | 1356 | 1240 | 1261 |
| 80° | 1141 | 1033 | 1040 |
| 85° | 803  | 683  | 678  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2515 cd/sqm

TEST NUMBER: P922152

CATALOG NUMBER: DFN2DIP-PN3F0-060D090US940-FLLFLL

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 195.9   | 1.6       |
| 10°-20°   | 551.3   | 4.4       |
| 20°-30°   | 810.2   | 6.5       |
| 30°-40°   | 941.0   | 7.6       |
| 40°-50°   | 939.8   | 7.6       |
| 50°-60°   | 819.5   | 6.6       |
| 60°-70°   | 605.8   | 4.9       |
| 70°-80°   | 342.7   | 2.8       |
| 80°-90°   | 97.7    | 0.8       |
| 90°-100°  | 157.1   | 1.3       |
| 100°-110° | 499.0   | 4.0       |
| 110°-120° | 854.0   | 6.9       |
| 120°-130° | 1123.1  | 9.1       |
| 130°-140° | 1260.7  | 10.2      |
| 140°-150° | 1236.2  | 10.0      |
| 150°-160° | 1037.0  | 8.4       |
| 160°-170° | 687.7   | 5.5       |
| 170°-180° | 240.4   | 1.9       |
| 0°-30°    | 1557.4  | 12.6      |
| 0°-40°    | 2498.4  | 20.1      |
| 0°-60°    | 4257.8  | 34.3      |
| 0°-90°    | 5304.0  | 42.8      |
| 90°-120°  | 1510.1  | 12.2      |
| 90°-150°  | 5130.1  | 41.4      |
| 90°-180°  | 7095.0  | 57.2      |
| 0°-180°   | 12399.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 2082 | 2082  | 2082 | 2082  | 2082 |      |
| 5°   | 2082 | 2074  | 2052 | 2068  | 2064 | 198  |
| 15°  | 1982 | 1970  | 1944 | 1952  | 1942 | 558  |
| 25°  | 1794 | 1778  | 1744 | 1748  | 1744 | 825  |
| 35°  | 1548 | 1528  | 1495 | 1483  | 1473 | 966  |
| 45°  | 1259 | 1245  | 1215 | 1193  | 1185 | 972  |
| 55°  | 953  | 941   | 917  | 893   | 883  | 852  |
| 65°  | 643  | 631   | 611  | 592   | 583  | 635  |
| 75°  | 336  | 332   | 322  | 310   | 314  | 359  |
| 85°  | 82   | 80    | 78   | 72    | 70   | 91   |
| 90°  | 2    | 28    | 75   | 70    | 73   | 12   |
| 95°  | 112  | 133   | 137  | 137   | 133  | 124  |
| 105° | 461  | 467   | 471  | 475   | 475  | 486  |
| 115° | 857  | 869   | 865  | 863   | 857  | 848  |
| 125° | 1246 | 1266  | 1260 | 1253  | 1250 | 1114 |
| 135° | 1612 | 1636  | 1641 | 1638  | 1632 | 1246 |
| 145° | 1957 | 1973  | 1985 | 1987  | 1979 | 1223 |
| 155° | 2238 | 2244  | 2251 | 2262  | 2255 | 1030 |
| 165° | 2435 | 2432  | 2432 | 2448  | 2437 | 687  |
| 175° | 2534 | 2527  | 2523 | 2538  | 2525 | 241  |
| 180° | 2538 | 2538  | 2538 | 2538  | 2538 |      |

TEST NUMBER: P922152

CATALOG NUMBER: DFN2DIP-PN3F0-060D090US940-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 2081.8 | 2081.8 | 2081.8 | 2081.8 | 2081.8 |
| 2.5°   | 2093.9 | 2083.9 | 2061.8 | 2081.8 | 2078.0 |
| 5°     | 2081.8 | 2073.9 | 2051.8 | 2067.8 | 2064.0 |
| 7.5°   | 2067.8 | 2055.9 | 2033.8 | 2050.0 | 2045.9 |
| 10°    | 2045.9 | 2031.9 | 2007.9 | 2023.8 | 2017.9 |
| 12.5°  | 2015.8 | 2003.9 | 1979.9 | 1989.9 | 1985.8 |
| 15°    | 1981.7 | 1969.9 | 1943.8 | 1951.9 | 1941.9 |
| 17.5°  | 1939.7 | 1927.9 | 1901.8 | 1911.6 | 1901.8 |
| 20°    | 1893.6 | 1881.8 | 1853.7 | 1859.7 | 1851.8 |
| 22.5°  | 1847.8 | 1829.7 | 1803.6 | 1803.6 | 1799.6 |
| 25°    | 1793.6 | 1777.7 | 1743.7 | 1747.5 | 1743.7 |
| 27.5°  | 1733.5 | 1719.5 | 1693.5 | 1687.7 | 1677.7 |
| 30°    | 1673.7 | 1657.4 | 1627.5 | 1621.6 | 1613.5 |
| 32.5°  | 1609.4 | 1597.6 | 1565.5 | 1553.4 | 1545.3 |
| 35°    | 1547.5 | 1527.5 | 1495.4 | 1483.3 | 1473.3 |
| 37.5°  | 1477.4 | 1459.3 | 1427.3 | 1413.2 | 1403.2 |
| 40°    | 1405.3 | 1389.2 | 1357.2 | 1339.3 | 1331.2 |
| 42.5°  | 1335.2 | 1319.1 | 1287.3 | 1267.1 | 1255.2 |
| 45°    | 1259.3 | 1245.2 | 1215.0 | 1193.2 | 1185.1 |
| 47.5°  | 1185.1 | 1171.1 | 1139.1 | 1117.0 | 1105.0 |
| 50°    | 1107.0 | 1097.0 | 1069.0 | 1040.9 | 1030.9 |
| 52.5°  | 1030.9 | 1016.9 | 991.0  | 968.9  | 954.9  |
| 55°    | 953.0  | 940.8  | 916.9  | 892.9  | 882.9  |
| 57.5°  | 874.9  | 864.9  | 838.7  | 814.8  | 806.6  |
| 60°    | 796.7  | 788.8  | 760.8  | 738.7  | 732.7  |
| 62.5°  | 720.6  | 706.6  | 686.6  | 666.6  | 658.6  |
| 65°    | 642.7  | 630.6  | 610.6  | 592.5  | 582.6  |
| 67.5°  | 562.6  | 552.4  | 534.6  | 520.6  | 512.5  |
| 70°    | 488.5  | 480.5  | 462.4  | 448.4  | 440.5  |
| 72.5°  | 412.4  | 404.4  | 394.4  | 380.4  | 374.4  |
| 75°    | 336.2  | 332.4  | 322.2  | 310.3  | 314.3  |
| 77.5°  | 268.2  | 260.2  | 256.1  | 250.2  | 244.2  |
| 80°    | 200.3  | 198.1  | 194.1  | 188.2  | 184.1  |
| 82.5°  | 136.2  | 136.2  | 134.2  | 126.2  | 126.2  |
| 85°    | 81.9   | 80.1   | 78.1   | 72.0   | 70.1   |
| 87.5°  | 36.1   | 32.1   | 28.0   | 22.1   | 20.0   |
| 90°    | 2.3    | 27.6   | 75.0   | 70.4   | 72.7   |
| 92.5°  | 47.4   | 64.3   | 66.6   | 68.8   | 68.8   |
| 95°    | 111.7  | 133.1  | 137.0  | 137.0  | 133.1  |
| 97.5°  | 185.9  | 205.8  | 214.3  | 214.3  | 214.3  |
| 100°   | 271.6  | 289.3  | 295.3  | 295.3  | 293.1  |
| 102.5° | 361.9  | 375.0  | 383.3  | 385.7  | 383.3  |
| 105°   | 460.7  | 466.7  | 471.4  | 475.2  | 475.2  |
| 107.5° | 558.6  | 567.8  | 567.8  | 569.3  | 558.6  |
| 110°   | 653.4  | 665.8  | 665.8  | 665.8  | 659.6  |

TEST NUMBER: P922152

CATALOG NUMBER: DFN2DIP-PN3F0-060D090US940-FLLFLL

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 756.0  | 769.0  | 766.7  | 760.6  | 756.0  |
| 115°   | 857.0  | 869.2  | 865.4  | 863.2  | 857.0  |
| 117.5° | 957.3  | 974.1  | 963.4  | 957.3  | 951.1  |
| 120°   | 1058.3 | 1075.0 | 1058.3 | 1058.3 | 1051.3 |
| 122.5° | 1150.0 | 1171.5 | 1160.8 | 1154.7 | 1150.0 |
| 125°   | 1246.5 | 1265.6 | 1259.5 | 1252.6 | 1250.4 |
| 127.5° | 1340.6 | 1364.3 | 1355.9 | 1346.8 | 1340.6 |
| 130°   | 1428.6 | 1456.2 | 1452.3 | 1447.7 | 1439.3 |
| 132.5° | 1527.3 | 1548.7 | 1550.2 | 1539.5 | 1533.5 |
| 135°   | 1612.2 | 1635.9 | 1640.6 | 1638.3 | 1632.2 |
| 137.5° | 1707.1 | 1726.3 | 1730.1 | 1728.6 | 1719.4 |
| 140°   | 1790.6 | 1809.6 | 1820.3 | 1820.3 | 1812.0 |
| 142.5° | 1876.2 | 1895.3 | 1901.5 | 1903.8 | 1895.3 |
| 145°   | 1957.4 | 1972.6 | 1984.9 | 1987.2 | 1978.8 |
| 147.5° | 2030.1 | 2049.2 | 2058.3 | 2062.2 | 2053.8 |
| 150°   | 2105.1 | 2118.1 | 2126.5 | 2133.3 | 2126.5 |
| 152.5° | 2171.6 | 2184.6 | 2195.3 | 2203.8 | 2195.3 |
| 155°   | 2238.2 | 2244.3 | 2251.2 | 2261.9 | 2255.0 |
| 157.5° | 2295.5 | 2300.2 | 2304.0 | 2319.2 | 2308.5 |
| 160°   | 2346.8 | 2351.4 | 2353.8 | 2366.7 | 2357.5 |
| 162.5° | 2394.2 | 2394.2 | 2396.6 | 2411.1 | 2400.4 |
| 165°   | 2434.8 | 2432.5 | 2432.5 | 2447.8 | 2437.1 |
| 167.5° | 2471.6 | 2464.7 | 2464.7 | 2479.9 | 2469.2 |
| 170°   | 2499.1 | 2493.0 | 2490.7 | 2506.0 | 2493.0 |
| 172.5° | 2518.2 | 2512.1 | 2509.8 | 2525.1 | 2512.1 |
| 175°   | 2533.5 | 2527.4 | 2522.8 | 2538.2 | 2525.1 |
| 177.5° | 2541.9 | 2535.8 | 2531.2 | 2544.2 | 2531.2 |
| 180°   | 2538.2 | 2538.2 | 2538.2 | 2538.2 | 2538.2 |

TEST NUMBER: P922152

CATALOG NUMBER: DFN2DIP-PN3F0-060D090US940-FLLFLL

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 9.61             | 10.41 | 10.63 | 11.44 | 12.81 | 9.18           | 9.98  | 10.19 | 11.00 | 12.37 |
|                 | 3H   | 11.26            | 11.98 | 12.29 | 13.02 | 14.41 | 10.78          | 11.50 | 11.81 | 12.53 | 13.92 |
|                 | 4H   | 11.85            | 12.52 | 12.88 | 13.56 | 14.96 | 11.36          | 12.04 | 12.40 | 13.08 | 14.47 |
|                 | 6H   | 12.24            | 12.86 | 13.29 | 13.90 | 15.31 | 11.75          | 12.37 | 12.80 | 13.41 | 14.82 |
|                 | 8H   | 12.34            | 12.93 | 13.39 | 13.99 | 15.40 | 11.85          | 12.44 | 12.90 | 13.50 | 14.91 |
|                 | 12H  | 12.38            | 12.95 | 13.44 | 14.00 | 15.43 | 11.88          | 12.45 | 12.94 | 13.50 | 14.93 |
| 4H              | 2H   | 10.06            | 10.74 | 11.11 | 11.78 | 13.18 | 9.71           | 10.39 | 10.76 | 11.43 | 12.83 |
|                 | 3H   | 11.92            | 12.49 | 12.97 | 13.55 | 14.96 | 11.52          | 12.08 | 12.57 | 13.15 | 14.56 |
|                 | 4H   | 12.62            | 13.14 | 13.69 | 14.20 | 15.63 | 12.21          | 12.73 | 13.27 | 13.78 | 15.22 |
|                 | 6H   | 13.13            | 13.58 | 14.20 | 14.66 | 16.09 | 12.71          | 13.15 | 13.78 | 14.23 | 15.66 |
|                 | 8H   | 13.28            | 13.69 | 14.35 | 14.77 | 16.21 | 12.85          | 13.27 | 13.92 | 14.34 | 15.78 |
|                 | 12H  | 13.34            | 13.72 | 14.43 | 14.81 | 16.26 | 12.91          | 13.28 | 13.99 | 14.37 | 15.82 |
| 8H              | 4H   | 12.81            | 13.23 | 13.88 | 14.30 | 15.75 | 12.44          | 12.86 | 13.51 | 13.93 | 15.38 |
|                 | 6H   | 13.43            | 13.78 | 14.53 | 14.89 | 16.33 | 13.06          | 13.40 | 14.15 | 14.52 | 15.96 |
|                 | 8H   | 13.65            | 13.95 | 14.75 | 15.05 | 16.51 | 13.27          | 13.57 | 14.37 | 14.67 | 16.13 |
|                 | 12H  | 13.77            | 14.04 | 14.88 | 15.13 | 16.63 | 13.37          | 13.64 | 14.48 | 14.73 | 16.23 |
| 12H             | 4H   | 12.79            | 13.17 | 13.88 | 14.26 | 15.71 | 12.43          | 12.81 | 13.52 | 13.90 | 15.34 |
|                 | 6H   | 13.46            | 13.76 | 14.56 | 14.86 | 16.32 | 13.10          | 13.40 | 14.20 | 14.50 | 15.96 |
|                 | 8H   | 13.70            | 13.96 | 14.80 | 15.05 | 16.55 | 13.32          | 13.59 | 14.43 | 14.68 | 16.18 |