

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922212

Luminaire Tested: DFN2DIP-PN3F0-090D030US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922212
REPORT IS A COMBINATION OF REPORTS P899523 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D030US940-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10312.6 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922212
CATALOG NUMBER: DFN2DIP-PN3F0-090D030US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P922212
 CATALOG NUMBER: DFN2DIP-PN3F0-090D030US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77			77
1	104	99	95	92	99	95	91	88	86	84	81	79	77	75	72	70	68	65			65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58	54			54
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	52	49	46			46
4	79	68	59	53	75	65	57	52	60	53	48	55	50	45	50	46	42	40			40
5	73	61	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37	34			34
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33	30			30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	37	33	29	27			27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	34	30	26	24			24
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24	22			22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	20			20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3650	3650	3650
5°	3654	3597	3622
10°	3622	3546	3572
15°	3567	3485	3493
20°	3493	3401	3413
25°	3419	3302	3321
30°	3327	3209	3204
35°	3240	3100	3081
40°	3132	2990	2963
45°	3025	2879	2843
50°	2908	2762	2703
55°	2786	2628	2575
60°	2647	2469	2428
65°	2495	2303	2254
70°	2301	2101	2067
75°	2034	1859	1891
80°	1711	1550	1561
85°	1207	1026	1017

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3025 cd/sqm



TEST NUMBER: P922212

CATALOG NUMBER: DFN2DIP-PN3F0-090D030US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.9	2.9
10°-20°	827.0	8.0
20°-30°	1215.3	11.8
30°-40°	1411.5	13.7
40°-50°	1409.7	13.7
50°-60°	1229.3	11.9
60°-70°	908.7	8.8
70°-80°	514.1	5.0
80°-90°	138.1	1.3
90°-100°	52.3	0.5
100°-110°	166.3	1.6
110°-120°	284.7	2.8
120°-130°	374.4	3.6
130°-140°	420.2	4.1
140°-150°	412.1	4.0
150°-160°	345.7	3.4
160°-170°	229.2	2.2
170°-180°	80.1	0.8
0°-30°	2336.2	22.7
0°-40°	3747.7	36.3
0°-60°	6386.7	61.9
0°-90°	7947.6	77.1
90°-120°	503.4	4.9
90°-150°	1710.0	16.6
90°-180°	2365.0	22.9
0°-180°	10312.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3123	3123	3123	3123	3123	
5°	3123	3111	3078	3102	3096	296
15°	2973	2955	2916	2928	2913	837
25°	2690	2666	2616	2621	2616	1238
35°	2321	2291	2243	2225	2210	1449
45°	1889	1868	1823	1790	1778	1458
55°	1430	1411	1375	1339	1324	1278
65°	964	946	916	889	874	953
75°	504	499	483	466	472	538
85°	123	120	117	108	105	137
90°	1	9	25	24	24	10
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	



TEST NUMBER: P922212

CATALOG NUMBER: DFN2DIP-PN3F0-090D030US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3122.7	3122.7	3122.7	3122.7	3122.7
2.5°	3140.9	3125.9	3092.8	3122.7	3117.0
5°	3122.7	3110.9	3077.8	3101.7	3095.9
7.5°	3101.7	3083.9	3050.7	3075.0	3068.9
10°	3068.9	3047.9	3011.8	3035.7	3026.8
12.5°	3023.6	3005.8	2969.8	2984.7	2978.8
15°	2972.7	2954.9	2915.6	2927.8	2912.8
17.5°	2909.6	2891.7	2852.6	2867.6	2852.6
20°	2840.5	2822.6	2780.5	2789.4	2777.7
22.5°	2771.6	2744.6	2705.4	2705.4	2699.3
25°	2690.4	2666.5	2615.6	2621.3	2615.6
27.5°	2600.2	2579.2	2540.4	2531.5	2516.5
30°	2510.4	2486.2	2441.2	2432.3	2420.3
32.5°	2414.2	2396.4	2348.2	2330.1	2318.0
35°	2321.2	2291.2	2243.1	2225.0	2210.0
37.5°	2216.1	2189.0	2140.8	2119.9	2104.9
40°	2108.0	2083.8	2035.7	2008.9	1996.9
42.5°	2002.9	1978.7	1930.9	1900.7	1882.8
45°	1888.8	1867.9	1822.6	1789.8	1777.7
47.5°	1777.7	1756.7	1708.5	1675.4	1657.6
50°	1660.5	1645.5	1603.4	1561.4	1546.4
52.5°	1546.4	1525.4	1486.5	1453.4	1432.4
55°	1429.5	1411.3	1375.3	1339.3	1324.4
57.5°	1312.2	1297.3	1258.1	1222.1	1210.0
60°	1195.0	1183.2	1141.1	1108.0	1099.1
62.5°	1080.9	1059.9	1029.9	1000.1	987.9
65°	964.0	945.8	915.9	888.9	873.9
67.5°	843.9	828.7	801.8	780.9	768.7
70°	732.7	720.6	693.6	672.5	660.8
72.5°	618.7	606.5	591.6	570.6	561.7
75°	504.4	498.6	483.3	465.5	471.5
77.5°	402.3	390.3	384.2	375.3	366.4
80°	300.4	297.2	291.1	282.2	276.3
82.5°	204.2	204.2	201.3	189.2	189.2
85°	123.0	120.1	117.3	108.0	105.1
87.5°	54.1	48.1	42.1	33.2	30.0
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9



TEST NUMBER: P922212

CATALOG NUMBER: DFN2DIP-PN3F0-090D030US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1



TEST NUMBER: P922212
 CATALOG NUMBER: DFN2DIP-PN3F0-090D030US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.93	15.10	14.61	15.80	16.63	13.49	14.66	14.18	15.36	16.19
	3H	15.61	16.66	16.30	17.37	18.23	15.12	16.18	15.82	16.89	17.75
	4H	16.20	17.20	16.92	17.92	18.79	15.72	16.71	16.44	17.44	18.31
	6H	16.62	17.53	17.34	18.27	19.15	16.13	17.04	16.86	17.78	18.66
	8H	16.73	17.60	17.47	18.35	19.24	16.24	17.11	16.98	17.86	18.75
	12H	16.78	17.62	17.53	18.36	19.28	16.29	17.12	17.03	17.87	18.78
4H	2H	14.42	15.42	15.14	16.14	17.01	14.07	15.07	14.79	15.79	16.66
	3H	16.31	17.14	17.04	17.90	18.79	15.91	16.74	16.64	17.50	18.39
	4H	17.03	17.79	17.78	18.55	19.46	16.62	17.37	17.36	18.13	19.05
	6H	17.56	18.21	18.33	19.00	19.92	17.14	17.79	17.90	18.58	19.50
	8H	17.71	18.32	18.48	19.11	20.04	17.29	17.90	18.06	18.68	19.62
	12H	17.80	18.35	18.59	19.15	20.10	17.36	17.91	18.15	18.72	19.66
8H	4H	17.25	17.86	18.02	18.64	19.58	16.88	17.49	17.65	18.27	19.21
	6H	17.89	18.39	18.69	19.22	20.16	17.51	18.02	18.31	18.84	19.78
	8H	18.11	18.56	18.92	19.38	20.33	17.72	18.17	18.53	19.00	19.95
	12H	18.25	18.65	19.06	19.46	20.47	17.85	18.25	18.66	19.06	20.07
12H	4H	17.25	17.80	18.04	18.60	19.55	16.89	17.44	17.68	18.24	19.18
	6H	17.92	18.37	18.73	19.19	20.15	17.55	18.00	18.36	18.83	19.78
	8H	18.17	18.57	18.98	19.38	20.39	17.80	18.20	18.61	19.01	20.02