

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924778

Luminaire Tested: DFN2DIP-PN3F0-030D040US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924778
REPORT IS A COMBINATION OF REPORTS P899526 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D040US950-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5809.8 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 53.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924778

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924778

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1383	1383	1383
5°	1384	1360	1369
10°	1370	1332	1324
15°	1350	1287	1254
20°	1324	1226	1169
25°	1298	1157	1087
30°	1263	1086	984
35°	1228	1010	892
40°	1193	932	788
45°	1152	846	693
50°	1110	758	601
55°	1066	665	512
60°	1015	567	421
65°	956	468	378
70°	884	376	341
75°	794	330	309
80°	665	273	266
85°	451	178	196

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1193 cd/sqm

TEST NUMBER: P924778

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	1.9
10°-20°	304.3	5.2
20°-30°	427.3	7.4
30°-40°	465.7	8.0
40°-50°	428.1	7.4
50°-60°	336.2	5.8
60°-70°	218.8	3.8
70°-80°	112.6	1.9
80°-90°	32.2	0.6
90°-100°	74.7	1.3
100°-110°	237.3	4.1
110°-120°	406.1	7.0
120°-130°	534.0	9.2
130°-140°	599.4	10.3
140°-150°	587.8	10.1
150°-160°	493.1	8.5
160°-170°	327.0	5.6
170°-180°	114.3	2.0
0°-30°	842.5	14.5
0°-40°	1308.2	22.5
0°-60°	2072.5	35.7
0°-90°	2436.1	41.9
90°-120°	718.0	12.4
90°-150°	2439.3	42.0
90°-180°	3374.0	58.1
0°-180°	5809.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1183	1178	1164	1173	1170	112
15°	1125	1113	1077	1057	1046	317
25°	1021	987	916	872	856	470
35°	880	825	731	664	640	551
45°	719	648	535	459	434	556
55°	547	464	348	284	263	489
65°	369	283	186	150	147	366
75°	197	122	86	78	77	208
85°	46	24	20	20	20	53
90°	1	13	36	34	34	6
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	

TEST NUMBER: P924778

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1182.9	1182.9	1182.9	1182.9	1182.9
2.5°	1188.2	1182.9	1171.0	1181.8	1179.7
5°	1182.9	1177.5	1163.6	1173.2	1170.0
7.5°	1173.2	1166.8	1151.9	1156.1	1150.7
10°	1160.4	1152.9	1131.5	1128.2	1121.9
12.5°	1144.3	1134.7	1105.8	1099.4	1087.6
15°	1125.1	1113.2	1076.9	1056.6	1045.9
17.5°	1102.5	1085.5	1040.4	1017.0	999.8
20°	1076.9	1055.4	1001.9	975.3	951.6
22.5°	1049.1	1024.4	962.3	926.0	909.9
25°	1021.3	986.9	916.3	872.4	856.3
27.5°	988.1	951.6	873.5	823.2	798.5
30°	952.8	912.0	826.4	771.9	742.9
32.5°	918.4	869.2	781.5	717.2	690.4
35°	880.0	825.3	731.1	663.7	640.1
37.5°	842.5	783.5	684.0	610.1	583.5
40°	802.9	738.7	634.8	558.8	531.0
42.5°	762.2	693.7	585.6	506.3	479.6
45°	719.4	647.6	535.3	459.2	433.5
47.5°	678.7	602.7	487.1	411.0	387.5
50°	633.7	557.7	440.0	366.0	343.6
52.5°	589.8	509.5	395.1	324.4	304.0
55°	546.9	463.5	347.8	283.7	263.4
57.5°	503.1	417.5	306.2	246.2	229.1
60°	458.1	372.5	262.3	207.7	190.6
62.5°	414.3	328.7	224.8	173.4	164.9
65°	369.3	282.6	186.2	149.9	146.6
67.5°	326.6	239.7	149.9	131.7	128.4
70°	281.5	198.1	124.1	113.4	109.1
72.5°	238.7	159.4	103.8	95.3	93.1
75°	196.9	122.0	85.7	78.1	77.1
77.5°	155.2	86.6	67.4	63.2	61.0
80°	116.7	62.1	51.3	47.1	47.1
82.5°	81.3	41.8	35.3	33.2	33.2
85°	46.0	23.5	20.3	20.3	20.3
87.5°	17.2	8.5	8.5	7.5	7.5
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7

TEST NUMBER: P924778

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8

TEST NUMBER: P924778

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.43	8.20	8.46	9.23	10.61	3.39	4.16	4.42	5.20	6.58
	3H	9.10	9.78	10.14	10.82	12.23	4.57	5.26	5.61	6.30	7.71
	4H	9.70	10.35	10.75	11.39	12.80	5.02	5.67	6.07	6.71	8.12
	6H	10.11	10.71	11.17	11.76	13.18	5.33	5.93	6.39	6.97	8.40
	8H	10.23	10.80	11.30	11.87	13.28	5.41	5.98	6.48	7.05	8.47
	12H	10.29	10.83	11.36	11.89	13.33	5.45	5.99	6.52	7.05	8.49
4H	2H	7.44	8.09	8.50	9.13	10.54	3.98	4.63	5.04	5.67	7.09
	3H	9.25	9.80	10.32	10.87	12.29	5.32	5.86	6.38	6.93	8.35
	4H	9.94	10.44	11.01	11.50	12.94	5.86	6.35	6.93	7.42	8.86
	6H	10.45	10.87	11.53	11.96	13.40	6.27	6.69	7.35	7.78	9.22
	8H	10.62	11.01	11.70	12.09	13.55	6.39	6.79	7.47	7.87	9.32
	12H	10.70	11.06	11.80	12.16	13.62	6.45	6.81	7.55	7.90	9.36
8H	4H	9.90	10.30	10.98	11.38	12.83	6.13	6.53	7.21	7.60	9.06
	6H	10.46	10.79	11.56	11.91	13.36	6.64	6.96	7.74	8.08	9.54
	8H	10.67	10.96	11.78	12.06	13.53	6.82	7.11	7.93	8.21	9.69
	12H	10.80	11.05	11.91	12.15	13.66	6.93	7.19	8.05	8.29	9.80
12H	4H	9.85	10.21	10.95	11.30	12.76	6.13	6.49	7.23	7.58	9.04
	6H	10.43	10.72	11.54	11.82	13.30	6.68	6.97	7.79	8.07	9.55
	8H	10.65	10.90	11.76	12.00	13.51	6.89	7.14	8.00	8.24	9.75