

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924785

Luminaire Tested: DFN2DIP-PN3F0-030D060US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924785
REPORT IS A COMBINATION OF REPORTS P901073 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D060US950-FLLONL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8500.1 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924785

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924785

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34			28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29			24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25			20
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21			17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18			15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16			13
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14			12
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13			10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12			9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1302	1302	1302
5°	1303	1283	1292
10°	1292	1265	1274
15°	1272	1243	1246
20°	1246	1213	1217
25°	1219	1177	1184
30°	1186	1144	1143
35°	1155	1105	1099
40°	1117	1066	1057
45°	1079	1027	1014
50°	1037	985	964
55°	993	937	918
60°	944	880	866
65°	890	821	804
70°	821	750	737
75°	725	663	675
80°	610	553	556
85°	431	366	363

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1304 cd/sqm

TEST NUMBER: P924785

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	1.2
10°-20°	294.9	3.5
20°-30°	433.4	5.1
30°-40°	503.4	5.9
40°-50°	502.7	5.9
50°-60°	438.4	5.2
60°-70°	324.1	3.8
70°-80°	183.3	2.2
80°-90°	51.8	0.6
90°-100°	63.7	0.7
100°-110°	237.5	2.8
110°-120°	629.8	7.4
120°-130°	1044.5	12.3
130°-140°	1109.5	13.1
140°-150°	1031.2	12.1
150°-160°	829.1	9.8
160°-170°	534.2	6.3
170°-180°	183.9	2.2
0°-30°	833.1	9.8
0°-40°	1336.5	15.7
0°-60°	2277.6	26.8
0°-90°	2836.8	33.4
90°-120°	930.9	11.0
90°-150°	4116.2	48.4
90°-180°	5663.0	66.6
0°-180°	8500.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1114	1114	1114	1114	1114	
5°	1114	1109	1098	1106	1104	106
15°	1060	1054	1040	1044	1039	299
25°	959	951	933	935	933	441
35°	828	817	800	793	788	517
45°	674	666	650	638	634	520
55°	510	503	490	478	472	456
65°	344	337	327	317	312	340
75°	180	178	172	166	168	192
85°	44	43	42	38	38	49
90°	1	17	28	35	38	8
95°	91	45	54	62	60	108
105°	425	467	85	101	106	454
115°	804	828	862	215	115	791
125°	1136	1155	1181	1191	1195	1014
135°	1406	1429	1441	1455	1452	1086
145°	1631	1630	1654	1663	1656	1020
155°	1796	1784	1800	1809	1798	828
165°	1893	1884	1888	1898	1888	535
175°	1936	1926	1929	1939	1925	184
180°	1932	1932	1932	1932	1932	

TEST NUMBER: P924785

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1113.6	1113.6	1113.6	1113.6	1113.6
2.5°	1120.1	1114.7	1102.9	1113.6	1111.6
5°	1113.6	1109.4	1097.6	1106.2	1104.1
7.5°	1106.2	1099.8	1087.9	1096.6	1094.4
10°	1094.4	1086.9	1074.1	1082.6	1079.5
12.5°	1078.3	1071.9	1059.1	1064.4	1062.3
15°	1060.1	1053.8	1039.8	1044.1	1038.7
17.5°	1037.6	1031.3	1017.3	1022.6	1017.3
20°	1013.0	1006.6	991.6	994.7	990.5
22.5°	988.4	978.8	964.8	964.8	962.6
25°	959.4	950.9	932.7	934.8	932.7
27.5°	927.3	919.8	905.9	902.8	897.4
30°	895.2	886.6	870.6	867.4	863.1
32.5°	861.0	854.6	837.4	830.9	826.6
35°	827.8	817.1	799.9	793.4	788.1
37.5°	790.3	780.7	763.5	755.9	750.6
40°	751.8	743.2	726.0	716.5	712.2
42.5°	714.3	705.7	688.6	677.8	671.4
45°	673.6	666.1	650.0	638.2	633.9
47.5°	633.9	626.5	609.3	597.5	591.1
50°	592.1	586.8	571.8	556.8	551.5
52.5°	551.5	544.0	530.1	518.3	510.8
55°	509.8	503.3	490.5	477.7	472.3
57.5°	467.9	462.6	448.7	435.8	431.5
60°	426.2	422.0	407.0	395.1	392.0
62.5°	385.5	378.0	367.3	356.6	352.3
65°	343.8	337.3	326.6	317.0	311.7
67.5°	301.0	295.5	285.9	278.5	274.2
70°	261.3	257.0	247.4	239.8	235.6
72.5°	220.7	216.3	210.9	203.5	200.3
75°	179.8	177.8	172.4	166.0	168.2
77.5°	143.5	139.2	137.0	133.8	130.7
80°	107.1	106.0	103.8	100.6	98.5
82.5°	72.8	72.8	71.8	67.4	67.4
85°	43.9	42.8	41.8	38.5	37.5
87.5°	19.3	17.2	15.0	11.8	10.7
90°	1.3	16.8	27.9	35.0	37.7
92.5°	35.0	29.4	33.5	36.3	37.7
95°	90.8	44.6	54.5	61.6	60.1
97.5°	163.5	48.9	71.2	75.6	76.9
100°	247.5	55.9	79.7	90.8	93.6
102.5°	339.6	337.0	82.5	97.8	102.1
105°	424.9	466.9	85.3	100.6	106.3
107.5°	524.2	559.0	88.1	103.4	109.0
110°	619.3	648.5	244.7	104.9	110.4

TEST NUMBER: P924785

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	708.7	733.8	710.1	107.5	111.9
115°	803.7	827.5	862.5	215.3	114.7
117.5°	886.2	914.1	938.0	738.0	371.8
120°	978.5	999.4	1024.7	1041.4	852.7
122.5°	1056.7	1079.1	1107.1	1115.4	1116.9
125°	1136.4	1154.6	1181.1	1191.0	1195.1
127.5°	1209.1	1228.7	1249.7	1263.7	1265.0
130°	1277.6	1300.0	1315.3	1330.7	1329.4
132.5°	1347.5	1365.7	1381.0	1393.6	1392.3
135°	1406.3	1428.7	1441.1	1455.2	1452.4
137.5°	1467.6	1484.4	1498.5	1512.5	1508.4
140°	1527.7	1539.1	1554.4	1566.9	1560.0
142.5°	1578.2	1588.0	1606.2	1617.2	1610.3
145°	1631.3	1629.8	1653.6	1663.4	1656.4
147.5°	1677.3	1673.1	1696.9	1703.8	1698.4
150°	1722.2	1712.3	1734.8	1743.1	1736.1
152.5°	1759.8	1748.7	1769.6	1778.1	1768.2
155°	1796.2	1783.7	1800.5	1808.8	1797.6
157.5°	1825.6	1814.4	1827.0	1836.8	1825.6
160°	1850.8	1842.3	1850.8	1859.1	1849.3
162.5°	1873.0	1864.7	1871.7	1881.5	1868.9
165°	1892.6	1884.3	1888.4	1898.3	1888.4
167.5°	1908.0	1899.6	1903.9	1913.7	1901.0
170°	1920.7	1912.2	1915.1	1924.8	1912.2
172.5°	1929.0	1920.7	1923.5	1933.3	1920.7
175°	1936.0	1926.1	1929.0	1938.7	1924.8
177.5°	1938.7	1929.0	1930.4	1940.2	1927.7
180°	1931.8	1931.8	1931.8	1931.8	1931.8

TEST NUMBER: P924785

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US950-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.38	7.11	7.46	8.19	9.68	5.94	6.67	7.03	7.75	9.24
	3H	8.02	8.67	9.12	9.77	11.28	7.54	8.19	8.63	9.29	10.79
	4H	8.60	9.22	9.71	10.31	11.83	8.11	8.73	9.22	9.83	11.34
	6H	8.99	9.56	10.10	10.66	12.18	8.50	9.07	9.61	10.17	11.69
	8H	9.08	9.63	10.20	10.74	12.26	8.59	9.14	9.71	10.25	11.77
	12H	9.13	9.64	10.25	10.75	12.29	8.63	9.15	9.75	10.25	11.80
4H	2H	6.82	7.44	7.93	8.53	10.05	6.47	7.09	7.58	8.18	9.70
	3H	8.66	9.18	9.79	10.31	11.83	8.26	8.78	9.38	9.90	11.43
	4H	9.37	9.84	10.49	10.96	12.50	8.95	9.43	10.08	10.54	12.09
	6H	9.87	10.28	11.00	11.41	12.95	9.45	9.86	10.58	10.99	12.53
	8H	10.01	10.39	11.14	11.52	13.08	9.59	9.97	10.72	11.09	12.65
	12H	10.08	10.42	11.23	11.56	13.12	9.64	9.98	10.79	11.12	12.68
8H	4H	9.55	9.93	10.68	11.06	12.61	9.18	9.56	10.31	10.69	12.24
	6H	10.17	10.48	11.32	11.65	13.20	9.79	10.11	10.95	11.28	12.83
	8H	10.38	10.66	11.54	11.81	13.38	10.00	10.27	11.16	11.42	13.00
	12H	10.50	10.75	11.67	11.89	13.50	10.10	10.35	11.27	11.49	13.10
12H	4H	9.53	9.87	10.68	11.01	12.57	9.17	9.51	10.32	10.65	12.21
	6H	10.20	10.47	11.35	11.62	13.19	9.83	10.11	10.99	11.26	12.83
	8H	10.43	10.67	11.59	11.81	13.42	10.05	10.30	11.22	11.44	13.05

END OF REPORT