

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924795

Luminaire Tested: DFN2DIP-PN3F0-030D080US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924795
REPORT IS A COMBINATION OF REPORTS P901102 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D080US950-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9988.4 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 85.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924795

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924795

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	101	101	101	101		90	90	90	90		69	69	69		50	50	50		33	33	33
1	92	88	85	81		82	79	76	73		61	59	57		44	43	42		29	28	28
2	84	77	71	67		75	69	64	60		53	50	47		39	37	35		26	25	24
3	77	68	61	56		68	61	55	50		47	43	40		35	32	30		23	22	21
4	70	60	53	47		62	54	48	43		42	38	34		31	28	26		21	19	18
5	65	54	46	40		57	48	42	37		38	33	30		28	25	23		19	17	16
6	59	48	40	35		53	43	37	32		34	29	26		25	22	20		17	15	14
7	55	43	36	30		49	39	32	28		31	26	23		23	20	17		16	14	12
8	51	39	32	27		45	35	29	25		28	23	20		21	18	16		14	13	11
9	47	36	29	24		42	32	26	22		25	21	18		19	16	14		13	11	10
10	44	33	26	21		39	29	23	19		23	19	16		18	15	13		12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1383	1383	1383
5°	1384	1360	1369
10°	1370	1332	1324
15°	1350	1287	1254
20°	1324	1226	1169
25°	1298	1157	1087
30°	1263	1086	984
35°	1228	1010	892
40°	1193	932	788
45°	1152	846	693
50°	1110	758	601
55°	1066	665	512
60°	1015	567	421
65°	956	468	378
70°	884	376	341
75°	794	330	309
80°	665	273	266
85°	451	178	196

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1740 cd/sqm

TEST NUMBER: P924795

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	1.1
10°-20°	304.3	3.0
20°-30°	427.3	4.3
30°-40°	465.7	4.7
40°-50°	428.1	4.3
50°-60°	336.2	3.4
60°-70°	218.8	2.2
70°-80°	112.6	1.1
80°-90°	33.3	0.3
90°-100°	84.9	0.9
100°-110°	316.6	3.2
110°-120°	839.7	8.4
120°-130°	1392.7	13.9
130°-140°	1479.4	14.8
140°-150°	1374.9	13.8
150°-160°	1105.4	11.1
160°-170°	712.3	7.1
170°-180°	245.2	2.5
0°-30°	842.5	8.4
0°-40°	1308.2	13.1
0°-60°	2072.5	20.7
0°-90°	2437.2	24.4
90°-120°	1241.3	12.4
90°-150°	5488.3	54.9
90°-180°	7551.0	75.6
0°-180°	9988.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1183	1178	1164	1173	1170	112
15°	1125	1113	1077	1057	1046	317
25°	1021	987	916	872	856	470
35°	880	825	731	664	640	551
45°	719	648	535	459	434	556
55°	547	464	348	284	263	489
65°	369	283	186	150	147	366
75°	197	122	86	78	77	208
85°	46	24	20	20	20	53
90°	2	22	37	47	50	9
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	

TEST NUMBER: P924795

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1182.9	1182.9	1182.9	1182.9	1182.9
2.5°	1188.2	1182.9	1171.0	1181.8	1179.7
5°	1182.9	1177.5	1163.6	1173.2	1170.0
7.5°	1173.2	1166.8	1151.9	1156.1	1150.7
10°	1160.4	1152.9	1131.5	1128.2	1121.9
12.5°	1144.3	1134.7	1105.8	1099.4	1087.6
15°	1125.1	1113.2	1076.9	1056.6	1045.9
17.5°	1102.5	1085.5	1040.4	1017.0	999.8
20°	1076.9	1055.4	1001.9	975.3	951.6
22.5°	1049.1	1024.4	962.3	926.0	909.9
25°	1021.3	986.9	916.3	872.4	856.3
27.5°	988.1	951.6	873.5	823.2	798.5
30°	952.8	912.0	826.4	771.9	742.9
32.5°	918.4	869.2	781.5	717.2	690.4
35°	880.0	825.3	731.1	663.7	640.1
37.5°	842.5	783.5	684.0	610.1	583.5
40°	802.9	738.7	634.8	558.8	531.0
42.5°	762.2	693.7	585.6	506.3	479.6
45°	719.4	647.6	535.3	459.2	433.5
47.5°	678.7	602.7	487.1	411.0	387.5
50°	633.7	557.7	440.0	366.0	343.6
52.5°	589.8	509.5	395.1	324.4	304.0
55°	546.9	463.5	347.8	283.7	263.4
57.5°	503.1	417.5	306.2	246.2	229.1
60°	458.1	372.5	262.3	207.7	190.6
62.5°	414.3	328.7	224.8	173.4	164.9
65°	369.3	282.6	186.2	149.9	146.6
67.5°	326.6	239.7	149.9	131.7	128.4
70°	281.5	198.1	124.1	113.4	109.1
72.5°	238.7	159.4	103.8	95.3	93.1
75°	196.9	122.0	85.7	78.1	77.1
77.5°	155.2	86.6	67.4	63.2	61.0
80°	116.7	62.1	51.3	47.1	47.1
82.5°	81.3	41.8	35.3	33.2	33.2
85°	46.0	23.5	20.3	20.3	20.3
87.5°	17.2	8.5	8.5	7.5	7.5
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2

TEST NUMBER: P924795

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7

TEST NUMBER: P924795

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.17	5.82	6.32	6.96	8.56	1.13	1.79	2.29	2.93	4.52
	3H	6.82	7.41	7.99	8.56	10.17	2.30	2.89	3.46	4.03	5.65
	4H	7.42	7.98	8.59	9.13	10.74	2.74	3.30	3.91	4.44	6.06
	6H	7.83	8.34	9.01	9.49	11.12	3.05	3.56	4.22	4.71	6.33
	8H	7.95	8.43	9.13	9.60	11.22	3.13	3.62	4.31	4.78	6.40
	12H	8.00	8.46	9.18	9.62	11.26	3.16	3.63	4.35	4.78	6.42
4H	2H	5.16	5.72	6.34	6.87	8.48	1.70	2.26	2.88	3.41	5.02
	3H	6.97	7.43	8.15	8.60	10.23	3.03	3.49	4.21	4.67	6.29
	4H	7.65	8.08	8.83	9.24	10.88	3.56	3.99	4.75	5.15	6.80
	6H	8.15	8.51	9.33	9.70	11.33	3.97	4.33	5.16	5.52	7.15
	8H	8.32	8.66	9.50	9.83	11.48	4.09	4.43	5.28	5.61	7.26
	12H	8.40	8.71	9.60	9.89	11.55	4.14	4.45	5.35	5.64	7.30
8H	4H	7.60	7.94	8.79	9.12	10.77	3.83	4.17	5.01	5.34	7.00
	6H	8.15	8.43	9.36	9.65	11.30	4.33	4.61	5.54	5.83	7.48
	8H	8.37	8.61	9.58	9.80	11.47	4.52	4.76	5.73	5.96	7.63
	12H	8.49	8.71	9.71	9.90	11.60	4.62	4.84	5.84	6.03	7.73
12H	4H	7.54	7.85	8.75	9.04	10.70	3.82	4.13	5.03	5.32	6.98
	6H	8.13	8.37	9.34	9.57	11.24	4.38	4.62	5.59	5.82	7.49
	8H	8.34	8.55	9.55	9.74	11.44	4.58	4.79	5.79	5.98	7.69

END OF REPORT