

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924805

Luminaire Tested: DFN2DIP-PN3F0-040D040US950-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P924805  
REPORT IS A COMBINATION OF REPORTS P901047 AND P897955  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-040D040US950-FLONL  
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7555.7 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 64.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9972  
Total Harmonic Distortion (THDi): 0.128  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P924805  
CATALOG NUMBER: DFN2DIP-PN3F0-040D040US950-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P924805  
 CATALOG NUMBER: DFN2DIP-PN3F0-040D040US950-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1736	1736	1736
5°	1737	1710	1722
10°	1722	1686	1698
15°	1696	1657	1661
20°	1661	1617	1623
25°	1626	1570	1579
30°	1582	1526	1524
35°	1540	1474	1465
40°	1489	1421	1409
45°	1439	1369	1352
50°	1383	1314	1285
55°	1324	1250	1224
60°	1258	1174	1154
65°	1186	1095	1072
70°	1094	999	983
75°	967	884	899
80°	813	737	742
85°	574	487	484

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1439 cd/sqm



TEST NUMBER: P924805

CATALOG NUMBER: DFN2DIP-PN3F0-040D040US950-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.8	1.8
10°-20°	393.2	5.2
20°-30°	577.9	7.6
30°-40°	671.2	8.9
40°-50°	670.3	8.9
50°-60°	584.5	7.7
60°-70°	432.1	5.7
70°-80°	244.5	3.2
80°-90°	66.8	0.9
90°-100°	42.5	0.6
100°-110°	158.3	2.1
110°-120°	419.9	5.6
120°-130°	696.4	9.2
130°-140°	739.7	9.8
140°-150°	687.5	9.1
150°-160°	552.7	7.3
160°-170°	356.1	4.7
170°-180°	122.6	1.6
0°-30°	1110.8	14.7
0°-40°	1782.0	23.6
0°-60°	3036.8	40.2
0°-90°	3780.1	50.0
90°-120°	620.6	8.2
90°-150°	2744.1	36.3
90°-180°	3776.0	50.0
0°-180°	7555.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	1	11	19	23	25	7
95°	60	30	36	41	40	72
105°	283	311	57	67	71	303
115°	536	552	575	144	76	527
125°	758	770	787	794	797	676
135°	938	952	961	970	968	724
145°	1088	1087	1102	1109	1104	680
155°	1198	1189	1200	1206	1198	552
165°	1262	1256	1259	1266	1259	356
175°	1291	1284	1286	1292	1283	123
180°	1288	1288	1288	1288	1288	



TEST NUMBER: P924805

CATALOG NUMBER: DFN2DIP-PN3F0-040D040US950-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	0.9	11.2	18.6	23.4	25.1
92.5°	23.4	19.6	22.3	24.2	25.1
95°	60.5	29.8	36.3	41.0	40.1
97.5°	109.0	32.6	47.5	50.4	51.2
100°	164.9	37.3	53.1	60.5	62.4
102.5°	226.4	224.7	55.0	65.2	68.0
105°	283.2	311.3	56.9	67.1	70.8
107.5°	349.5	372.7	58.8	69.0	72.7
110°	412.9	432.4	163.1	69.9	73.6



TEST NUMBER: P924805

CATALOG NUMBER: DFN2DIP-PN3F0-040D040US950-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	472.5	489.2	473.4	71.7	74.6
115°	535.8	551.6	575.0	143.5	76.5
117.5°	590.8	609.4	625.3	492.0	247.8
120°	652.3	666.3	683.1	694.3	568.5
122.5°	704.4	719.4	738.1	743.6	744.6
125°	757.6	769.8	787.4	794.0	796.8
127.5°	806.0	819.1	833.1	842.5	843.3
130°	851.7	866.7	876.8	887.1	886.3
132.5°	898.3	910.5	920.7	929.1	928.2
135°	937.5	952.5	960.8	970.1	968.3
137.5°	978.4	989.6	999.0	1008.3	1005.5
140°	1018.5	1026.0	1036.2	1044.6	1040.0
142.5°	1052.2	1058.7	1070.8	1078.1	1073.5
145°	1087.6	1086.6	1102.3	1108.9	1104.3
147.5°	1118.2	1115.4	1131.3	1135.9	1132.3
150°	1148.0	1141.6	1156.5	1162.1	1157.4
152.5°	1173.2	1165.8	1179.7	1185.3	1178.9
155°	1197.5	1189.2	1200.3	1205.9	1198.4
157.5°	1217.0	1209.6	1218.1	1224.6	1217.0
160°	1233.8	1228.2	1233.8	1239.3	1232.9
162.5°	1248.7	1243.2	1247.8	1254.3	1245.9
165°	1261.8	1256.2	1259.0	1265.5	1259.0
167.5°	1272.1	1266.3	1269.3	1275.8	1267.4
170°	1280.5	1274.8	1276.6	1283.2	1274.8
172.5°	1286.0	1280.5	1282.4	1288.9	1280.5
175°	1290.6	1284.1	1286.0	1292.5	1283.2
177.5°	1292.5	1286.0	1286.9	1293.5	1285.1
180°	1287.9	1287.9	1287.9	1287.9	1287.9



TEST NUMBER: P924805  
 CATALOG NUMBER: DFN2DIP-PN3F0-040D040US950-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.15	10.01	10.11	10.99	12.26	8.71	9.57	9.67	10.55	11.82
	3H	10.81	11.58	11.77	12.56	13.85	10.32	11.10	11.29	12.08	13.37
	4H	11.39	12.12	12.37	13.11	14.41	10.91	11.64	11.89	12.62	13.92
	6H	11.79	12.46	12.78	13.45	14.76	11.30	11.97	12.29	12.96	14.27
	8H	11.89	12.53	12.89	13.54	14.85	11.40	12.04	12.40	13.05	14.36
	12H	11.93	12.54	12.94	13.55	14.88	11.44	12.05	12.44	13.05	14.38
4H	2H	9.61	10.34	10.60	11.33	12.63	9.26	9.99	10.25	10.98	12.28
	3H	11.47	12.08	12.47	13.09	14.41	11.07	11.68	12.06	12.69	14.01
	4H	12.18	12.74	13.18	13.74	15.08	11.76	12.32	12.77	13.33	14.67
	6H	12.69	13.17	13.70	14.20	15.54	12.26	12.75	13.28	13.78	15.11
	8H	12.83	13.28	13.85	14.31	15.66	12.41	12.86	13.43	13.88	15.23
	12H	12.90	13.31	13.94	14.35	15.71	12.47	12.87	13.50	13.91	15.27
8H	4H	12.37	12.82	13.39	13.84	15.19	12.00	12.45	13.02	13.47	14.82
	6H	12.99	13.37	14.04	14.43	15.78	12.62	12.99	13.66	14.06	15.40
	8H	13.21	13.54	14.26	14.59	15.96	12.83	13.16	13.88	14.21	15.57
	12H	13.34	13.63	14.39	14.67	16.08	12.94	13.23	13.99	14.27	15.68
12H	4H	12.36	12.76	13.39	13.80	15.16	11.99	12.40	13.03	13.44	14.79
	6H	13.02	13.35	14.07	14.40	15.77	12.66	12.99	13.71	14.04	15.40
	8H	13.26	13.55	14.31	14.59	16.00	12.89	13.18	13.94	14.22	15.63