

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924833

Luminaire Tested: DFN2DIP-PN3F0-050D040US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924833
REPORT IS A COMBINATION OF REPORTS P901049 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-050D040US950-FLLONL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8500.1 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924833

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924833

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	54	53	52
2	90	83	76	71	84	77	72	67	66	62	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	50	46	43	42	39	37
4	75	64	56	50	70	60	53	48	52	47	42	45	40	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2170	2170	2170
5°	2172	2138	2153
10°	2153	2108	2123
15°	2120	2071	2076
20°	2076	2022	2029
25°	2032	1962	1974
30°	1977	1907	1905
35°	1925	1842	1831
40°	1862	1777	1761
45°	1798	1711	1690
50°	1729	1642	1607
55°	1656	1562	1530
60°	1573	1467	1443
65°	1483	1369	1340
70°	1368	1249	1228
75°	1209	1105	1124
80°	1017	922	928
85°	717	609	605

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1798 cd/sqm

TEST NUMBER: P924833

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	2.1
10°-20°	491.5	5.8
20°-30°	722.3	8.5
30°-40°	838.9	9.9
40°-50°	837.9	9.9
50°-60°	730.6	8.6
60°-70°	540.1	6.4
70°-80°	305.6	3.6
80°-90°	82.9	1.0
90°-100°	42.5	0.5
100°-110°	158.3	1.9
110°-120°	419.9	4.9
120°-130°	696.4	8.2
130°-140°	739.7	8.7
140°-150°	687.5	8.1
150°-160°	552.7	6.5
160°-170°	356.1	4.2
170°-180°	122.6	1.4
0°-30°	1388.5	16.3
0°-40°	2227.5	26.2
0°-60°	3796.0	44.7
0°-90°	4724.6	55.6
90°-120°	620.6	7.3
90°-150°	2744.1	32.3
90°-180°	3776.0	44.4
0°-180°	8500.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1856	1856	1856	1856	1856	
5°	1856	1849	1829	1844	1840	176
15°	1767	1756	1733	1740	1731	498
25°	1599	1585	1554	1558	1554	736
35°	1380	1362	1333	1322	1314	862
45°	1123	1110	1083	1064	1057	866
55°	850	839	817	796	787	760
65°	573	562	544	528	519	567
75°	300	296	287	277	280	320
85°	73	71	70	64	62	82
90°	1	11	19	23	25	8
95°	60	30	36	41	40	72
105°	283	311	57	67	71	303
115°	536	552	575	144	76	527
125°	758	770	787	794	797	676
135°	938	952	961	970	968	724
145°	1088	1087	1102	1109	1104	680
155°	1198	1189	1200	1206	1198	552
165°	1262	1256	1259	1266	1259	356
175°	1291	1284	1286	1292	1283	123
180°	1288	1288	1288	1288	1288	

TEST NUMBER: P924833

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1856.0	1856.0	1856.0	1856.0	1856.0
2.5°	1866.8	1857.9	1838.3	1856.0	1852.7
5°	1856.0	1849.0	1829.3	1843.5	1840.2
7.5°	1843.5	1832.9	1813.3	1827.7	1824.0
10°	1824.0	1811.6	1790.2	1804.3	1799.1
12.5°	1797.1	1786.6	1765.2	1774.1	1770.4
15°	1766.8	1756.2	1732.9	1740.2	1731.2
17.5°	1729.3	1718.7	1695.4	1704.3	1695.4
20°	1688.3	1677.7	1652.7	1658.0	1651.0
22.5°	1647.4	1631.2	1608.0	1608.0	1604.3
25°	1599.1	1584.9	1554.5	1558.0	1554.5
27.5°	1545.5	1533.0	1509.9	1504.6	1495.7
30°	1492.1	1477.7	1451.0	1445.7	1438.5
32.5°	1434.9	1424.3	1395.7	1384.9	1377.8
35°	1379.6	1361.8	1333.2	1322.4	1313.6
37.5°	1317.1	1301.1	1272.4	1259.9	1251.1
40°	1253.0	1238.6	1210.0	1194.0	1186.9
42.5°	1190.5	1176.1	1147.7	1129.6	1119.0
45°	1122.7	1110.2	1083.3	1063.8	1056.6
47.5°	1056.6	1044.1	1015.5	995.8	985.2
50°	986.9	978.0	953.0	928.1	919.1
52.5°	919.1	906.6	883.5	863.8	851.3
55°	849.6	838.9	817.4	796.0	787.1
57.5°	779.9	771.0	747.7	726.4	719.1
60°	710.3	703.3	678.3	658.5	653.3
62.5°	642.5	630.0	612.2	594.3	587.2
65°	573.0	562.2	544.4	528.3	519.4
67.5°	501.6	492.6	476.6	464.1	456.9
70°	435.5	428.3	412.2	399.7	392.8
72.5°	367.8	360.5	351.6	339.1	333.8
75°	299.7	296.3	287.2	276.7	280.3
77.5°	239.2	231.9	228.4	223.0	217.8
80°	178.6	176.7	173.1	167.8	164.2
82.5°	121.3	121.3	119.6	112.5	112.5
85°	73.1	71.4	69.6	64.2	62.5
87.5°	32.1	28.6	25.0	19.7	17.8
90°	0.9	11.2	18.6	23.4	25.1
92.5°	23.4	19.6	22.3	24.2	25.1
95°	60.5	29.8	36.3	41.0	40.1
97.5°	109.0	32.6	47.5	50.4	51.2
100°	164.9	37.3	53.1	60.5	62.4
102.5°	226.4	224.7	55.0	65.2	68.0
105°	283.2	311.3	56.9	67.1	70.8
107.5°	349.5	372.7	58.8	69.0	72.7
110°	412.9	432.4	163.1	69.9	73.6



TEST NUMBER: P924833

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	472.5	489.2	473.4	71.7	74.6
115°	535.8	551.6	575.0	143.5	76.5
117.5°	590.8	609.4	625.3	492.0	247.8
120°	652.3	666.3	683.1	694.3	568.5
122.5°	704.4	719.4	738.1	743.6	744.6
125°	757.6	769.8	787.4	794.0	796.8
127.5°	806.0	819.1	833.1	842.5	843.3
130°	851.7	866.7	876.8	887.1	886.3
132.5°	898.3	910.5	920.7	929.1	928.2
135°	937.5	952.5	960.8	970.1	968.3
137.5°	978.4	989.6	999.0	1008.3	1005.5
140°	1018.5	1026.0	1036.2	1044.6	1040.0
142.5°	1052.2	1058.7	1070.8	1078.1	1073.5
145°	1087.6	1086.6	1102.3	1108.9	1104.3
147.5°	1118.2	1115.4	1131.3	1135.9	1132.3
150°	1148.0	1141.6	1156.5	1162.1	1157.4
152.5°	1173.2	1165.8	1179.7	1185.3	1178.9
155°	1197.5	1189.2	1200.3	1205.9	1198.4
157.5°	1217.0	1209.6	1218.1	1224.6	1217.0
160°	1233.8	1228.2	1233.8	1239.3	1232.9
162.5°	1248.7	1243.2	1247.8	1254.3	1245.9
165°	1261.8	1256.2	1259.0	1265.5	1259.0
167.5°	1272.1	1266.3	1269.3	1275.8	1267.4
170°	1280.5	1274.8	1276.6	1283.2	1274.8
172.5°	1286.0	1280.5	1282.4	1288.9	1280.5
175°	1290.6	1284.1	1286.0	1292.5	1283.2
177.5°	1292.5	1286.0	1286.9	1293.5	1285.1
180°	1287.9	1287.9	1287.9	1287.9	1287.9

TEST NUMBER: P924833

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.42	11.34	11.33	12.27	13.45	9.99	10.90	10.89	11.83	13.02
	3H	12.08	12.90	13.00	13.84	15.05	11.60	12.42	12.52	13.36	14.57
	4H	12.67	13.44	13.60	14.39	15.61	12.18	12.96	13.12	13.90	15.12
	6H	13.07	13.78	14.01	14.73	15.96	12.58	13.29	13.52	14.24	15.48
	8H	13.17	13.85	14.12	14.82	16.05	12.68	13.36	13.63	14.33	15.56
	12H	13.22	13.87	14.18	14.82	16.08	12.72	13.37	13.68	14.33	15.59
4H	2H	10.89	11.66	11.83	12.61	13.83	10.54	11.31	11.48	12.25	13.48
	3H	12.75	13.40	13.70	14.37	15.61	12.35	13.00	13.30	13.97	15.21
	4H	13.46	14.06	14.42	15.02	16.28	13.05	13.64	14.01	14.60	15.87
	6H	13.98	14.49	14.95	15.48	16.74	13.55	14.06	14.53	15.05	16.31
	8H	14.12	14.60	15.10	15.58	16.86	13.70	14.17	14.67	15.16	16.43
	12H	14.20	14.63	15.19	15.63	16.91	13.76	14.19	14.75	15.19	16.47
8H	4H	13.66	14.14	14.64	15.12	16.40	13.29	13.77	14.27	14.75	16.03
	6H	14.29	14.68	15.29	15.71	16.98	13.91	14.31	14.91	15.33	16.60
	8H	14.50	14.85	15.51	15.86	17.16	14.12	14.47	15.13	15.48	16.77
	12H	14.63	14.94	15.65	15.95	17.28	14.23	14.54	15.25	15.55	16.88
12H	4H	13.65	14.08	14.64	15.08	16.36	13.29	13.72	14.28	14.72	16.00
	6H	14.32	14.66	15.32	15.68	16.97	13.95	14.30	14.96	15.31	16.60
	8H	14.55	14.86	15.57	15.87	17.20	14.18	14.49	15.20	15.50	16.83