

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924834

Luminaire Tested: DFN2DIP-PN3F0-050D040US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924834
REPORT IS A COMBINATION OF REPORTS P899530 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-050D040US950-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7431.7 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924834

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924834

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2305	2305	2305
5°	2307	2266	2282
10°	2283	2220	2206
15°	2250	2145	2091
20°	2207	2043	1949
25°	2163	1928	1812
30°	2104	1810	1639
35°	2047	1684	1487
40°	1988	1554	1313
45°	1920	1409	1155
50°	1850	1263	1001
55°	1776	1108	853
60°	1691	945	701
65°	1593	781	630
70°	1474	627	569
75°	1324	549	515
80°	1107	456	443
85°	752	297	328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1920 cd/sqm

TEST NUMBER: P924834

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.5
10°-20°	507.2	6.8
20°-30°	712.1	9.6
30°-40°	776.3	10.4
40°-50°	713.5	9.6
50°-60°	560.3	7.5
60°-70°	364.7	4.9
70°-80°	187.7	2.5
80°-90°	51.4	0.7
90°-100°	74.7	1.0
100°-110°	237.3	3.2
110°-120°	406.1	5.5
120°-130°	534.0	7.2
130°-140°	599.4	8.1
140°-150°	587.8	7.9
150°-160°	493.1	6.6
160°-170°	327.0	4.4
170°-180°	114.3	1.5
0°-30°	1404.1	18.9
0°-40°	2180.4	29.3
0°-60°	3454.1	46.5
0°-90°	4058.0	54.6
90°-120°	718.0	9.7
90°-150°	2439.3	32.8
90°-180°	3374.0	45.4
0°-180°	7431.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1971	1963	1939	1955	1950	187
15°	1875	1855	1795	1761	1743	528
25°	1702	1645	1527	1454	1427	783
35°	1467	1376	1219	1106	1067	918
45°	1199	1079	892	765	722	926
55°	912	772	580	473	439	815
65°	616	471	310	250	244	610
75°	328	203	143	130	128	347
85°	77	39	34	34	34	88
90°	1	13	36	34	34	7
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	

TEST NUMBER: P924834

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1971.4	1971.4	1971.4	1971.4	1971.4
2.5°	1980.3	1971.4	1951.8	1969.7	1966.1
5°	1971.4	1962.6	1939.3	1955.3	1950.1
7.5°	1955.3	1944.7	1919.7	1926.8	1917.8
10°	1933.9	1921.5	1885.9	1880.4	1869.7
12.5°	1907.2	1891.2	1842.9	1832.3	1812.6
15°	1875.1	1855.4	1794.9	1761.0	1743.1
17.5°	1837.6	1809.1	1734.1	1694.9	1666.3
20°	1794.9	1759.1	1669.9	1625.4	1586.0
22.5°	1748.5	1707.4	1603.9	1543.3	1516.6
25°	1702.0	1644.9	1527.2	1454.1	1427.2
27.5°	1646.8	1586.0	1455.8	1371.9	1330.9
30°	1587.9	1520.0	1377.3	1286.4	1238.1
32.5°	1530.8	1448.6	1302.5	1195.4	1150.7
35°	1466.6	1375.6	1218.6	1106.2	1066.9
37.5°	1404.1	1305.9	1140.1	1016.9	972.4
40°	1338.1	1231.1	1057.9	931.3	884.9
42.5°	1270.3	1156.2	975.9	843.8	799.4
45°	1199.0	1079.4	892.1	765.3	722.5
47.5°	1131.2	1004.6	811.9	685.1	645.9
50°	1056.3	929.6	733.3	610.1	572.8
52.5°	983.0	849.2	658.4	540.6	506.8
55°	911.6	772.5	579.7	472.8	438.9
57.5°	838.6	695.8	510.3	410.4	381.8
60°	763.6	620.9	437.0	346.2	317.6
62.5°	690.5	547.8	374.6	289.1	274.8
65°	615.5	471.0	310.4	249.9	244.4
67.5°	544.2	399.6	249.9	219.4	214.1
70°	469.3	330.1	206.9	189.1	181.9
72.5°	397.9	265.8	173.1	158.8	155.2
75°	328.3	203.3	142.7	130.2	128.5
77.5°	258.7	144.4	112.5	105.2	101.6
80°	194.4	103.5	85.6	78.5	78.5
82.5°	135.6	69.6	58.9	55.2	55.2
85°	76.7	39.2	33.9	33.9	33.9
87.5°	28.6	14.2	14.2	12.5	12.5
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7

TEST NUMBER: P924834

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8

TEST NUMBER: P924834

CATALOG NUMBER: DFN2DIP-PN3F0-050D040US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.43	11.30	11.35	12.23	13.44	6.39	7.26	7.32	8.20	9.41
	3H	12.10	12.88	13.04	13.83	15.06	7.58	8.36	8.51	9.30	10.53
	4H	12.71	13.44	13.66	14.39	15.63	8.03	8.76	8.98	9.71	10.95
	6H	13.13	13.80	14.09	14.76	16.01	8.34	9.02	9.31	9.98	11.23
	8H	13.25	13.89	14.22	14.87	16.12	8.43	9.08	9.40	10.05	11.30
	12H	13.31	13.92	14.29	14.89	16.17	8.47	9.09	9.45	10.05	11.33
4H	2H	10.45	11.18	11.40	12.13	13.37	6.99	7.72	7.95	8.68	9.92
	3H	12.27	12.88	13.24	13.87	15.12	8.34	8.95	9.30	9.93	11.18
	4H	12.96	13.52	13.94	14.50	15.77	8.88	9.44	9.86	10.41	11.69
	6H	13.47	13.95	14.46	14.95	16.23	9.30	9.77	10.28	10.77	12.05
	8H	13.65	14.09	14.64	15.09	16.38	9.42	9.87	10.41	10.86	12.15
	12H	13.74	14.14	14.75	15.15	16.45	9.49	9.89	10.49	10.90	12.19
8H	4H	12.93	13.38	13.92	14.37	15.66	9.16	9.61	10.15	10.60	11.89
	6H	13.49	13.86	14.51	14.90	16.19	9.67	10.04	10.69	11.08	12.36
	8H	13.71	14.03	14.73	15.05	16.36	9.86	10.18	10.88	11.20	12.51
	12H	13.84	14.13	14.87	15.14	16.50	9.97	10.26	11.00	11.27	12.63
12H	4H	12.89	13.29	13.89	14.30	15.59	9.17	9.57	10.17	10.58	11.87
	6H	13.47	13.79	14.49	14.82	16.12	9.72	10.05	10.74	11.07	12.37
	8H	13.69	13.97	14.71	14.99	16.34	9.93	10.21	10.95	11.23	12.58

END OF REPORT