

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924915

Luminaire Tested: DFN2DIP-PN3F0-080D030US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924915
REPORT IS A COMBINATION OF REPORTS P901042 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D030US950-RLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9320.6 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 103.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924915
CATALOG NUMBER: DFN2DIP-PN3F0-080D030US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924915
 CATALOG NUMBER: DFN2DIP-PN3F0-080D030US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20									
RC	80					70					50					30					10					0				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0						
RCR	0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74	74	74	74	60				
1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	64	64	64	64	64	64	60				
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	59	57	55	55	55	55	55	55	55	55	55	51				
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48	48	48	48	48	48	48	48	48	44				
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42	42	42	42	42	42	42	42	42	39				
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	37	37	37	37	37	37	37	37	34				
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	33	33	33	33	33	33	33	33	30				
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	32	29	29	29	29	29	29	29	29	29	27				
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	27	27	27	27	27	27	27	27	24				
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	24	24	24	24	24	24	24	24	22				
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	22	22	22	22	22	22	22	22	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3687	3687	3687
5°	3691	3626	3650
10°	3652	3552	3530
15°	3600	3433	3345
20°	3531	3268	3118
25°	3461	3085	2900
30°	3367	2897	2623
35°	3275	2695	2380
40°	3181	2486	2101
45°	3073	2255	1849
50°	2960	2021	1602
55°	2842	1773	1365
60°	2706	1513	1122
65°	2549	1249	1008
70°	2358	1003	910
75°	2118	879	825
80°	1771	729	710
85°	1204	474	524

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3073 cd/sqm



TEST NUMBER: P924915

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	3.2
10°-20°	811.5	8.7
20°-30°	1139.4	12.2
30°-40°	1242.0	13.3
40°-50°	1141.5	12.2
50°-60°	896.5	9.6
60°-70°	583.5	6.3
70°-80°	300.4	3.2
80°-90°	78.4	0.8
90°-100°	31.9	0.3
100°-110°	118.7	1.3
110°-120°	314.9	3.4
120°-130°	522.3	5.6
130°-140°	554.8	6.0
140°-150°	515.6	5.5
150°-160°	414.5	4.4
160°-170°	267.1	2.9
170°-180°	91.9	1.0
0°-30°	2246.6	24.1
0°-40°	3488.6	37.4
0°-60°	5526.6	59.3
0°-90°	6488.9	69.6
90°-120°	465.5	5.0
90°-150°	2058.1	22.1
90°-180°	2832.0	30.4
0°-180°	9320.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3154	3154	3154	3154	3154	
5°	3154	3140	3103	3128	3120	299
15°	3000	2969	2872	2818	2789	845
25°	2723	2632	2444	2327	2284	1252
35°	2347	2201	1950	1770	1707	1469
45°	1918	1727	1427	1224	1156	1481
55°	1459	1236	928	756	702	1303
65°	985	754	497	400	391	976
75°	525	325	228	208	206	555
85°	123	63	54	54	54	141
90°	1	8	14	18	19	9
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	



TEST NUMBER: P924915

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3154.3	3154.3	3154.3	3154.3	3154.3
2.5°	3168.5	3154.3	3122.8	3151.5	3145.8
5°	3154.3	3140.1	3102.8	3128.5	3120.1
7.5°	3128.5	3111.6	3071.6	3082.9	3068.5
10°	3094.3	3074.4	3017.4	3008.6	2991.6
12.5°	3051.7	3025.9	2948.6	2931.6	2900.2
15°	3000.1	2968.7	2871.7	2817.5	2789.0
17.5°	2940.1	2894.4	2774.5	2711.8	2666.0
20°	2871.7	2814.5	2671.9	2600.7	2537.6
22.5°	2797.5	2731.8	2566.2	2469.2	2426.5
25°	2723.3	2631.9	2443.5	2326.6	2283.6
27.5°	2634.9	2537.6	2329.3	2195.2	2129.4
30°	2540.7	2431.9	2203.6	2058.3	1981.0
32.5°	2449.2	2317.8	2084.0	1912.6	1841.1
35°	2346.6	2200.9	1949.8	1770.0	1706.9
37.5°	2246.6	2089.5	1824.1	1627.0	1555.8
40°	2141.0	1969.8	1692.7	1490.1	1415.8
42.5°	2032.5	1849.9	1561.5	1350.2	1278.9
45°	1918.3	1726.9	1427.4	1224.5	1156.1
47.5°	1809.9	1607.3	1299.0	1096.1	1033.4
50°	1689.9	1487.4	1173.3	976.1	916.4
52.5°	1572.8	1358.6	1053.3	865.0	810.8
55°	1458.6	1236.0	927.7	756.5	702.3
57.5°	1341.7	1113.3	816.5	656.6	610.8
60°	1221.7	993.4	699.3	553.9	508.2
62.5°	1104.8	876.4	599.4	462.5	439.8
65°	984.9	753.5	496.7	399.8	390.9
67.5°	870.7	639.4	399.8	351.0	342.6
70°	750.8	528.2	331.0	302.5	291.1
72.5°	636.6	425.2	276.9	254.1	248.3
75°	525.2	325.3	228.4	208.4	205.7
77.5°	414.0	231.1	179.9	168.4	162.7
80°	311.0	165.7	136.9	125.6	125.6
82.5°	216.8	111.4	94.2	88.4	88.4
85°	122.7	62.7	54.2	54.2	54.2
87.5°	45.7	22.7	22.7	20.0	20.0
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2



TEST NUMBER: P924915

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9



TEST NUMBER: P924915
 CATALOG NUMBER: DFN2DIP-PN3F0-080D030US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.30	14.33	14.08	15.12	16.08	9.27	10.29	10.05	11.08	12.05
	3H	14.99	15.90	15.78	16.71	17.70	10.47	11.38	11.26	12.18	13.18
	4H	15.60	16.46	16.41	17.28	18.28	10.92	11.78	11.73	12.59	13.60
	6H	16.03	16.82	16.85	17.64	18.66	11.25	12.04	12.07	12.86	13.88
	8H	16.16	16.91	16.99	17.75	18.77	11.34	12.10	12.17	12.93	13.95
	12H	16.22	16.94	17.06	17.77	18.82	11.39	12.11	12.22	12.94	13.98
4H	2H	13.34	14.21	14.16	15.02	16.02	9.89	10.75	10.70	11.56	12.56
	3H	15.18	15.90	16.01	16.74	17.76	11.25	11.96	12.07	12.81	13.83
	4H	15.88	16.53	16.71	17.37	18.42	11.80	12.45	12.63	13.29	14.34
	6H	16.40	16.96	17.25	17.83	18.88	12.22	12.78	13.07	13.65	14.70
	8H	16.57	17.10	17.43	17.96	19.02	12.35	12.87	13.20	13.73	14.80
	12H	16.67	17.14	17.55	18.03	19.10	12.42	12.89	13.29	13.77	14.84
8H	4H	15.86	16.38	16.71	17.24	18.31	12.09	12.61	12.94	13.47	14.54
	6H	16.43	16.86	17.31	17.76	18.83	12.60	13.04	13.49	13.94	15.01
	8H	16.64	17.02	17.53	17.92	19.00	12.79	13.17	13.69	14.07	15.16
	12H	16.78	17.12	17.68	18.01	19.15	12.91	13.25	13.81	14.14	15.28
12H	4H	15.82	16.29	16.69	17.17	18.24	12.10	12.57	12.97	13.45	14.52
	6H	16.40	16.78	17.29	17.68	18.77	12.65	13.04	13.55	13.94	15.02
	8H	16.63	16.96	17.52	17.85	18.99	12.87	13.20	13.76	14.09	15.23